

CYRAH

PTL2529-PBR/CLG

The totemic composition of the Cyrah lamp marries geometry and a stone-like finish to create a striking stack of shapes. Adding a matte surface texture and muted hue, the lunar grey glaze gives Cyrah an ancient, earthy look. Tapping into the trend of dusty, non-glossy ceramics, this lamp makes an artful statement on a side table or bedside.

*Due to the one-of-a-kind nature of the medium, exact colors and patterns may vary slightly from the image shown.

FINISHES

PATINA BRASS w/ Ceramic Lunar Grey
Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 28.5"
Width/Diameter: 20"
Canopy/Backplate: 5.75"
Product Weight: 14.3lb
Canopy/Backplate Shape: Round
Sloped Ceiling Compatible: No
Living Finish: No
Uplight Only: No

Shade

Shade 1: Fabric
Shade 1 Finish: White Linen 1
Shade 1 Top Width: 5"
Shade 1 Bottom L/W: 0" / 20"
Shade 1 Height: 10.5"

ELECTRICAL



Bulb 1

Bulb Included: No
Socket: E26 Medium Base
Bulb Type: A19
Max Wattage: 15
Bulb Quantity: 1
Bulb Included: No
Cord Type: SPT-2 SILVER
Switch Type: ON/OFF SWITCH ON SOCKET
Gem Box Required (2"x3"): No
Dark Sky: No

SHIPPING

Carton 1: 22" x 22" x 30"
Carton 1 Weight: 26lb
Shipping Method: Ground
Country of Origin: PH

