



Technical Data

Color	Natural
Sizes Available	S-XL
Packaging	Bulk Pack
Packed	10 Dozen/Case
Case Dimensions (in)	25.98 x 10.51 x 10.51
Case Weight (lbs)	35.27
Country of Origin	India
Hide	Top Grain Cowhide
Grade	Regular
Cuff	Slip-on
Stitching	Kevlar
Thumb	Keystone
Construction	Cut-and-Sewn
Certifications	Chromium VI Free
Product Circularity	--

PIP®

Regular Grade Top Grain Leather Drivers Glove with Split Cowhide Back and Kevlar® Stitching - Keystone Thumb

- Top Grain/Shoulder Split Cowhide leather construction provides comfort, durability, excellent abrasion resistance, and breathability
- Top Grain leather palm is smooth, provides durability and dexterity
- Shoulder Split Cowhide leather back provides comfort, durability, excellent abrasion resistance, and breathability
- Shoulder Split Cowhide leather back makes this glove more economical than full top grain construction
- Stitched with Kevlar® adding strength and burn resistance
- Drivers gloves feature slip-on styling to provide good fit and comfort

Applications

- General Applications
- Construction Applications
- Roofing
- Farming
- Utility Work
- Roping

Performance Data

ANSI Cut Level (2016)	--
ANSI Puncture Level	--
EN 388	--

Care Instructions



Do Not Wash



SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
68-163SB/S	Natural	S	616314008580	01616314008580	02616314008580
68-163SB/M	Natural	M	616314008597	01616314008597	02616314008597
68-163SB/L	Natural	L	616314008603	01616314008603	02616314008603
68-163SB/XL	Natural	XL	616314008610	01616314008610	02616314008610