



QRP® PolyTuff® Polyurethane Solvent Glove - 8 mil

- Packaged for ISO 5 (Class 100) applications
- Tough, chemical and solvent resistant to solvent process polyurethane, sulfur-free
- Protection from chlorinated solvents, (MeCL and TCE), acetone, xylene, freons and IPA
- Excellent resistance to punctures, snags and abrasion, coupled with high tactile sensitivity
- Ergonomic Comfort Curve hand specific design
- RoHS Compliant
- Meets or exceeds all applicable requirements of IEST-RP-CC005.4

Technical Data

Color	Clear
Sizes Available	S-XL
Packaging	Case
Packed	5 Bags/Case
Case Dimensions (in)	17.00 x 8.00 x 5.00
Case Weight (lbs)	2.60
Country of Origin	Japan
Polymer	Polyurethane
Grip	Smooth
Cuff	Straight
Length	12"
Powder	Powder Free
Thickness	8 Mil
Construction	Unsupported
Certifications	TAA Compliant

Performance Data

ISO Cleanroom

ISO 5 (Class 100)

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
20GS	Clear	S	616314277924	10616314277921	20616314277928
20GM	Clear	M	616314277917	10616314277914	20616314277911
20GL	Clear	L	616314277900	10616314277907	20616314277904
20GXL	Clear	XL	616314277931	10616314277938	20616314277935