



Technical Data

Color	Gray
Sizes Available	OS
Packaging	Bagged Each
Packed	50/Case
Case Dimensions (in)	20.20 x 18.40 x 16.10
Case Weight (lbs)	13.60
Country of Origin	Mexico
Ventilation	Indirect
Headband	Neoprene Rubber
Lens Color	Clear
Lens	Clear
Lens Coating	Anti-Fog,
Certifications	ANSI Z87.1, CSA Z94.3 Certified, TAA Compliant

UVEX® Stealth®

Indirect Vent Goggle with Gray Body, Clear Lens
and Hydroshield® Anti-Fog coating - Neoprene
Strap

- Futuristic, low profile design for chemical splash and impact
- Toric lens provides superior optics and peripheral vision
- Easiest lens replacement system available
- Hydroshield® coating permanently bonded to the lens
- Low profile design and indirect venting system for chemical splash and impact protection
- Soft, elastomer body flexes and conforms to the face for a secure, comfortable, gap-free fit
- Pivoting, quick-adjust headband provides easy adjustment
- Meets ANSI Z87.1+
- Meets CSA Z94.3

SKU Information

SKU	FRAME COLOR	LENS	LENS COLOR	LENS COATING	UPC	UPC (INNER)	UPC (CASE)
S3960HS	Gray	Clear	Clear	AF/	603390130878		50603390130873
S3960HS-BR	Gray				7898524003606		27898524003600
S3960HSI					603390131721		
S3960HSI-BR	Gray				603390134302		70603390134301

KEY: AF = Anti-Fog / AR = Anti-Reflective / AS = Anti-Scratch / FL360 = Fogless 3Sixty / U = Uncoated