# TORQUE WRENCH TESTER

## PCE-TWT 50



## Specification

| Torque | |
|---|---|
| Measuring range up to | 0,001 ... 50 Nm |
| Resolution | 0,001 Nm |
| Accuracy | ±1% of the measured value (of m.v.) |

| General technical data | |
|---|---|
| Measuring functions | peak, MAX, MIN, AVG |
| Units | Nm, kgf cm, lbf in |
| Display Typ | LCD |
| Display size | 3,3 Inch |
| Storage medium | Internal memory |
| Storage capacity | 99 Values |
| Data interface | RS232 |
| Automatic shutdown adjustable | 0 ... 9999 min. |
| Automatic switch-off can be deactivated | Yes |
| Menu language | English (GB), English (US) |
| Protection class (device) | IP40 |
| Power supply | 100 ... 240V AC / 12V DC |
| Connector type | Euro plug |
| Operating conditions | 5 ... 35 °C , 15 ... 80 %RH |
| Storage conditions | -10 ... 60 °C , 15 ... 80 %RH |
| Dimensions ( L x W x H ) | 370 x 250 x 160 mm |
| Weight | 11000 g |

PCE Americas Inc. dba PCE Instruments
1201 Jupiter Park Drive, Suite 8
Jupiter, FL 33458
USA

Phone: +1-561-320-9162
info@pce-americas.com