

Top Tec 4100 SAE 5W-40

Description

Fully synthetic low SAPS motor oil that provides exceptional protection against wear, reduced oil consumption and improved fuel consumption. Suitable for alternative fueled CNG and LPG vehicles. Use with extended oil change intervals as per manufacturer.

Properties

- outstanding engine cleanliness
- ideal with turbochargers and catalytic converters
- optimum oil pressure under all operating conditions
- smooth engine running
- miscible with all commercially available motor oils
- long engine service life
- high shear stability
- instant lubrication after cold start
- high lubrication reliability

Specifications / Approvals

ACEA C3 • API SQ • BMW Longlife-04 • MB-Approval 229.51

LIQUI MOLY recommends this product for vehicles or assemblies for which the following specifications or original spare part numbers are required:

Fiat 9.55535-H2 • Fiat 9.55535-M2 • Fiat 9.55535-S2 • Ford WSS-M2C 917-A • GM dexos2 • MB 229.31 • MB 229.52 • Renault RN 0700 • Renault RN 0710 • VW 505 00 • VW 505 01

Technical data

SAE class (engine oils)	5W-40 SAE J300
Density at 59 °F	0,855 g/cm ³ DIN 51757
Viscosity at 104 °F	88 mm ² /s ASTM D 7042-04
Viscosity at 212°F	14,3 mm ² /s ASTM D 7042-04
Viscosity at -31 °F (MRV)	< 60000 mPas ASTM D4684
Viscosity at -22 °F (CCS)	≤ 6600 mPas ASTM D5293
Viscosity index	169 DIN ISO 2909
HTHS at 302 °F	≥ 3,5 mPas ASTM D5481
Pour point	-43 °F DIN ISO 3016

Technical data

Evaporation loss (Noack)	9,5 % CEC-L-40-A-93
Flash point	449 °F DIN ISO 2592
Total base number	7,5 mg KOH/g DIN ISO 3771
Sulfate ash	≤ 0,8 g/100g DIN 51575
Color number (ASTM)	L 2,5 DIN ISO 2049

Areas of application

For gasoline or diesel engines where a motor oil according to current specifications is required or recommended. Tested safe with catalytic converters and turbochargers.

⚠ WARNING: This product can expose you to chemicals including toluene, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Application

Observe the manufacturers instructions!

Available pack sizes

1 l Canister plastic	2329 CAEN-CAFR-USEN
5 l Canister plastic	2330 CAEN-CAFR-USEN
60 l Black plate barrel	22067 CAEN-CAFR-USEN
205 l Black plate barrel	22068 CAEN-CAFR-USEN

Our information is based on thorough research and may be considered reliable, although not legally binding.

