

A high-visibility knitted glove with nitrile dipping and touchscreen functionality.

TEGERA® 8820

Learn more

VERY DURABLE WITH A PERFECT FIT

A high visibility knitted glove for precision work in dry-to moist environments. Flexible and soft with touchscreen functionality ensuring seamless transition between duties without having to remove the glove. Nitrile foam dipping for ultimate grip . Made of 15 gg fibre to ensure all-day comfort.

CHARACTERISTICS

- Good fingertip sensitivity
- Flexible
- Very durable
- Good grip
- Comfortable

FUNCTIONS

- Withstands contact heat up to 100°C
- For touchscreen
- Latex-free
- High visibility colour

ORIGINAL 04 EXCELLENT 2019 dermatest

OEKO TEX® STANDARD 100 SE 14-214 RISE

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

PREVENTS RISK OF

Abrasion injuries, Blisters, Scratches, lacerations, Contact with dirt

PRIMARY ENVIRONMENTS OF USE

Dry environments, Moist environments, Dirty environments

PRIMARY AREAS OF USE

Agricultural work, Airport work, Assembly, Building and construction, Construction, Repair work, Transport work, Warehouse work

PRIMARY INDUSTRIES OF USE

Agriculture, forestry and fishing, Rubber and plastics manufacturing, Basic metals manufacturing, Transportation and logistics, Electricity and gas supply, Building and construction, Mining and quarrying, Warehousing

TYPE OF WORK

Light weight

SPECIFICATION

TYPE Assembly gloves, Heat protection gloves, Precision work gloves
CATEGORY Cat. II
KNITTING GAUGE (GG) 15
LINING MATERIAL Polyester, Spandex
LENGTH 200-270 mm
DEXTERITY 5
GRIP DESIGN Micro foam grip pattern
COLOUR Black
PAIRS PER: BUNDLE/CARTON 12/120
DISPLAY TYPE Bulk pack
DIPPING Palm-dipped
DIPPING MATERIAL Nitrile foam
CUFF STYLE Knitwrist cuff
CUFF MATERIAL Textile
INNER MATERIAL SPECIFICATION Polyester, Elastane
OUTER MATERIAL SPECIFICATION Nitrile

COMPLIANCE

CE Cat. II

EAC TP TC 019:2011

EN ISO 21420:2020

EN 388:2016+A1:2018 4131A

EN 407:2020 (No flame protection) X1XXXX

ANSI 4 ABR

Contact heat rating valid for palm area only

FEATURES

For touchscreen

SIZE		ARTICLE NUMBER	EAN
5	XXS	8820-5	7340118389363
6	XS	8820-6	7340118389516
7	S	8820-7	7340118389660
8	M	8820-8	7340118389875
9	L	8820-9	7340118390055
10	XL	8820-10	7340118390239
11	XXL	8820-11	7340118390413
12	3XL	8820-12	7340118390598

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.