

# Panelboards

## Warehouse Stock/Unassembled

Selection

### AFCI/GFCI

Electronic Circuit Breakers		1-Pole		2-Pole		Catalog Number	
Trip Type	Breaker Type	Max IR (kA) at 120V	Amp Ratings Available	Max IR (kA) at 120/240	Amp Ratings Available		
Combination AFCI	BAF2	10	15	—	—	BA115AFC	
		10	20	—	—	BA120AFC	
	BAFH2	22	15	—	—	BA115AFCH	
		22	20	—	—	BA120AFCH	
	HBAF2	65	15	—	—	BA115AFCHH	
		65	20	—	—	BA120AFCHH	
	BAF	—	—	10	15	B215AFC	
		—	—	10	20	B220AFC	
BAFH	—	—	22	15	B215AFCH		
	—	—	22	20	B220AFCH		
Dual Function AFCI/GFCI	BFGA2	10	15	—	—	B115DF	
		10	20	—	—	B120DF	
	BFGAH2	22	15	—	—	B115DFH	
		22	20	—	—	B120DFH	
	HBFGA2	65	15	—	—	B115DFHH	
		65	20	—	—	B120DFHH	
GFCI Personnel Protection (5mA)	BLF2	10	15	—	—	BF115A	
		10	20	—	—	BF120A	
		10	30	—	—	BF130A	
	BLF	—	—	10	15	BF215A	
		—	—	10	20	BF220A	
		—	—	10	30	BF230A	
		—	—	10	40	BF240A	
		—	—	10	50	BF250A	
		—	—	10	60	BF260A	
	BLHF2	22	15	—	—	BF115AH	
		22	20	—	—	BF120AH	
		22	30	—	—	BF130AH	
	BLHF	—	—	22	15	BF215AH	
		—	—	22	20	BF220AH	
		—	—	22	30	BF230AH	
		—	—	22	40	BF240AH	
		—	—	22	50	BF250AH	
		—	—	22	60	BF260AH	
	HBLF2	65	15	—	—	BF115AHH	
		65	20	—	—	BF120AHH	
		65	30	—	—	BF130AHH	
	GFCI Ground Fault Equipment Protection (30mA)	BLE	10	15	—	—	BE1153
			10	20	—	—	BE1203
			10	30	—	—	BE130
—			—	10	15	BE215	
—			—	10	20	BE220	
—			—	10	30	BE230	
—			—	10	40	BE240	
—			—	10	50	BE250	
—			—	10	60	BE260	
BLEH			22	15	—	—	BE115H2
		22	20	—	—	BE120H2	
		22	30	—	—	BE130H2	
		—	—	22	15	BE215H2	
		—	—	22	20	BE220H2	
		—	—	22	30	BE230H2	
		—	—	22	40	BE240H2	
		—	—	22	50	BE250H2	
		—	—	22	60	BE260H2	

① Built to order. Additional "circuit" is included for neutral (via pigtail) and is NOT connected to bus. 2-pole is one phase and one neutral pigtail. 3-pole is two phase connections and one neutral pigtail.

② Allow 8-10 weeks for delivery

③ UL Listed as SWD (Switching Duty) Rated, suitable for 120V AC fluorescent lighting