SIEMENS

Data sheet US2:Q1520NC



Siemens Low Voltage Residential Circuit Breakers Miniature Thermal Mag Circuit Breakers - Duplex, Triplex, Quadplex are Circuit Protection Load Center Mains, Feeders, and Miniature Circuit Breakers. Type: QT Application: Electrical Distribution Standard: UL 489 Voltage Rating: 120V Amperage Rating: 15-20A Trip Range: Thermal Magnetic Interrupt Rating: 10 AIC Number Of Poles: 1P

number of poles	1
suitability for operation	Electrical Distribution
Model	
product brand name	SIEMENS
type of electrical connection	PLUG-IN
Mechanical Design	
depth [in]	3 in
design of the product	QT
height [in]	3 in
width [in]	1 in
General product approval	
standard	UL 489

last modified: 1/6/2021

Subject to change without notice
© Copyright Siemens