



CTR21PL



66.63" x 29.5" x 32.88" (H x W x D)

20.5 cu.ft. frost-free refrigerator-freezer with reversible stainless steel doors and gray cabinet

Highlights:

- Full 18 cu.ft. storage capacity to meet the needs of most kitchens
- ENERGY STAR certified performance for added efficiency and cost savings
- Fully featured for convenient storage with crispers, adjustable shelves, and more

Product Features:

Top Mount Refrigerator-Freezer	Full-size refrigerator-freezer ideal for break rooms and other kitchen settings
ENERGY STAR certified	Rated by the DOE to perform with more efficiency than federal standards require, saving your unit energy and you on higher utility costs
Frost-free operation	No-frost convenience requires no manual defrosting
Adjustable shelves	Rearrange refrigerator space to accommodate all sizes or remove shelves for simple cleanup
Interior light	Automatically illuminates when you open the door
Crisper drawers	Clear twin crispers with humidity control
Door storage	Keep bottles and condiments in easy reach
Gallon door storage	Lower refrigerator door shelf can hold gallon-sized containers
Adjustable thermostat	Interior thermostat with simple control panel for easy use



CTR21PL Specifications:

Overview	
Nominal Height	66.0" (168 cm)
Height of Cabinet	66.0" (168 cm)
Height to Hinge Cap	66.63" (169 cm)
Nominal Width	30.0" (76 cm)
Width	29.5" (75 cm)
Width with Door Open	30.25" (77 cm)
Nominal Depth	33.0" (84 cm)
Depth	32.88" (84 cm)
Depth with Handle	34.88" (89 cm)
Depth with door at 90°	60.25" (153 cm)
Capacity	20.5 cu.ft. (580 L)
Defrost Type	Frost-Free
Door	Stainless Look
Cabinet	Gray
US Electrical Safety	UL
Canadian Electrical Safety	ULC
Energy Usage/Year	390.0kWh/year
Amps	1.1
Voltage/Frequency	115 V AC/60 Hz
Weight	172.0 lbs. (78 kg)
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
UPC	761101089089

Refrigerator-Freezer	
Door Swing	RHD
Reversible	Yes
Adjustable Shelves	Yes
Crisper Qty	2
Crisper Finish	Transparent
Crisper Cover	Glass
Interior Light	Yes
Refrigerator - Interior Height	38.75" (98 cm)
Refrigerator - Interior Width	26.0" (66 cm)
Refrigerator - Interior Depth	27.0" (69 cm)
Refrigerator - Shelf Type	Glass

Refrigerator - Shelf Qty	2
Refrigerator - Full Door Shelves	2
Refrigerator - Half Door Shelves	2
Refrigerator - Temperature Range	36 to 46°F
Freezer - Interior Height	18.5" (47 cm)
Freezer - Interior Width	24.5" (62 cm)
Freezer - Interior Depth	22.25" (57 cm)
Freezer - Shelf Type	Wire
Freezer - Shelf Qty	1
Freezer - Full Door Shelves	2
Gallon Door Storage	Yes
Thermostat Type	Dial
Fan Type	Interior
Refrigerant Type	R600a
Refrigerant Amount	2.29 oz.
High Side PSI	150.0
Low Side PSI	60.0
Freezer - Temperature Range	0 to 10°F
Compressor Step Height	9.5" (24 cm)
Compressor Step Width	26.0" (66 cm)
Compressor Step Depth	9.0" (23 cm)

