

CHIASO

537-38-VPB

A series of concentric hoops dangle below the marionette suspension of the Chiasso chandelier, creating a sculptural sense of verticality. Within each ring, a convex curved diffuser directs light inwards, emitting a glow that surrounds the entire piece. Available in two three-light chandelier sizes, Chiasso's grandeur is enriched by a Vintage Patina Brass finish.

FINISHES

VINTAGE POLISHED BRASS

Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 16.25"

Width/Diameter: 38"

Minimum Height: 18.25"

Maximum Height: 77.75"

Canopy/Backplate: 13.75"

Hanging Type: 72" Chain

Product Weight: 9lb

Canopy/Backplate Shape: Round

Sloped Ceiling Compatible: No

Living Finish: Yes

Uplight Only: No

Shade

Shade 1: Acrylic

Shade 1 Finish: White

Shade 1 Top Width: 22"

Shade 1 Height: 2"

ELECTRICAL



Bulb 1

Bulb Included: N/A

Socket: Integrated LED

Max Wattage: 78

Bulb Quantity: 3

Wire Length: 144"

Cord Type: LOW VOLTAGE DC WIRE

Dimmer Type: TRIAC, 0-10 VOLT

Gem Box Required (2"x3"): No

Dark Sky: No

CRI: 90

Color Temp.: 2700k

Lumens: 2825

Title 24: No

Field Serviceable: No



SHIPPING

Carton 1: 40" x 38" x 13"

Carton 1 Weight: 22lb

Shipping Method: Truck Only

Country of Origin: VN

HUDSON VALLEY
LIGHTING GROUP

| hvlgroup.com | 1.800.814.3993