



PIP® Dom™

Cap Style Smooth Dome Hard Hat with HDPE Shell, 4-Point Textile Suspension and Wheel-Ratchet Adjustment

- Lightweight shell made with UV stabilized High Density Polyethylene (HDPE) reduces worker fatigue
- Smooth dome shell has a rain trough for extra convenience in adverse weather conditions
- 4-Point quick release suspension with strong textile straps and crown comfort pad provides a comfortable and secure fit
- Non-chaffing, replaceable foam sweatband for maximum sweat absorption
- SURE LOCK wheel adjustment system for one hand size adjustments
- Precise height adjustment settings to ensure proper depth

Applications

- Construction Applications
- Road Work
- Excavation
- Industrial Applications

Technical Data

Color	Lime, Royal, Red, Yellow, Sky Blue, Steel Blue, Black, Orange, White, Forest Green, Gray, Dark Green, Navy, Hi-Vis Yellow, Hi-Vis Orange
Sizes Available	OS
Packaging	Bagged Each
Packed	12/Case
Case Dimensions (in)	20.30 x 14.00 x 28.10
Case Weight (lbs)	13.23
Country of Origin	Canada
Shell Material	HDPE
Shell	Non-Vented
Brim Style	Cap Style
Brim Length	Standard
Size Adjustment	Wheel Ratchet
Suspension	4 Point Nylon Webbing Cradle
Sweatband	Felt Lined Foam
Size Range	53cm-63cm
Certifications	ANSI/ISEA Z89.1, CSA Z94.1 Certified, TAA Compliant

Performance Data

ANSI Type	Type I
Electrical Class	Class E

Care Instructions

The unit may be cleaned with soap and warm water and dried with a soft cloth. The helmet should not be cleaned with chemical or abrasive cleaners. The helmet should be stored out of direct sunlight, away from chemicals and not exposed to extremes of temperature.

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
280-HP341R-11	Black	OS	620606001197	10616314317214	10620606001194
280-HP341R-04	Dark Green	OS	620606001128	10616314317214	10620606001125
280-HP341R-74	Forest Green	OS	620606001241	10616314317252	10620606001248
280-HP341R-09	Gray	OS	620606001173	10616314317252	10620606001170
280-HP341R-31	Hi-Vis Orange	OS	620606002309	10616314418980	10620606002306
280-HP341R-44	Hi-Vis Yellow	OS	620606002316	10616314419024	10620606002313
280-HP341R-45	Lime	OS	620606198170	10616314415552	10620606198177
280-HP341R-08	Navy	OS	620606001166	10616314323420	10620606001163
280-HP341R-03	Orange	OS	620606001111	10616314323468	10620606001118
280-HP341R-15	Red	OS	620606001210	10616314323581	10620606001217
280-HP341R-17	Royal	OS	620606001227	10616314323598	10620606001224
280-HP341R-07	Sky Blue	OS	620606001159	10616314323581	10620606001156
280-HP341R-71	Steel Blue	OS	620606001234	10616314323635	10620606001231
280-HP341R-01	White	OS	620606001098	10616314317382	10620606001095
280-HP341R-02	Yellow	OS	620606001104	10616314323673	10620606001101