
MASTER®
THE PROFESSIONAL'S CHOICE SINCE 1953


Master MAC-18WB 18" High Velocity Wall Fan—3040 CFM, 1/6 HP, 120 Volt



- Compact design with included wall/ceiling mount, perfect for your home, garage, barn, or workshop
- All-metal construction for durability
- Direct-drive motor with high airflow, up to 3040 CFM
- Tilt-angle head for directional airflow control
- 1-year limited warranty

Product Description

When you need to cool down quickly, look no further than Master's industry-leading 18" High Velocity Wall/Ceiling Mount Fan. The heat of summer is no match for its powerful, direct-drive motor and long-lasting all-metal construction. Plus, the tilt-angle head lets you direct the airflow wherever's most convenient. Whether you're in the barn, relaxing at home on the patio, or working in the garage, this fan will do the job while giving your A/C and wallet a rest. Master – built for power.



©2021 Pinnacle Climate Technologies

Features and Benefits

- Great for your home patio, garage, barn, or workshop
- All-metal construction for durability
- Direct-drive motor with airflow up to 3040 CFM
- 1/6 HP industrial motor
- Tilt-angle head for directional airflow control
- All-metal safety guard
- Included wall/ceiling mount
- 3 variable speed settings for user preference
- Balanced blades for optimal air flow
- Suitable for outdoor use and damp locations
- 1-year limited warranty

Key Specs

Model Number	MAC-18WB
Brand	Master
Warranty	1-year limited warranty
Net Weight (lb.)	24
Air Flow (CFM)	1970 / 2590 / 3040
Motor Size (HP)	1/6
Variable Speed	Yes
Volts	120
Amps	1.0
Product Dimensions (L x W x H) (in.)	24 x 24 x 9

©2021 Pinnacle Climate Technologies