



Technical Data

Color	White
Sizes Available	10.5
Packaging	Boxed
Packed	32 Pair/Case
Case Dimensions (in)	33.50 x 25.50 x 26.50
Case Weight (lbs)	63.01
Country of Origin	United States
Polymer	Chlorosulfonated Polyethylene
Grip	Smooth
Cuff	Rolled
Length	32"
Powder	Powder Free
Thickness	15 Mil
Construction	Waterproof, Unsupported
Certifications	TAA Compliant

North®

15 Mil, 8" Port Ambidextrous CSM Glovebox Glove - 32"

- CSM (Chlorosulfonated Polyethylene) is a soft abrasion resistant material that provides superior resistance to ozone and oxidizing chemicals such as alcohols, alkalis, and acids
- White CSM surface will not hide contamination and can be easily cleaned (important for "clean" applications, such as in the pharmaceutical industry)
- Rolled bead cuff resists tearing, improves donning strength and maintains a secure seal on glovebox ports
- Available in 9.75" and 10.5" sizes (palm diameter)
- Every glove is electrically tested to detect holes or thin spots, ensuring greater safety
- Made in the USA

Care Instructions

Three year shelf life when stored in original packaging in a cool dry place away from light. Recommended temperature range: 50F to 86F (10C to 30C).

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
8Y1532A/9Q	White	9.75	883940165806		00883940165561
8Y1532A/10H	White	10.5	883940165790		00883940165554