

WMCS8 SERIES OUTDOOR LIGHTING

WESTGATE
THE FUTURE IS HERE...AND IT'S QUITE BRIGHT!

WMCS8-UDL-MCTD-BK-D
WMCS8-UDL-MCTD-BR-D
WMCS8-UDL-MCTD-WH-D
WMCS8-UDL-MCTD-SIL-D
8" LED SQUARE CYLINDER LIGHTS


MCT Multi Color Temperature (Selectable)

Customer Name: _____

Project Name: _____

Note: _____

Type: _____



10.39"(H) x 10.73"(W) x 7.99"(D)

8" LED Square Cylinder Lights – Sleek and modern square design with energy-efficient LED technology, ideal for indoor or outdoor applications. Provides powerful, uniform illumination with a clean architectural look.

Features

- Finish: Black, Bronze, Brushed Nickel & White
- Multi CCT (Selectable Switch on the Bottom of the Arm, Protected by Silicon Cover to be Waterproof)
- 7-Year Warranty
- Outdoor UP/Down Light

Technical Specifications

Electrical:

- Voltage: 120-277V AC
- Power Factor: >0.95
- Wattage: 40W
- Efficacy: 80 LPW
- THD: <20%

Mechanical:

- Housing: Die-cast Aluminum & Glass
- Finish: Black, Bronze, Silver & White
- Maximum Ambient Temperature: -68°F to 104°F
- Suitable for Wet Location
- 7-Year Warranty

Lighting:

- Dimming: 0-10V Dimming
- Total Lumens: 3200LM
- Color Temperatures: 3000K/4000K/5000K
- Multi CCT (Selectable Switch on the Bottom of the Arm, Protected by Silicon Cover to be Waterproof)
- Color Rendering Index: CRI ≥ 80
- Rated life: 70,000 hrs
- Beam angle: 45° for each side

Applications:

- Ideal for general site lighting, walkways, and stairways, alleys, loading docks, doorway, pathway and parking areas





Phone: (877) 805-2252 | Fax: (877) 805-2252
www.westgatemfg.com




WG-02 152022

Photometrics: WMCS8-UDL-MCTD-D



BUG Rating: B1-U5-G0



Other Views:

Black Finish:



Side View



Back View



Lens View

Bronze Finish:



Side View



Back View



Lens View

White Finish:



Side View



Back View



Lens View


Silver Finish:



Side View



Back View



Lens View



Performance Table: WMCS5-UDL-MCT-DD

MODEL NO.	Wattage	Voltage	Lumens	Color Temp.	BUG Rating	LPW
WMCS8-UDL-MCTD-BK-D WMCS8-UDL-MCTD-BR-D WMCS8-UDL-MCTD-WH-D WMCS8-UDL-MCTD-SIL-D	40W	120-277V	3200LM	3000K/ 4000K/ 5000K	B1-U5-G0	80

Sample Ordering

Model	Light Direction		Color Temp.	Finish	Dimming	
WMCS8	-	UDL	-	MCTD	-	DD

BK = Black
BR = Bronze
WH = White
SIL = Silver

Factory-Installed Option:

Blank = No Option For Accessories

OPT-PC-B = FOR 120V-277V PHOTOCELL

OPT-EM-WMC = INTERNAL EMERGENCY BACK UP BATTERY

FACTORY-INSTALLED OPTION:



OPT-PC-B
FOR 120V-277V PHOTOCELL



OPT-EM-WMC
INTERNAL EMERGENCY
BACK UP BATTERY

