




LVE Vanity Lights



Wattage

32W

Voltage Input

120V AC 50/60Hz

Efficacy

102-103 LPW


Dimming

0-10V Dimmable


Finish

Steel Base
Brushed-Nickel
White Powder Coated

Beam Angles



Color Temperatures



Features



Catalog No.	Fig.
LVE-24-MCT-BN	A.
LVE-36-MCT-BN	B.
LVE-48-MCT-BN	C.

Factory-Installed Options

Watts	277V Option	Description	Option Box	Description	Paint	Sensor	Description
ALL	OPT-277V	INTERNAL	OPT-VL-RS-BK	BOX	N/A	N/A	N/A

WESTGATE MFG
Order at:
TEL: 877.805.2252 FAX: 877.809.2252
ORDERS@WESTGATEMFG.COM