


LED system and workplace light



Product-Nr.	110994-12
EAN:	4260556623450
Model:	UNILED SL RGB-W
Order number:	110994-12
Model:	UNILED SL RGB-W
Type:	LED system and workplace light
Illuminant:	RGB SMD + SMD LED
Power consumption white:	~19 W
White lamp luminous flux:	2430 lm
Lamp luminous efficiency:	126 lm/W
Power consumption RED:	~18 W
Lamp luminous flux RED:	480 lm
Power consumption GREEN:	~5 W
Lamp luminous flux GREEN:	710 lm
Power consumption BLUE:	~18 W
Lamp luminous flux BLUE:	300 lm
Light distribution:	Direct
Light colour white:	5000K 3-step MacAdam
Colour rendering WHITE (Ra):	>80
Supply voltage:	24 V DC -10 % +7 % (RGB) – 24 V DC ±10 % (W)
Connection (connector):	M12 A-coded
Degree of protection:	IP50
Class of protection:	III
Glare control:	opal white
Beam angle (optics):	100°
Operating temperature:	-10 °C - +50 °C (14 °F - 122 °F)
Lamps lifetime:	> 100,000 h (L80/B10)
Housing material:	aluminium
Cover material:	plastics, soft
Height [B] x Width [C]:	35 mm x 85 mm (~1,38" x ~3,35")
Length [A]:	545 mm (~21,46")
Weight (net):	770 g (~27 oz)
Gross weight:	1320 g (~47 oz)
Risk group (DIN EN 62471):	Free group
Markings:	CE, UKCA, ETL Listed (5003529)
Mounting accessories:	Optional
Made in:	Germany
Feature:	RGB-W: Illumination and beacon in one light