



AUGUST 2023 PRODUCT LAUNCH

This product launch continues with a variety of new LEDVANCE branded LED Luminaires, Lamps and Ballasts to fit a wide assortment of applications. Find the full list below.

LUMINAIRES

VALUE CLASS DUAL SELECTABLE MINI WALL PACK 2A
VALUE CLASS DUAL SELECTABLE JELLY JAR 2A
VALUE CLASS WATTAGE SELECTABLE AREA LIGHT 5A
VALUE CLASS DUAL SELECTABLE WALL PACK 8A
VALUE CLASS CCT SELECTABLE LINEAR SLOT
PERFORMANCE CLASS FLAME RESISTANT SELECTABLE SLIM MICRODISK
PERFORMANCE CLASS SLIM CCT SELECTABLE MICRODISK
LEDVANCE LINK SENSOR ADAPTOR AND SIGNAL BOOSTER

LAMPS

LEDlescent™ 360 SELECT™ T8 SIGNAGE LAMPS
--

BALLASTS

LEDVANCE T4 COMPACT FLUORESCENT PROGRAMMED RAPID START BALLAST
--

LEDVANCE NEW LUMINAIRES

LUMINAIRES

Click or scan
QR code for
more information



VALUE CLASS SELECTABLE MINI WALL PACK 2A

- The LEDVANCE Value Class Mini Wall Pack 2A is available in 120-347V, as well as selectable wattage (10/20/30W) and selectable color temperature (3000K/4000K/5000K)
- It's available in bronze, black, and white
- These “all in one” luminaires come standard with a photocell for additional energy savings



VALUE CLASS DUAL SELECTABLE JELLY JAR 2A

- The LEDVANCE Value Class Jelly Jar 2A is both wattage (10W/20W) and color selectable (3000K/4000K/5000K)
- NEW Flex Mount, which allows for wall, ceiling, and pendant mount all in one fixture
- With its rugged glass lens and cage, it can be used in most extreme environments. Also, the 120-347 voltage allows for many more applications due to its range



VALUE CLASS WATTAGE SELECTABLE AREA LIGHT 5A

- The Value Class Wattage Selectable Area Flood 5A combines affordability with contractor friendly installation
- With types III, IV, and V distributions and great thermal performance, the Area Lights come with an universal mounting bracket for multiple installation options
- It also allows for field installable screw-in sensors that require no wiring. An easy and economical solution for outdoor applications!



VALUE CLASS DUAL SELECTABLE WALL PACK 8A

- Redefining the standard of an economical wall pack, the Value Class Dual Selectable Wall Pack 8A family combines dual selectability, high quality and affordability
- With an integrated photocell and a slim design that still matches the footprint of traditional wall packs, they help reduce energy consumption, and save on freight and storage costs.



VALUE CLASS CCT SELECTABLE LINEAR SLOT

LINE EXTENSION - WALL MOUNTED, BLACK FINISH, ACCESSORIES

- This product was initially presented last November. There have been numerous updates to the product family worth discussing.
- The product will now be offered with a black finish. We have also moved to stock the wall mount versions meaning they are no longer MTO.
- Multiple accessory updates have also been executed including the decision to bring in the L/X/and T connectors to allow for the connecting of multiples linear segments.



BLAZE GUARD™ FLAME RESISTANT SELECTABLE SLIM MICRODISK

LINE EXTENSION - 120-277V

- This product was last presented in May's product launch and has an update.
- The product was initially offered in 120V only, it is now also going to be offered in 120-277V on an MTO basis.
- This is a continual effort to show that we will consider and support existing product families while leveraging our MTO capabilities.



LEDVANCE NEW LUMINAIRES, LAMPS, AND BALLASTS

LUMINAIRES

Click or scan
QR code for
more information




PERFORMANCE CLASS SLIM CCT SELECTABLE MICRODISK LINE EXTENSION - 120-277V

- This product was last presented in May's product launch and has an update.
- The product was initially offered in 120V only, it is now also going to be offered in 120-277V on an MTO basis.
- This is a continual effort to show that we will consider and support existing product families while leveraging our MTO capabilities.

LEDVANCE LINK™ ADAPTOR AND SIGNAL BOOSTER

- The product team is happy to provide the continued support of the LEDVANCE LINK products, first showcased last year at Light Fair 2022
- The most important addition is the sensor adaptor, a product that allows many existing HIDr and Industrial LUM families to be LINK enabled



LAMPS

LEDlescent™ 360 SELECT™ T8 SIGNAGE LAMPS

- These LEDlescent 360 SELECT T8 Ballast-Free, Direct wire lamps are designed to replace traditional high output T8 and T12 signage lamps by bypassing the existing ballast
- They are color selectable to allow for application flexibility on site to display the sign material content in the most appropriate correlated color temperature
- 360 SELECT lamps are available in lengths ranging from 18" to 10'



BALLASTS

LEDVANCE T4 COMPACT FLUORESCENT PROGRAMMED RAPID START BALLAST

- LEDVANCE is proud to carry it's own line of electronic ballasts which now welcomes the Dual Entry CFL ballast which operates DULUX D/E and T/E lamps
- This ballast model has color coded connectors located on the side and bottom for mounting flexibility
- Visit our Ballast compatibility list for more details on potential TLED pairing.





LEDVANCE

[LEDVANCEUS.COM](https://www.ledvanceus.com)

LEDVANCE LLC
181 Ballardvale Street, Suite 203
Wilmington, MA 01887 USA
Phone 1-800-LIGHTBULB (1-800-544-4828)
www.ledvanceUS.com



SCAN TO FOLLOW US
ON SOCIAL MEDIA

LEDVANCE is a registered trademark. All other trademarks are those of their respective owners. Specifications subject to change without notice.

© 2023 LEDVANCE LLC