




Schaefer® WM24D-SS Adjustable Wall Fan Mount—Stainless Steel, 16" Depth, Up to 24" Fan Diameter



- HEAVY-DUTY—stainless steel construction
- LEGENDARY—for use with Schaefer® fans up to 24" in diameter and weighing up to 75 pounds
- BEST-IN-CLASS—convenient fan mounting
- 2-year limited warranty

Product Description

The Schaefer® WM24D-SS Adjustable Wall Fan Mount—Steel, 16" Depth, Up to 24" Fan Diameter provides you with convenient fan wall mounting for fans up to 24 inches in diameter and weighing up to 75 pounds. The heavy-duty stainless steel construction works to keep your fan secure. Includes a 2-year limited warranty.



Key Specs

Model Number	WM24D-SS	Max Fan Diameter (inches):	24
Able to Ship Small Parcel:	Yes	Max Fan Weight (pounds):	75
Brand:	Schaefer	Mounting Surface:	Wall or Column
Warranty	2-year limited	Product Color:	Metallic
Country of Origin:	China	Product Dimensions (D x H) inches:	16 x 13
Description:	Adjustable Wall Mount for up to 24" Fans	Shipping Dimensions (L x W x H) inches:	21 x 4 x 3
Hardware Included:	No	Product Weight (pounds):	5
Material:	Stainless Steel		