

PRODUCT DATASHEET

DOOR KIT LINK 2x2 UNV

RETROFIT DOOR KIT LINK™ | Door Kit luminaire featuring built-in LEDVANCE LINK bluetooth low energy mesh connectivity



Areas of application

- Offices
- Retail
- Hallways
- Multipurpose Rooms
- Hospitality

Product features

- Selectable CCT: 3000/3500/4000/5000K
- Bluetooth® Low Energy Mesh and a range of up to 100 ft between luminaires
- Easy to deploy - install, commission, and control
- Convenient control via LINK™ app or wireless wall/controller
- Optional LINK PIR sensor enables field-installable occupancy & daylight control
- DLC listing maximizes rebate opportunities
- Up to 125 LPW
- Optional emergency battery backup versions
- CRI > 80
- Wirelessly sync luminaires and set group/individual scenes using the LINK app

TECHNICAL DATA

Additional product data

Ordering Abbreviation	RDORKIT7A/S030UNVD8SC8/22/BLE
Abbrev. With Packaging Info.	RDORKIT7AS030UNVD8SC822BLE 2/CS 2/SKU
NAED	62572
Family Brand Name	ValueLED
General Description	2x2 Retrofit Door Kit, Selectable wattage, 15, 20, 25, 30W, 120-277V, CCT Selectable, 3000, 3500, 4000, 5000K, Bluetooth enabled, motion sensors sold separately
Warranty	5 years

Electrical data

Nominal Wattage	15.00/20.00/25.00/30.00 W
Nominal voltage	120.00...277.00 V
Power factor	≥0.90
Total Harmonic Distortion	< 20 %

Photometrical data

Lumens	1905/2540/3200/3810 lm
Efficacy	125 lm/W
Color Temperature/CCT	3000/3500/4000/5000 K
Color Rendering Index (CRI)	> 80
Luminaire Type	Retrofit

Dimensions & Weight

Length	23.82 in
Width	23.86 in
Height	3.09 in
Product weight	8.66 lb

Materials & Colors

Luminaire Finish	White
Housing color	White
Housing	Steel
Mercury content	0.0 mg

Application & Mounting

Ambient temperature range	-20...+50 °C
Maximum Operating Temperature	122 °F
Minimum Operating Temperature	-4 °F

Dimming	Yes
Type of Dimming	0-10V
Mounting	Recessed
Indoor/Outdoor	Indoor
Replaceable light source	No

Lifespan

Average Rated Life (hr)	125000
-------------------------	--------

Logistical data

Case Qty	2
Case Length (in)	26.614
Case Width (in)	25.158
Case Depth (in)	5.354
Case Cube (ft)	2.075
Case Weight (lbs)	19.484
Pallet Qty	32

Certificates & Standards

Certification Listing	RoHS / FCC / cULus
Replaceable light source (EPREL)	Not replaceable

Optional accessories

Product image	Product name	UPC
	AREA DUSK-TO-DAWN 55W 120-277V D 3CCT T5 GR P	OS61751

EQUIPMENT / ACCESSORIES

- Mounting brackets

Safety advice

- Retrofit luminaire is designed to be installed in existing troffers

DOWNLOAD DATA

Spec Sheets and Product Documents		Document name
	Installation Guide	RETROFIT DOOR KIT 7A
	Installation Guide	INSTALLATION GUIDE LEDVANCE LINK LOW-VOLTAGE PLUG&PLAY ECOSENSOR

Spec Sheets and Product Documents		Document name
	Product Family Spec Sheet	BLUETOOTH MESH ENABLED CONNECTED RETROFIT DOOR KIT LEDLUM165

Photometric and lighting design files		Document name
	IES file (IES)	VOLUME DOORKIT 7A IES

DISCLAIMER

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.