



1' x 4', 2' x 2' & 2' x 4' Backlit Panels


Applications:

- ----
- ----
- ----

Product Information:

- Flicker-free integrated driver, 0-10V dimmable
- Backlit design provides diffuse, shadowless light
- No UV, no RF, non-yellowing PMMA lens
- Powder-coated white frame






1'x4'

23.75"


47.6"



2'x2'

23.75"

23.75"



2'x4'

23.75"

47.6"



3"



Selectable Wattage



Selectable CCT



Knockouts



End Knockout




Aluminum Trim



Mounting Clips

- 40 Watt
- 6550 Lumens
- Dimmable
- Integrated LED
- IP20 Rated
- 120-277V

RETAIL READY STAND OUT PACKAGING



Packaging subject to size change based on product size



1" X 4" BACKLIT PANEL

NW-BL-1X4-20.30.40W-3CT

LUMENS	20W- 2,600 30W- 3,900 40W- 5,200
WATTAGE	20W/30/40W
VOLTAGE	120/277V
TRIM	WH- White
COLOR TEMP	35/40/50K
BEAM ANGLE	120°
LIFE HOURS	50,000
CRI	80
DIMMABLE	0-10V Commercial Dimmer

2" X 2" BACKLIT PANEL

NW-BL-2X2-20.30.40W-3CT

LUMENS	20W- 2,600 30W- 3,900 40W- 5,200
WATTAGE	20W/30/40W
VOLTAGE	120/277V
TRIM	WH- White
COLOR TEMP	35/40/50K
BEAM ANGLE	120°
LIFE HOURS	50,000
CRI	80
DIMMABLE	0-10V Commercial Dimmer

2" X 4" BACKLIT PANEL

NW-BL-2X4-30.40.50W-3CT

LUMENS	35W- 3,900 40W- 5,200 50W- 6,500
WATTAGE	30W/40/50W
VOLTAGE	120/277V
TRIM	WH- White
COLOR TEMP	35/40/50K
BEAM ANGLE	120°
LIFE HOURS	50,000
CRI	80
DIMMABLE	0-10V Commercial Dimmer