

ASSEMBLY AND INSTALLATION INSTRUCTIONS

C0360 / C0361

WARNING: TO AVOID RISK OF ELECTRICAL SHOCK, BE SURE TO SHUT OFF POWER BEFORE INSTALLING OR SERVICING THIS FIXTURE.

NOTE: 1. Before installing, consult local electrical codes for wiring and grounding requirements.
2. Read and save these instructions.

Hardware Package (included):



Mounting Screw (A)



Wire Connector (B)

Installation Steps

Turn off the power at fuse or circuit box

1. Attach the two mounting screws (A) to the holes on outlet box, thread them in part way: 2 to 3 turns only.
2. Connect the black wire to black (power) wire, white wire to white (neutral) wire and fixture ground wire to house ground wire with supplied wire connectors (B). Tuck all wires into outlet box.
3. Attach the fixture to the outlet box by inserting two mounting screws (A) head into the keyholes, then rotate the fixture until it is locked in place, finally secure the mounting screws (A) tightly with screwdriver (not included).
4. Roll up and tilt the shade into the fixture, and then release it until it is laid in fixture side to side.

Turn on the power at fuse or circuit box





Fig.1



Remote Control

Install two 1.5 volt batteries (type AAA, not included) into the remote control.

Remote control functions:

1. "ON" Button:
Press this button to turn the light on.
2. "OFF" Button:
Press this button to turn the light off.
3. Bright+ Button: Adjust from low brightness to high brightness.
Dim- Button: Adjust from high brightness to low brightness.
Warm Button: Adjust from high color temperature (Daylight) to low color temperature (Warm White).
Cool Button: Adjust from low color temperature (Warm White) to high color temperature (Daylight).
4. "CCT" Color Temperature Button:
Press this button to change the color temperature of the light. There are 5 selectable colors at 2700K, 3000K, 3500K, 4000K, 5000K.
5. "Night Light" Button:
Press this button to put the light into a low brightness.
6. "Timer" Button:
Press the timer button, the light will turn off in one hour. If you want to cancel the timer function, press the OFF button.

7. "RGB" Button:

Press this button to change to a single solid RGB color. There are a total 7 colors to choose from.



8. "RGB IC" Button:

Press this button to change RGB party mode, there are a total 6 RGB party modes to choose from.

Note: This remote control has a memory setting function. If the wall switch is used to turn off the light for more than 10 seconds, it will remember the state before the power was turned off.

If the light fixture cannot be controlled by the remote, please turn off the power first and then turn it on. Next, press and hold the middle button (a) on the remote for 5 seconds to pair. Flashing indicates successful pairing.

The following parts are available for reorder if damaged or missing.



A: 2"
B: 16-1/2"

5 Year Limited Warranty

Vaxcel warrants all of our products against defects in workmanship and finishes for one year following the date of shipment.

In addition:

- Any product with an integrated motion sensor or dusk-to-dawn photocell is supported by a 5-year warranty for the functionality of the product.
- Any product with integrated LED modules is covered by a 5-year warranty on the LED functionality.

Exclusions: This warranty does not include the failure of products from extreme acts of nature; environmental conditions not suited for the products intended use; operation in temperatures outside of the range specified in the instruction manual; usage with improper power supply, power surges or dips. For coastal locations, some corrosion is considered normal for the environment.

Vaxcel reserves the right to repair, replace or issue a credit for any properly installed product, provided it is returned per RMA instruction. This warranty is limited to the cost of the product only and does not extend to transportation, installation or replacement costs.

How can warranty service be obtained?

info@vaxcel.com
1-800-482-9235