

210.00 mm

145.00 mm


TO CLEAN FAN BLADE OR GRILL:

WARNING:

Unplug from electrical supply source before cleaning.

1. Clean the blade by using a soft, damp cloth then wipe with dry cloth. Please be caution around the motor housing area.
2. Do not allow the motor or other electrical components to be exposed to water.
Reassemble after cleaning by reversing above procedure.
3. Do not bend the blades.
4. Put several drops of sewing machine oil into the oil ways on the front and rear shells at regular intervals, (Recommendation, every 3 months with 24 hour use or every 6 month with regular use)

**(12"18"/20") HIGH VELOCITY
FLOOR FAN
OPERATION INSTRUCTIONS**



145.00 mm

210.00 mm

READ AND FOLLOW ALL INSTRUCTIONS BEFORE OPERATION FAN

CAUTION:

Read and follow all instructions before operating fan. Do not use fan if any part is damaged or missing.

WARNING:

1. To reduce the risk of fire or electric shock, do not use this fan with any solid state speed control device.
2. This appliance has a ground plug which is intended to fit in an outlet only one way. If this does not fit outlet, contact a qualified electrician. Do not attempt to by-pass this procedure.
3. This product is used for indoor.
4. Unplug from electrical supply source before cleaning.
5. If the power cord is damaged, contact your local service centre or a qualified electrician to install an appropriate replacement cord to prevent any injury or damage.
6. This appliance is not intended for use by persons (including children) with reduced physical, sensory or mental capabilities, or lack of experience and knowledge, unless they have been given supervision or instruction concerning use of the appliance by a person responsible for their safety.
7. Children should be supervised to ensure that they do not play with the appliance.

RULES FOR SAFE OPERATION:

1. Never insert fingers, pencils, or any other object through the guard when fan is running.
2. Disconnect the fan when moving from one location to another.
3. Disconnect the fan when removing grilles for cleaning.
4. Be sure fan is on a stable surface when operating to avoid overturning.
5. DO NOT use fan in window. Rain may create electrical hazard.
6. The fan is for commercial use only.
7. Do not leave the fan running unattended.

USER SERVICING INSTRUCTIONS

1. Grasp plug and remove from the receptacle or other outlet device. Do not unplug by pulling on cord
2. Risk of fire. Do not replace attachment plug. Discard product if the attachment plug is damaged.

TO ADJUST AIRFLOW UPWARD OR DOWNWARD:

Tilt head of fan to desired angle.

Loosen the POSITION KNOB. Tilt motor to the desired angle then firmly tighten the position knob.

OPERATING INSTRUCTIONS:

SPEED CONTROL:

Select air speed by setting switch at the back of the fan Low, Medium and High speed for desired air movement.

It is normal for the motor to feel warm to the touch after continuous operation. This fan features a thermostat that will automatically shut off if it overheats for any reason. If it happens, unplug the fan from the outlet immediately.

FAN CRADLE ASSEMBLY:

Simple assembly is required to use this fan.

1. Align Cradle Base with support brackets attached to fan body sides. Note: you may need to flex the parts to make them align properly.
2. Insert support bracket into opening of cradle base. Press spring loaded button down to allow it to insert into cradle base, see Fig.1.
3. Press support bracket into cradle base until spring button protrudes out open hole in cradle base, see Fig.2.
4. Repeat above process for opposite side of fan.

Fig.1




Fig.2

