




## Schaefer® WM24D-B Adjustable Wall Fan Mount—Steel, 16" Depth, Up to 24" Fan Diameter



- HEAVY-DUTY—steel construction
- LEGENDARY—for use with Schaefer® fans up to 24" in diameter and weighing up to 75 pounds
- BEST-IN-CLASS—convenient fan mounting
- 2-year limited warranty

### Product Description

The Schaefer® WM24D-B Adjustable Wall Fan Mount—Steel, 16" Depth, Up to 24" Fan Diameter provides you with convenient fan wall mounting for fans up 24 inches in diameter and weighing up to 75 pounds. The heavy-duty steel construction works to keep your fan secure. Includes a 2-year limited warranty.



## Key Specs

---

|                            |                                          |                                         |                |
|----------------------------|------------------------------------------|-----------------------------------------|----------------|
| Model Number               | WM24D-B                                  | Max Fan Diameter (inches):              | 24             |
| Able to Ship Small Parcel: | Yes                                      | Max Fan Weight (pounds):                | 75             |
| Brand:                     | Schaefer                                 | Mounting Surface:                       | Wall or Column |
| Warranty                   | 2-year limited                           | Product Color:                          | Black          |
| Country of Origin:         | China                                    | Product Dimensions (D x H) inches:      | 16 x 13        |
| Description:               | Adjustable Wall Mount for up to 24" Fans | Shipping Dimensions (L x W x H) inches: | 21 x 4 x 3     |
| Hardware Included:         | No                                       | Product Weight (pounds):                | 5              |
| Material:                  | Steel                                    |                                         |                |