

TOP FEATURES

5^{YR}
WARRANTY

3 CCT
30K
40K
50K

40 W
POWER

4000
LUMENS

DIMMABLE
0-10V

DAMP
RATED

HIGH
BRIGHTNESS

110°
BEAM
ANGLE

120-277
VOLT

1"
THIN

DIE-CAST
ALUMINUM

EDGE LIT
LED
TECH

50K
HOURS

CERTIFICATIONS



SPECIFICATIONS

2 X 2 FOOT LED

40W | SURFACE MOUNT | EDGE LIT

NW-SM-2X2-40W-3CT-UV

Effortless Installation - High quality internal driver, lightweight led flat panel light can be quickly & easily installed as a surface mount, flush mount and suspended mount without a mounting kit. The distinct hook design makes installation easy and secures when attaching to suspended

TECHNICAL SPECS



VOLTAGE	AC 120-277V
WATTAGE	40W
POWER FACTOR	>0.9
LUMENS	4000
CRI	80
EQUIVALENCY	N/A
DIMMABLE	0-10 VOLT
BEAM ANGLE	110°
EFFICACY (LM/W)	100
COLOR TEMPERATURE	3CCT COLOR FIELD SELECTABLE 3000K 4000K 5000K
OPERATING TEMPERATURE	-15~40°C
IP RATING	N/A
MOISTURE RATING	DAMP LOCATION

LIFETIME PERFORMANCE

WARRANTY	5 YEAR WARRANTY
LIFETIME HOURS	50,000 HOURS

CONSTRUCTION




HOUSING MATERIAL	ALUMINUM
TRIM MATERIAL	DIE-CAST ALUMINUM
PRODUCT WEIGHT	7.8 LB. / 3.5 KGS
PRODUCT DIMENSIONS	23.85 IN. X 23.85 IN. X 1.06 IN.
LENS DIAMETER	21.54 IN X 21.54 X 0.04 IN
LENS MATERIAL	PS



TECHNICAL

2X2 FOOT LED | 40W | SURFACE MOUNT | EDGE LIT

NW-SM-2X2-40W-3CT-UV




LUMINOUS INTENSITY DISTRIBUTION DIAGRAM

4000 LUMENS

IN STORE DISPLAY



MULTI-PACK BOX



PALLET