

YSR8CFX10CLTCKITC

Attributes	Values
Application	Wire Reducing Splice
AWG Size	750 kcmil - 500 kcmil
Barrel Style	Skived
Barrel Type	Standard
Coating	Tin-Plated
Collection Name	HYREDUCER
Color Code	Red
Cond. Material	Copper
CSA Approved	No
cUL Approved	No
cULus Approved	No
Die Index	49;
ETL Approved	No
Height (in)	0.21
Length (in)	1.41
Length L2 (in)	0.57
Material	Copper
Plated	Yes
Plating Type	Tin - Electro Plated
Power Cond. AWG Size	8 - 10 AWG
Strip Length (in)	0.57
Temperature Rating	194 Deg C
Voltage	35 kV
Width (in)	0.27