





Schaefer® Twister™ TW24B 24" Oscillating Circulation Fan - Black



- Schaefer oscillation technology
- 2-speed high efficiency motor with 10 foot cord
- OSHA compliant guards, available in black or white
- 90 degrees of total oscillation
- 45 degrees of fan head adjustability up or down
- Low noise levels, quieter than conversational voice
- Fixed or portable mounting capabilities
- Two year warranty
- Assembled in the USA

Product Description

Geared for performance, Twister's oscillating motor utilizes highest quality metal gear design for unparalleled strength, greater load capacity and higher accuracy. Whether aimed at a workstation using a standard wall mount or down an aisle or assembly line using a pedestal, Twister provides the versatility and performance needed to improve worker productivity and safety.



Key Specs

Model Number	TW24B
Brand	Schaefer® Twister™
Warranty	2-year limited warranty
Net Weight (lb.)	34
Air Flow (CFM)	5400/4900
Motor Size (HP)	1/4

Fan Diameter (in.)	24
Variable Speed	2
Volts	115
Amps	3
Tested	BL

Schaefer® and Twister™ are trademarks of Pinnacle Climate Technologies, Inc.