

PRODUCT DATASHEET

ARCHITECTURAL LINEAR VALUE 8 ft WH

Direct Light Ceiling/Suspended/Recessed

ARCHITECTURAL LINEAR VALUE | Architectural Linear with selectable CCT

Areas of application

- Offices
- Lobbies
- Waiting rooms
- Hospitality
- Retail



Product features

- Selectable CCT: 3000/4000/5000K
- Direct or Direct/Indirect
- Accessories available for suspended, surface or recessed mounting are available
- Linkable
- Sleek and modern design
- Two different finishes
- CRI > 80

TECHNICAL DATA

Additional product data

Ordering Abbreviation	LNSLOT1A68UNHD8SC196CWH
Abbrev. With Packaging Info.	LNSLOT1A68UNHD8SC196CWH 2/CS 1/SKU
SKU UPC	0046135624568
NAED	62456
General Description	Linear Slot 1A, 4', 120-347V, 68W, CCT selectable 3000, 3500, 4000K, 0- 10V dimming, ceiling mount
Warranty	5 years

Electrical data

Nominal Wattage	68.00 W
Nominal voltage	120.00...347.00 V
Power factor	≥0.90
Total Harmonic Distortion	< 20 %

Photometrical data

Lumens	6800 lm
Efficacy	100 lm/W
Color Temperature/CCT	3000/3500/4000 K
Color Rendering Index (CRI)	> 80
Luminaire Type	Linear luminaires

Dimensions & Weight

Length	97.64 in
Width	8.86 in
Height	5.71 in
Product weight	11.02 lb

Materials & Colors

Luminaire Finish	White
Housing color	White
Housing	Aluminum
Mercury content	0.0 mg

Application & Mounting

Ambient temperature range	-20...+40 °C
Maximum Operating Temperature	104 °F
Minimum Operating Temperature	-4 °F
Dimming	Yes

Type of Dimming	0-10V
Mounting	Surface
Indoor/Outdoor	Indoor
Replaceable light source	No
Primary Lamp Type	SMD

Lifespan

Average Rated Life (hr)	50000
-------------------------	-------

Logistical data

SKU Qty	1
Case Qty	2
Case Length (in)	97.638
Case Width (in)	8.858
Case Depth (in)	5.709
Case Cube (ft)	2.857
Case Weight (lbs)	25.331
SKU UPC	0046135624568
Pallet Qty	56

Certificates & Standards

Certification Listing	RoHS / FCC
Replaceable light source (EPREL)	Not replaceable

EQUIPMENT / ACCESSORIES

- Suspended Mount Kit - available with all SKUs aside wall mount version
- Wall Mount Kit - available for all wall mounting version only

Safety advice

- Connect up to 700W

DOWNLOAD DATA

Spec Sheets and Product Documents		Document name
	Installation Guide	Value Class Linear Slot Installation Guide
	Installation Guide	VALUE CLASS Linear Slot
	Installation Guide	Value Class Linear Slot
	Product Family Spec Sheet	LEDLUM154 CCT SELECTABLE LINEAR SLOT

Photometric and lighting design files		Document name
	IES file (IES)	Value Class CCT Selectable Linear Slot IES FILES

DISCLAIMER

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.