


|           |       |       |
|-----------|-------|-------|
| JOB NAME: | DATE: | TYPE: |
| COMMENTS: |       |       |



| LIGHT INFORMATION  |                | DIMENSIONS & WEIGHT  |                | PRODUCT FINISH                                                                        |
|--------------------|----------------|----------------------|----------------|---------------------------------------------------------------------------------------|
| Light Type         | Integrated LED | Height (In)          | 12             | Matte Black                                                                           |
| CRI                | 90             | Min Height (In)      | 33.75          | SHADE FINISH                                                                          |
| Delivered Lumens   | 4882           | Max Height (In)      | 193.75         | Organic Mixed Glass                                                                   |
| Color Temperature  | 3000K          | Diameter (In)        | 39             | ADDITIONAL INFORMATION                                                                |
| LED Lifespan (L70) | 50000          | Weight (Lbs)         | 109.89         | Power Wire Length (In) 180                                                            |
| Number of Lights   | 33             | INSTALLATION         |                | Replaceable LED Yes                                                                   |
| Light Direction    | Ambient        | Mounting Type        | J-Box          | CERTIFICATIONS & COMPLIANCE                                                           |
| Dimming Method     | Triac/Elv      | Rating               | Dry            |  |
| Current Type       | DC             | Hanging Support Type | Aircraft Cable |                                                                                       |
| Input Voltage      | 120            |                      |                |                                                                                       |
| Total Wattage      | 80.85          |                      |                |                                                                                       |