



LED system light and workplace lighting



Product-Nr.	110914-23
EAN:	4260556623405
Model:	UNILED SL DC
Order number:	110914-23
Model:	UNILED SL DC
Type:	LED system light and workplace lighting
Illuminant:	SMD LED
Power consumption:	~48 W
Lamp luminous flux:	7596 lm
Lamp luminous efficiency:	~155 lm/W
Light distribution:	Direct
Light colour:	5700K 3-step MacAdam
Colour rendering (Ra):	>85
Supply voltage:	24V DC $\pm$ 10%
Connection (connector):	M12 A-coded
Degree of protection:	IP50
Class of protection:	III
Glare control:	Microprisms
Beam angle (optics):	100°
Operating temperature:	-10 °C - +60 °C (14 °F - 140 °F)
Lamps lifetime:	> 100,000 h (L80/B10)
Housing material:	aluminium
Cover material:	micro prisms cover
Height [B] x Width [C]:	35 mm x 85 mm (~1,38" x ~3,35")
Length [A]:	1045 mm (~41,14")
Weight (net):	1720 g (~61 oz)
Gross weight:	2370 g (~84 oz)
Risk group (DIN EN 62471):	Free group
Markings:	CE, UKCA, ETL Listed (5003529)
Dimmable:	Optional via accessories
Mounting accessories:	Optional
Made in:	Germany
Feature:	high light diffusion