




Electrolux

Vega Series | Single-Zone Ductless Mini Split



Everything you need from a smart mini split.
Certified, connected, and built to last.

The Vega Series delivers the Electrolux mini split experience where it matters most — reliable heating and cooling, full smart connectivity, and AHRI-certified performance, at a price point that opens the door to more homes and more installations. WiFi, Alexa, and Google Assistant are standard across all four models. R32 refrigerant across the range. A complete, capable unit — no compromises on what your customers use every day.



WHISPER-QUIET IN THE ROOMS THAT MATTER

The Vega 9K and 12K run as quietly as 27 dB(A) — below the threshold of a whisper. Bedrooms, home offices, nurseries. Comfort that's felt without being heard, from a unit that runs all day without intruding.



UP TO 20.5 SEER2 — EFFICIENT BY DESIGN

DC inverter compressor across all four models adjusts output continuously to match demand — drawing only the power needed, not a fixed wattage. Eco mode and Auto mode extend efficiency further in daily use.



WIFI, ALEXA & GOOGLE — FULLY SMART, OUT OF THE BOX

Full app control via the Electrolux app with native Alexa and Google Assistant support. On-device 24-hour timer works without WiFi. Filter alerts and self-diagnosis built in. No extra accessories required.



SHIPS READY. QUICK-RELEASE INDOOR UNIT.

The indoor unit releases without tools for fast filter access and coil cleaning. Top-access washable dust filter. Chassis heater, auto-restart, and fire-rated electrical box protect the system long-term. 3-year warranty across the range.

	9,000 BTU	12,000 BTU	18,000 BTU	24,000 BTU
Model	SAC09SNV19-1	SAC12SNV19-1	SAC18SHV19-1	SAC24SHV19-1
Wifi	Yes	Yes	Yes	Yes
Room Coverage	Up to 450 sq ft	Up to 750 sq ft	Up to 1,000 sq ft	Up to 1,250 sq ft
Cooling Capacity	9,000 BTU	12,000 BTU	18,000 BTU	24,000 BTU
Heating Capacity	10,000 BTU	12,300 BTU	18,700 BTU	24,000 BTU
SEER2 / EER2 / HSPF	20.5 / 10.9 / 8.5	19 / 11 / 8.5	19 / 10.5 / 8	19 / 10.5 / 8.5
Voltage	115V	115V	208/230V	208/230V
Min. Noise (Indoor)	27 dB(A)	27 dB(A)	35 dB(A)	39 dB(A)
Certifications	AHRI	AHRI	AHRI	AHRI
Warranty	3-yr compressor / 1-yr parts	3-yr compressor / 1-yr parts	3-yr compressor / 1-yr parts	3-yr compressor / 1-yr parts



All specifications AHRI-certified. R32 refrigerant across all models (lower GWP than R410A). Full spec sheet available on request.

WHAT'S INCLUDED

- Pre-charged line set (no refrigerant tank required on-site)
- Wall mounting bracket + outdoor pad
- Washable dust filter
- Full-function backlit remote with 24-hour timer
- All installation hardware included

Professional installation recommended for full warranty coverage.
Supports standard line set cover kits for a clean finished look.

READY TO STOCK
THE VEGA SERIES?

[distributor contact email]

[distributor contact phone]

For better living.