

14AWG

GCP SERIES



INSTANT AC POWER ACCESS. INTEGRATED AC PORT EXTENSION CABLES.

15A

PEAK PERFORMANCE

Rated at 15-amps with heavy-duty 14 AWG copper wiring to maximum power flow and full-sized AC port prongs for maximum conductivity.

EASY INSTALL

LOW-PROFILE.

A low-profile flanged AC power inlet provides endless possibilities for engine block heaters, battery chargers, and outdoor outlets.

125V


AC PORT PLUG.

A 125-volt power inlet socket with an integrated 16-inch outdoor extension cord for a car, boat, marine, truck, trailer, pickup, RV, industrial and electrical applications.

NOCO

30339 Diamond Parkway, #102
Glenwillow, OH 44139 | USA
1.800.456.6626

no.co



PLUG AND PLAY.
ENDLESS POSSIBILITIES.

Easily install a pass-through power outlet anywhere. Perfect for powering AC applications, like engine block heaters and battery chargers, on boats, trucks, trailers, RVs, and more.



WATER PROOF.
PRESSURE FIT CAP.

Includes a snap-fit cap for a watertight seal.




SELF-TAPPING.
NO PRE-DRILLING.

Drill through fiberglass, wood, plastic, and metal.

EASY INSTALL.
NO HARDWIRING NEEDED.

Connect the GCP port with four easy steps.



	GCP1	GCP1E	GCP1EX	GCP2				
CORD LENGTH:	16 inches (40.6 cm)	6 feet (1828 mm)	12 feet (3657 mm)	18 inches (45.7 cm)				
AC INPUT:	Single AC Type B	Single AC Type B	Single AC Type B	Single AC Type B				
AC OUTPUT:	Single AC Type B	Single AC Type B	Single AC Type B	Dual AC Type B				
NET WEIGHT:	0.47 lbs (0.21 kg)	0.91 lbs (0.41 kg)	1.49 lbs (0.67 kg)	0.71 lbs (0.32 kg)				
WHATS IN THE BOX:	• GCP1 AC Port Plug With 16-inch Extension Cord • Pressure-fit Cap • (3) Self-tapping Screws	• GCP1E AC Port Plug With 6-foot Extension Cord • Pressure-fit Cap • (3) Self-tapping Screws	• GCP1EX AC Port Plug With 12-foot Extension Cord • Pressure-fit Cap • (3) Self-tapping Screws	• GCP2 AC Port Plug With Dual 18-inch Extension Cord • Pressure-fit Cap • (3) Self-tapping Screws				
VOLUMETRICS:	Retail Packaging: Dimensions: 5.2" x 2.6" x 5.3" Weight: 0.60 lbs UPC: 0-46221-12050-9 Inner Carton: Dimensions: 5.5" x 2.9" x 5.5" Weight: 0.71 lbs	Master Carton: Dimensions: 15.8" x 11.7" x 12.2" Weight: 14.9 lbs Quantity: 20 UCC: 10046221120506 Units Per Pallet: 900 Units	Retail Packaging: Dimensions: 5.2" x 3.4" x 5.3" Weight: 1.06 lbs UPC: 0-46221-19015-1 Inner Carton: Dimensions: 5.5" x 3.7" x 5.5" Weight: 1.1 lbs	Master Carton: Dimensions: 11.3" x 10" x 13.1" Weight: 25.2 lbs Quantity: 20 UCC: 10046221190158 Units Per Pallet: 800 Units	Retail Packaging: Dimensions: 5.2" x 3.4" x 5.3" Weight: 1.68 lbs UPC: 0-46221-19016-8 Inner Carton: Dimensions: 5.5" x 3.7" x 5.5" Weight: 1.7 lbs	Master Carton: Dimensions: 19.8" x 11.7" x 12.2" Weight: 36.7 lbs Quantity: 20 UCC: 10046221190165 Units Per Pallet: 800 Units	Retail Packaging: Dimensions: 5.2" x 2.6" x 5.3" Weight: 0.6 lbs UPC: 0-46221-19017-5 Inner Carton: Dimensions: 5.5" x 2.9" x 5.5" Weight: 0.71 lbs	Master Carton: Dimensions: 15.8" x 11.7" x 12.2" Weight: 20 lbs Quantity: 20 UCC: 10046221190172 Units Per Pallet: 900 Units

NOCO

30339 Diamond Parkway, #102
Glenwillow, OH 44139 | USA
1.800.456.6626

no.co