

GRIPPS®

ANSI/ISEA
121-2023
COMPLIANT

H02108 UNIVERSAL LEATHER BELT

The GRIPPS® Universal Leather Belt is a premium, genuine-leather work belt delivering long-wear comfort with rugged durability.


Crafted from robust, high-grade cow leather, it offers an ideal balance of strength, comfort, and professional finish for workers at heights. With its universal fit system, it accommodates waist sizes from 28 to 55 inches, allowing users to customise belt length for a precise fit.

Independently certified to ANSI/ISEA 121-2023, this belt delivers proven reliability for dropped-object prevention. Pair with GRIPPS® holsters and tethers to safely manage tools up to 2.5 kg/5.5 lb and tether lengths up to 1.5 m / 59 in.



2.5 KG **5.5** LB

MAX LOAD




ENGINEERED FOR DROP PREVENTION

gripps.com

KEY FEATURES

Universal Fit System

Accommodates waist sizes from 28 to 55 inches, enabling easy customisation for a secure, comfortable fit.



100% Genuine Leather

Built from high-grade cow leather for superior longevity, abrasion resistance, and consistent performance.



Durable Hardware

Heavy-duty components are designed to resist stretching and deformation under load.




Work-at-Height Ready

Optimised to integrate with GRIPPS holsters, pouches, and tool tethers for a streamlined setup.




HOW TO USE

1




Put the belt on to determine fit. After using a 2.5 mm hex key, remove the grub screws from the belt tip and detach the tip.

2



Mark the cut point, keeping at least 5 inches (about 5 holes) of extra length for flexibility in sizing. *If using with the GRIPPS universal back support, first set the back support to the desired length and wear it with the belt attached before cutting. Ensure the belt tip holes align with the belt holes. Cut the leather at the marked point.

3



Reinstall the belt tip and secure it with the grub screws.

SPECIFICATIONS

SKU	MAX LOAD	MAX TETHER LENGTH	WAIST SIZE RANGE
H02108	2.5 kg 5.5 lb	150 cm 59 in	71 cm - 140 cm 28 in - 55 in

