



Schaefer® 30PFR-Y - 30" OSHA-Compliant Circulation Fan with Round Pedestal, Safety Yellow—9420 CFM, 1/2 HP, 115 Volt



- **HEAVY-DUTY**—great for any commercial, industrial, or agricultural facility
- **LEGENDARY**—greater air movement and superior cooling
- **BEST-IN-CLASS**—energy-efficient design for unrivaled cost savings
- Matched heavy-duty motor and blades
- 2-year limited warranty


Product Description

The Schaefer® 30PFR-Y 30" OSHA-Compliant Circulation Fan with Round Pedestal, Safety Yellow—9420 CFM, 1/2 HP, 115 Volt is the ideal cooling solution for any commercial, industrial, or agricultural facility. Engineered to produce greater air movement and superior cooling, it's the right choice no matter the application. The best-in-class energy-efficient design provides unrivaled cost savings, drawing as little as 2.8 amps. The matched heavy-duty motor and blades provide maximum velocity, and the specifically designed, powercoated safety yellow steel guards give this legendary fan its trusted durability, long life, and corrosion resistance. Plus, the included pedestal gives you maximum portability to place this fan wherever is most convenient. Includes a 2-year limited warranty.

**Thermally-Protected,
Maintenance-Free,
2-Speed Motor**

**Matched Heavy-Duty
Motor and Blades**

**Sturdy Pedestal for
Maximum Portability**



**Best-in-Class
Energy-Efficient
Design**

**Specifically Designed,
Powder-Coated Steel
Guards**

Features and Benefits

- Great for any commercial, industrial, or agricultural facility
- Engineered to produce greater air movement and superior cooling
- Best-in-class energy-efficient design for unrivaled cost savings
- Specifically designed, powder-coated steel guards for trusted durability and corrosion resistance
- Maximum velocity for up to 9420 CFM
- Matched heavy-duty motor and blades
- Thermally-protected, maintenance-free, 2-speed motor for long life
- Power cord included
- Sturdy, round pedestal included
- Variable speed control with two-speed pull chain
- Safety yellow guards and pedestal
- Assembled in the USA
- 2-year limited warranty

Key Specs

Model Number	30PFR-Y
Brand	Schaefer®
Warranty	2-year limited warranty
Net Weight (lb.)	81
Air Flow (CFM)	7000 / 9420
Motor Size (HP)	1/2
Fan Diameter (in.)	30

Variable Speed	Yes
Speed (RPM)	1075
Volts	115
Amps	2.8 / 5.2
Product Dimensions (L x W x H Inches)	33.5 x 33.5 x 13.5
Product Net Weight (lbs)	50
Guard Spacing (Inches)	1/2 OSHA

Schaefer is a registered trademark of Pinnacle Climate Technologies, Inc.

