



PIP® Kilimanjaro™

Type II Full Brim Safety Helmet with HDPE Shell,
4-Point Textile Suspension, Wheel Ratchet
Adjustment and 4-Point Chinstrap

- Lightweight HDPE shell made with UV stabilized High Density Polyethylene (HDPE) reduces worker fatigue
- EPS foam liner provides front, rear and lateral protection from impact and penetration
- 4-Point quick release suspension with strong textile straps and crown comfort pad provides a comfortable and secure fit
- Non-chaffing, replaceable foam sweatband for maximum sweat absorption
- SURE LOCK wheel adjustment system for one hand size adjustments
- Precise height adjustment settings to ensure proper depth

Technical Data

Color	Navy, Royal, White, Gray, Yellow, Red, Orange, Sky Blue, Hi-Vis Yellow, Dark Green, Black, Hi-Vis Orange, Pink
Sizes Available	OS
Packaging	Bagged Each
Packed	12/Case
Case Dimensions (in)	26.00 x 15.50 x 28.50
Case Weight (lbs)	15.98
Country of Origin	Canada
Shell Material	HDPE
Shell	Non-Vented
Brim Style	Full
Brim Length	Standard
Size Adjustment	Wheel Ratchet
Suspension	4 Point Nylon Webbing Cradle
Chin Strap	4-Point Polyester
Sweatband	Felt Lined Foam
Size Range	53cm-63cm
Certifications	ANSI/ISEA Z89.1, CSA Z94.1 Certified, TAA Compliant

Performance Data

ANSI Type	Type II
Electrical Class	Class E

Care Instructions

The unit may be cleaned with soap and warm water and dried with a soft cloth. The helmet should not be cleaned with chemical or abrasive cleaners. The helmet should be stored out of direct sunlight, away from chemicals and not exposed to extremes of temperature.

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
280-HP642R-CH-11	Black	OS	848309048077	10848309048074	20848309048071
280-HP642R-CH-04	Dark Green	OS	848309048114	10848309048111	20848309048118
280-HP642R-CH-09	Gray	OS	848309048794	10848309048791	20848309048798
280-HP642R-CH-31	Hi-Vis Orange	OS	848309048152	10848309048159	20848309048156
280-HP642R-CH-44	Hi-Vis Yellow	OS	848309048190	10848309048197	20848309048194
280-HP642R-CH-08	Navy	OS	848309048237	10848309048234	20848309048231
280-HP642R-CH-03	Orange	OS	848309048275	10848309048272	20848309048279
280-HP642R-CH-20	Pink	OS	198987043490	10198987043497	20198987043494
280-HP642R-CH-15	Red	OS	848309048312	10848309048319	20848309048316
280-HP642R-CH-17	Royal	OS	848309048718	10848309048715	20848309048712
280-HP642R-CH-07	Sky Blue	OS	848309048756	10848309048753	20848309048750
280-HP642R-CH-01	White	OS	616314958212	10616314958219	20616314958216
280-HP642R-CH-02	Yellow	OS	616314958250	10616314958257	20616314958254