

PRODUCT DATASHEET

WRAP HNG DUAL SELECTABLE 4FT S60W 3CCT 120-347V

WRAP HNG | Wrap luminaire with a wide body design and selectable CCT and wattage



Areas of application

- Offices
- Retail
- Closet storage spaces when installed per NEC 410.16 requirements
- Education
- Hallways
- Low Bay locations

Product features

- Selectable CCT: 3500/4000/5000K
- Wattage Selectable
- Advanced Quad-Pack LED optics for maximum edge-to-edge uniformity
- Factory installed polarized wiring system for end-to-end mounting
- Simple field installable PIR, Microwave, or LINK™ sensors
- Wide Body covers the footprint of the luminaire that was removed
- White powder coated metal body
- Includes V-hook mounting bracket
- Screw-In LINK™ compatible

TECHNICAL DATA

Additional product data

Ordering Abbreviation	WRAP/HNG/S060UNHD8SC7/48WH
Abbrev. With Packaging Info.	WRAPHNGS060UNHD8SC748WH 1/CS 1/SKU
NAED	64118
General Description	Wrap, Performance Class, selectable wattage, 120-347V, 80+CRI, Selectable CCT, 4ft, white
Warranty	5 years

Electrical data

Nominal Wattage	30.00/40.00/50.00/60.00 W
Nominal voltage	120.00...347.00 V
Power factor	≥ 0.90
Total Harmonic Distortion	< 20 %

Photometrical data

Lumens	4290/5680/7050/8400 lm
Efficacy	130 lm/W
Color Temperature/CCT	3500/4000/5000 K
Color Rendering Index (CRI)	80
Luminaire Type	Wrap

Dimensions & Weight

Length	47.99 in
Width	10.39 in
Height	2.76 in
Product weight	10.32 lb

Materials & Colors

Luminaire Finish	White
Housing color	White
Housing	Steel
Mercury content	0.0 mg

Application & Mounting

Ambient temperature range	-40...+50 °C
Maximum Operating Temperature	122 °F
Minimum Operating Temperature	-40 °F
Dimming	Yes
Type of Dimming	0-10V

Mounting	Suspended/Surface
Indoor/Outdoor	Indoor
Replaceable light source	No

Lifespan

Average Rated Life (hr)	125000
-------------------------	--------

Logistical data

Case Qty	1
Case Length (in)	50.079
Case Width (in)	11.969
Case Depth (in)	3.661
Case Cube (ft)	1.270
Case Weight (lbs)	11.984
Pallet Qty	39

Certificates & Standards

Certification Listing	RoHS / FCC / cULus
Replaceable light source (EPREL)	Not replaceable

Optional accessories

Product image	Product name	UPC
	CABLE MOUNT 10FT	OS63906
	ADAPTER PIN BRACKET L-SHAPE ADJUSTABLE	OS63909
	Standalone PIR Motion sensor 3.5mm Screw-in 19.7ft 12V	OS63908
	CHAIN MOUNT LNHIBA2A/CHAINM	OS60573
	Standalone Microwave Motion Sensor Behind the lens 19.7ft 12V	OS63907

Product image	Product name	UPC
	Standalone Commissioning Remote G2 VAPOR/WRAP/STRIP/PANEL	OS66592
	LINK WIRELESS CONTROLLER 5 KEY BATTERY BLE	OS62636
	LINK CONTROLLER 3.5mm AUX12V BLE	OS62630
	LINK SENSOR PIR 40FT 3.5mm BLE WH	OS62634

EQUIPMENT / ACCESSORIES

- V-hooks

Safety advice

- cULus listed to UL1598 and CSA C22.2 luminaire standards
- 2.5kV surge protection
- Indoor use

DOWNLOAD DATA

Spec Sheets and Product Documents		Document name
	Installation Guide	Wrap HNG Installations Instructions
	Product Family Spec Sheet	WRAP HNG DUAL SELECTABLE SPEC SHEET
Photometric and lighting design files		Document name
	IES file (IES)	HNG IES Files

DISCLAIMER

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.