




Surface Mount Installation (1)




1. Fix A1/A2/B1/B2 with snap-in plastic corners, making it a complete frame




2. Fix A1/A2 to ceiling with screws. Remove B1 and its two corner connectors.




3. Cut off the incoming power. Take off the driver box cover, and slide the panel partially into the mounting frame. Connect the L-shape conduit fitting to the incoming MC cable.



4. Remove the knockout on the driver box cover plate and attach the L-shape fitting to it. Connect the power line to the driver according to the wiring diagram with the provided hardware.



5. Fix the driver box cover plate back on the box and slide the panel into the frame seamlessly.



6. Put B1 onto the frame with its two corner connectors. Turn power back on. The installation is complete.

Panel Information		Surface Mount Information		Screw Information		
NAED CODE	Model	NAED CODE	Model	Screw Quantity	Screw Model	Screwdriver Model
62699	PANELF3BS045UNVD8SC724GWH	62065	SMKIT3A24WH	6	ST4*30	PH1
62698	PANELF3BS035UNVD8SC722GWH	62064	SMKIT3A22WH	4	ST4*30	PH1
65896	PANELF3BS035UNVD8SC714GWH	62066	SMKIT3A14WH	4	ST4*30	PH1
65897	PANELF3BS035UNVD8SC722GWH	62064	SMKIT3A22WH	4	ST4*30	PH1
65898	PANELF3BS045UNVD8SC724GWH	62065	SMKIT3A24WH	6	ST4*30	PH1
65899	PANELF3B018UNVD8SC714GWH	62066	SMKIT3A14WH	4	ST4*30	PH1
62701	PANELF3BS045UNVD8SC724GWH	62065	SMKIT3A24WH	6	ST4*30	PH1
62704	PANELF4BS036UNHD8SC722GWH	62064	SMKIT3A22WH	4	ST4*30	PH1
62700	PANELF3B018UNVD8SC714GWH	62066	SMKIT3A14WH	4	ST4*30	PH1
63744	PANELF3BS035UNVD8SC722GWH	62064	SMKIT3A22WH	4	ST4*30	PH1