

TOP FEATURES

5^{YR}
WARRANTY

3 CCT
30K
40K
50K

50 W
POWER

5000
LUMENS

DIMMABLE
0-10V

DAMP
RATED

HIGH
BRIGHTNESS

110°
BEAM
ANGLE

120-277
VOLT

1"
THIN

DIE-CAST
ALUMINUM

EDGE LIT
LED
TECH

50K
HOURS

CERTIFICATIONS



SPECIFICATIONS

2X4 FOOT LED

50W | WHITE | SURFACE MOUNT | EDGE LIT

NW-SM-2X4-50W-3CT-UV

Effortless Installation - High quality internal driver, lightweight led flat panel light can be quickly & easily installed as a surface mount, flush mount and suspended mount without a mounting kit. Distinct hook design makes installation easy and secures when attaching to suspended grid ceilings and troffer fixtures.

TECHNICAL SPECS


VOLTAGE	AC 120-277V
WATTAGE	50W
POWER FACTOR	>0.9
LUMENS	5000
CRI	80
EQUIVALENCY	N/A
DIMMABLE	0-10 VOLT
BEAM ANGLE	110°
EFFICACY (LM/W)	100
COLOR TEMPERATURE	3CCT COLOR FIELD SELECTABLE 3000K 4000K 5000K
OPERATING TEMPERATURE	-15~40°C
IP RATING	N/A
MOISTURE RATING	DAMP LOCATION

LIFETIME PERFORMANCE

WARRANTY	5 YEAR WARRANTY
LIFETIME HOURS	50,000 HOURS

CONSTRUCTION




HOUSING MATERIAL	ALUMINUM
TRIM MATERIAL	DIE-CAST ALUMINUM
PRODUCT WEIGHT	14.5 LB / 232 KG
PRODUCT DIMENSIONS	23.74 IN. X 47.76 IN. X 1.06 IN.
LENS DIAMETER	20.35 IN X 45.55 X 0.04 IN
LENS MATERIAL	PS



TECHNICAL

2X4 FOOT LED | 50W | WHITE | SURFACE MOUNT | EDGE LIT


NW-SM-2X4-50W-3CT-UV



IN STORE DISPLAY



MULTI-PACK BOX



PALLET