



GET THE RIGHT ANGLE

UFO HIGH BAY 3A


Choosing the right UFO High Bay for your application has become easier with the new Dual Selectable UFO High Bay 3A. This IP65 high bay is available in two wattage ranges: 100W, 120W, or 150W and 200W, 220W, or 240W. Both models also feature the selectability of 3500K, 4000K, or 5000K CCTs. For even greater installation flexibility, these fixtures feature optional field installable screw-in motion/daylight sensors and EMBB as well as a multiple refractor, reflector, and wire guard options. The UFO High Bay 3A is ideal for illuminating warehouses, gymnasiums, and other industrial applications.

VALUE CLASS



For more information, visit www.ledvanceUS.com/luminaires

LEDVANCE LLC
181 Ballardvale Street, Suite 203
Wilmington, MA 01887 USA
Phone 1-800-LIGHTBULB
(1-800-544-4828)



ORDERING GUIDE

UFOHIBA	3A	/ SXXX	UNV	D	8	SC7	/ XX
Product Name	Generation	Wattage	Voltage	Dimming	CRI	Color Temp	Color/Finish
UFOHIBA= LED UFO High Bay Luminaire	3A= Generation 3A	S150= 100, 120, or 150W S240= 200, 220, or 240W	UNV= 120-277V	D = 0-10V	8= >80	SC7= 3500, 4000, or 5000K	WH= White finish BL= Black finish

CONTRACTOR BENEFITS

- Dual wattage and CCT selectability means 9 lighting options from each SKU
- Field installable motion/daylight sensors and EMBB
- Multiple optical accessories available

PRODUCT FEATURES

- Lightweight fixture is designed for easy and safe installation
- Multiple mounting options for a variety of applications – pendant, hook, surface mount
- All fixtures ship with a pre-wired sensor base that is ready to accept an optional, field installable, screw-in motion/daylight sensor – sensor installs in seconds
- 90° polycarbonate front lens minimizes glare
- Variety of optics – polycarbonate refractor and aluminum reflector available
- IP65 rated aluminum body
- Up to 150 LPW
- 3500K, 4000K, or 5000K color temperature selectable
- CRI >80
- Offered in 100, 120, or 150 watts selectable and 200, 220, or 240 watts selectable
- Energy savings up to 78%



SCAN TO FOLLOW US
ON SOCIAL MEDIA

LEDVANCE is a registered trademark. All other trademarks are those of their respective owners. Specifications subject to change without notice.

Scan the QR tag to view
or download additional
product information

