

PRODUCT DATASHEET

TROFFER 5A 2x2 (20, 25 or 30W) 5000K

SYLVANIA Volumetric Troffer Lumen Selectable | Troffer with selectable wattage



Areas of application

- Offices
- Retail
- Hallways
- Multipurpose Rooms
- Hospitality

Product features

- Lumen selectability increases the versatility of this product
- All models are DLC Standard
- Ideal for retrofits, delivering major energy savings vs. traditional lighting
- Standard 0–10V driver enables added energy savings via dimming
- Up to 125 LPW
- 3500K, 4000K, or 5000K color temperature
- 0–10V Dimmable
- CRI > 80



TECHNICAL DATA

Additional product data

Ordering Abbreviation	VOLUME5AS030UNVD85022UWH
Abbrev. With Packaging Info.	VOLUME5AS030UNVD85022UWH 1/CS 1/SKU
NAED	61514
General Description	ValueLED Volumetric 5A, 20/25/30 Watts, 125 LPW, 120-277V, 0-10V Dimmable, 80+ CRI, 5000K, 2x2, For lay in grid ceilingsWhite
Warranty	5 years

Electrical data

Nominal Wattage	20.00/25.00/30.00 W
Nominal voltage	120.00...277.00 V
Power factor	≥0.90
Total Harmonic Distortion	< 20 %

Photometrical data

Lumens	2500/3125/3750 lm
Efficacy	125 lm/W
Color Temperature/CCT	5000 K
Color Rendering Index (CRI)	> 80
Luminaire Type	Troffer

Dimensions & Weight

Length	23.78 in
Width	23.78 in
Height	3.62 in
Product weight	7.72 lb

Materials & Colors

Luminaire Finish	White
Housing color	White
Housing	Steel
Mercury content	0.0 mg

Application & Mounting

Connectors	Plug, quick disconnect
Dimming	Yes

Type of Dimming	0-10V
Mounting	Recessed
Indoor/Outdoor	Indoor
Replaceable light source	No

Lifespan

Average Rated Life (hr)	50000
-------------------------	-------

Logistical data

Case Qty	1
Case Length (in)	25.433
Case Width (in)	24.685
Case Depth (in)	3.063
Case Cube (ft)	1.113
Case Weight (lbs)	10.396
Pallet Qty	30

Certificates & Standards

Certification Listing	RoHS / FCC / cULus
Replaceable light source (EPREL)	Not replaceable

EQUIPMENT / ACCESSORIES

– Optional flange kit

Safety advice

– Luminaire lays in standard 15/16" and 9/16" T-grid ceilings

DOWNLOAD DATA

Spec Sheets and Product Documents		Document name
	Installation Guide	SYLVANIA ValueLED Volumetric Troffer
	Product Family Spec Sheet	ValueLED Lumen Selectable Volumetric Troffer

DISCLAIMER

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.