



## Portable Air Conditioner-Pro

### Cooling / Heating

- Indoor / Outdoor -


Residential / Commercial

Equator 18,000Btu PRO PORTABLE AIR CONDITIONER Cool+Heat 1,000sf In-Outdoor 110V

| USES                                                                     |          |                 |
|--------------------------------------------------------------------------|----------|-----------------|
| Unit Location                                                            | Cooling  | Hot Air Exhaust |
| <b>Indoors</b><br>Eg: Stores, workshops, garages, warehouses             | Indoors  | Outdoors        |
| <b>Outdoors</b><br>(for closed spaces)<br>Eg: Tents, stables, log cabins | Indoors  | Outdoors        |
| <b>Outdoors</b><br>Eg: BBQ, picnics, weddings                            | Outdoors | Outdoors        |



#### Control Panel



#### KEY FEATURES

- Cooling / Heating
- Indoor / Outdoors
- Residential / Commercial
- Fully Portable
- Easy to Install

#### MODE

- Cool
- Heat
- Fan

#### FEATURES

- Handles
- Freestanding
- Auto Shut-off
- Washable Filters
- 1 - 24 Hours Timer
- Dual Supply Hoses
- Temperature Control
- Window Kit (included)
- Anti-Corrosion Coating
- 360 Rotating Air Hoses
- Heat Pump Technology
- Water Tank Full Warning
- LCD Display Control Panel
- Portable - Lockable Castors
- Removable Water Tank / Direct Drain

#### SPECIFICATIONS

|                                              |                         |
|----------------------------------------------|-------------------------|
| Model                                        | PAC 8000                |
| Color                                        | Yellow                  |
| Capacity (Cooling/Heating)                   | 18,000 Btu / 18,500 Btu |
| Air Volume / Cover Area                      | 800 m³/h / 1000 sq.ft.  |
| Electrical                                   | 110V / 60Hz             |
| Rated Current (Cooling/Heating)              | 15 A / 14.5 A           |
| Input Power (Cooling/Heating)                | 1700W / 1600W           |
| Noise Level                                  | 60-65 dB                |
| Indoor Temperature (Cooling/Heating)         | 50°F - 113°F            |
| Operating Outdoor Temperature                | 32°F - 131°F            |
| Outdoor Waterproof Rating                    | IP 24                   |
| Refrigerant                                  | R 32                    |
| Water Drainage (Water Tank / Drain Hose)     | 3 ft. Drain Hose        |
| Water Tank Capacity                          | 4 gal                   |
| Compressor Type                              | Rotary                  |
| Power Cord Length                            | 6 feet                  |
| Cooling Hose Diameter                        | 5 inches                |
| Weight (Net/Gross) lbs                       | 198 / 205               |
| Product Dimensions without Hose (HxWxD) inch | 43.1 x 17.3 x 24.4      |
| Package Dimensions (HxWxD) inch              | 52 x 18.9 x 31.9        |
| Type of Shipping                             | LTL                     |
| Certification                                | ETL                     |
| Warranty                                     | 1 Year Parts and Labor  |

Keywords: 18K BTU Industrial AC, Freestanding Industrial PAC, Industrial Portable Air Conditioner Spot Cooler, Indoor Outdoor Industrial AC, Movable / Portable Air Conditioner, Worksite Climate Control Unit, Mobile Spot Cooler, Commercial Store Cooler, Room Cooler, Cabin Cooler, Residential AC Mobile Spot, Residential Portable, Spot Air Conditioner with dual hoses.



**Equator Advanced Appliances** • 5006 Steffani Lane, Houston, Texas, 77041-7820, USA

Toll Free: 800-935-1955 • [www.EquatorAppliances.com](http://www.EquatorAppliances.com) • Email: [mail@equatorappliances.com](mailto:mail@equatorappliances.com)

Document#: WSSEQPAC800009062025