

PRODUCT DATASHEET

ARCHITECTURAL LINEAR VALUE 2 ft BL

Direct Light Ceiling/Suspended/Recessed

ARCHITECTURAL LINEAR VALUE | Architectural Linear with selectable CCT



Areas of application

- Offices
- Lobbies
- Waiting rooms
- Hospitality
- Retail

Product features

- Selectable CCT: 3000/4000/5000K
- Direct or Direct/Indirect
- Accessories available for suspended, surface or recessed mounting are available
- Linkable
- Sleek and modern design
- Two different finishes
- CRI > 80

TECHNICAL DATA

Additional product data

Ordering Abbreviation	LNSLOT1A18UNVD8SC124CBL
Abbrev. With Packaging Info.	LNSLOT1A18UNVD8SC124CBL 6/CS 1/SKU
SKU UPC	0046135637285
NAED	63728
General Description	18W 2ft linear slot 1A, 120-277V and 0-10V dimmable. CCT selectable, ceiling mount and black finish
Warranty	5 years

Electrical data

Nominal Wattage	18.00 W
Nominal voltage	120.00...277.00 V
Power factor	≥ 0.90
Total Harmonic Distortion	< 20 %

Photometrical data

Lumens	1800 lm
Efficacy	100 lm/W
Color Temperature/CCT	3000/3500/4000 K
Color Rendering Index (CRI)	> 80

Dimensions & Weight

Length	25.98 in
Width	12.2 in
Height	10.04 in
Product weight	2.98 lb

Materials & Colors

Luminaire Finish	Black
Housing color	Black
Housing	Aluminum
Mercury content	0.0 mg

Application & Mounting

Ambient temperature range	-20...40 °C
Maximum Operating Temperature	104 °F
Minimum Operating Temperature	-4 °F
Dimming	Yes
Type of Dimming	0-10V

Mounting	Surface
Indoor/Outdoor	Indoor
Replaceable light source	No

Lifespan

Average Rated Life (hr)	50000
-------------------------	-------

Logistical data

SKU Qty	1
Case Qty	6
Case Length (in)	25.984
Case Width (in)	12.205
Case Depth (in)	10.039
Case Cube (ft)	1.842
Case Weight (lbs)	23.845
SKU UPC	0046135637285
Pallet Qty	144

Certificates & Standards

Certification Listing	cETLus / FCC
Replaceable light source (EPREL)	Not replaceable

EQUIPMENT / ACCESSORIES

- Suspended Mount Kit - available with all SKUs aside wall mount version
- Wall Mount Kit - available for all wall mounting version only

Safety advice

- Connect up to 700W

DOWNLOAD DATA

Spec Sheets and Product Documents		Document name
	Installation Guide	VALUE CLASS Linear Slot
	Installation Guide	Value Class Linear Slot
	Installation Guide	Value Class Linear Slot Installation Guide
	Product Family Spec Sheet	LEDLUM154 CCT SELECTABLE LINEAR SLOT

Photometric and lighting design files		Document name
	IES file (IES)	18W 2ft linear slot 1A, 120-277V and 0-10V dimmable. CCT selectable
	IES file (IES)	Value Class CCT Selectable Linear Slot IES FILES

DISCLAIMER

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.