




OPERATING MANUAL

ELECTRIC BLOWER



NBT-EB-30A

SPECIFICATIONS

Rated Voltage	220-240V
Rated Frequency	50/60Hz
Rated Power	600W
No-load Speed	0-18000r/min
Wind Volume	2.5m ³ /min

MADE IN CHINA




Read through carefully and understand these instructions before use.


The unit is used for cleaning or coldshouldering machines and instruments of various industries.

HOW TO USE

When use for blowing with nozzle attached to outlet of wind by c.w.turn the nozzle.




When use for suction, with nozzie attached to suction port and dust bag attached to outlet of wind.



When dust bag is full, remove the bag and open outlet of bag then clean the dust to a dust bin.



Pressing the switch button, the unit is started. Loosing the switch button, the unit is stoped. When lock butto is pressed after unit is started, the unit can continually work and the unit can be stoped if press the switch button again.



MAINTENANCE

Before maintenance must disconnect the unit from power source.

Check the carbon brushes at regular intervals. It's must be replaced with new brushes when it's shorter than 6mm. Remove brush covers and brushes by screwdriver, then insert new brushes and turn brush covers to tighten.




FOR SAFE OPERATION

- When the unit is not to be used, place it in room. Never expose it to rain.
- As the unit is operated the operator must wear a providing cap, eyeglass and cover mouth.
- Before connecting the unit to a wall outlet, check that the marked voltage on name plate of the unit is same with local power source. If not, the unit may be damaged.
- Do not use the unit in the places where there is any inflammable liquid or gas.
- Do not suck up burned tobacco end and just cutted shred of metal.
- Do not direct the nozzle to nearby anybody.
- To prevent the fan is damaged due to increased speed of the motor, do not obstruct the suction port and outlet of wind.
- Do not pull on the power cord to disconnect the unit from the mains outlet or to move it.
- Keep the power cord away from high temperature substance, such as shred of metal and grease.

FEATURES

No operator fatigue from long use because it's small in size and light in weight. Powerful motor produces great wind pressure and volume to double work efficiency.

Double insulated for safety and convenience.



NO	Specification	Qty
1	608 bearing	2
2	roror	1
3	fan cover	1
4	screw ST4*30	4
5	fan	1
6	flat washer	1
7	nut M6	1
8	fan cover	1
9	filter net	1
10	screw ST4*16	12
11	rear cover	1
12	cord	1
13	sleeve	1
14	brush holder	2
15	carbon brush	2
16	B type screw ST3*8	2
17	housing	1
18	screw ST4*16	2
19	tension disc	1
20	switch	1
21	handle	1
22	Insert spring clasp	2
23	stator	1
24	screw ST4*40	2
25	seal ring	1
26	air pipe	1
27	sealing ring	1
28	dust bag	1
29		



Return receipt

WARRANTY CARD

DEALER'S NAME AND ADDRESS: _____

Please fill all the details and return the warranty registration card within 7 days from the date of purchase to the Dealer's address mentioned above. Unregistered warranty card is not applicable for any warranty service.

MODEL NO.: _____ SERIAL NO.: _____

NAME: _____ DATE OF PURCHASE: _____

ADDRESS: _____



Customer copy

WARRANTY CARD

MODEL NO.: _____ SERIAL NO.: _____

NAME: _____

ADDRESS: _____

DATE OF PURCHASE: _____

DEALER'S STAMP & SIGNATURE: _____

WARRANTY POLICY

CONGRATULATIONS for becoming a proud owner of NEWBEAT power tool(s). It is warranted to be free of defects from workmanship and materials for the period of SIX MONTHS from the date of original purchase.

This warranty covers the normal operation of the products and excludes damage caused by

- A) Accident, negligence, abuse and improper use.
- B) fire, flood and natural calamities;
- C) unauthorized repairs and alterations;
- D) wrong voltage/wild voltage fluctuation;
- E) entry into machine of water, slurry, dust, etc.;
- F) normal wear and tear;
- G) seal, carbon brush and other spare parts that easy to be worn and broken;
- H) rough transportation after sale.
- I) improper or lack of maintenance as indicated in the Operation Instructions;
- J) not using our company original spare parts & accessories as stipulated.

WARRANTY STRICTLY FOR ARMATURE AND FIELD COIL ONLY.

To ensure the effectiveness of this warranty, the following particulars must be entered on the Warranty Card on the date of purchase: Dealer's stamp, the date of purchase, the particular of buyer.

PLEASE KEEP THIS WARRANTY CARD SAFE WITH YOU. WARRANTY WILL NOT BE PROVIDED WITHOUT THIS WARRANTY CARD. This warranty is neither Assignable nor Transferable. Should any trouble develop during this six months period, return the COMPLETE tool, together with the warranty card and purchase bill of the related machine, to where it was bought for repair.

Note: The contents of this warranty card may be changed without prior notice and we reserves the authority for final interpretation.

NEWBEAT®

WARRANTY CARD



MADE IN CHINA



*Professional Series
For Industrial Use Only*