

# Norah

Pendant, 13", Matte Black, Smoked Glass

ITEM N°  
50788-026


EUROfase

JOB NAME:

DATE:

TYPE:

COMMENTS:



## LIGHT INFORMATION

|                    |                |
|--------------------|----------------|
| Light Type         | Integrated LED |
| CRI                | 90             |
| Delivered Lumens   | 227            |
| Color Temperature  | 3000K          |
| LED Lifespan (L70) | 50000          |
| Light Direction    | Ambient        |
| Dimming Method     | Triac/Elv      |
| Current Type       | DC             |
| Input Voltage      | 120            |
| Total Wattage      | 5              |

## DIMENSIONS & WEIGHT

|                 |        |
|-----------------|--------|
| Length (In)     | 9      |
| Width (In)      | 5.5    |
| Height (In)     | 13     |
| Min Height (In) | 24.25  |
| Max Height (In) | 158.25 |
| Weight (Lbs)    | 2.75   |

## INSTALLATION

|                      |                |
|----------------------|----------------|
| Mounting Type        | J-Box          |
| Rating               | Dry            |
| Hanging Support Type | Aircraft Cable |

## PRODUCT FINISH

Matte Black

## SHADE FINISH

Organic Smoked Glass

## ADDITIONAL INFORMATION

|                        |     |
|------------------------|-----|
| Power Wire Length (In) | 144 |
| Replaceable LED        | Yes |

## CERTIFICATIONS & COMPLIANCE

