


TW36B

TW36B

Features



Specifications

Air Velocity (@ 10')	1150
Blade Color	Metallic
Brand	Schaefer
Cfm (free Air)	12600
Cfm/watt (@0.10")	TBD
Drive	Direct
Phase	1
Speeds	2
Vfd Compatible	No
Cfm/watt (free Air)	24.2
Cord	Included - Wired
Diameter (inches)	36
Frequency (hz)	60
Guard Color	Black

Nameplate Amps	5.9
Number Of Wings	3
Cfm/watt (@0.05")	TBD
Power (hp)	1/2
Product Dimensions (L X W X H Inches)	TBD
Product Net Weight (lbs)	68
Performance Test #	699
Switch	On product
Voltage	115
Maximum Rpm	1075
Blade Material	Aluminum
Cfm (high)	12600
Cfm Calculation Standard	ANSI/AMCA Standard 230-99
Product Color	Black

Speed Control Compatible?	No
Able To Ship Small Parcel	No
Cfm (low)	10600
Cfm Range (free Air)	10001 - 15000
Cord Length (feet)	10
Fixed Or Portable	Fixed
Guard Material	Powder Coated Steel
Mount Type Recommended	TBD
Oscillating	Yes
Sound Level (dda @ 10')	76
Country Of Origin	US
Guard Spacing (inches)	1/2 OSHA