

# MaxLite® Double Tube Shop Light



## General Safety Information

### WARNING: RISK OF ELECTRICAL SHOCK

- House electrical current can cause painful shock or serious injury unless handled properly. For your safety, always remember to:
  - Turn off the power at the fuse or circuit breaker box before you install the shop light.
- This shop light is designed for use in a circuit protected by a fuse or circuit breaker. This shop light is intended to be installed directly beneath a ceiling-mounted receptacle and any excess cord should be kept out of the workspace. It is also designed to be installed in accordance with local electrical codes. If you are unsure about your wiring, consult a qualified electrician or local electrical inspector, and consult your electrical code.
- Account for small parts and destroy packing material, as these may be hazardous to children.



*Pictures are for illustration purposes only.  
Your model may vary.*

### WARNING: RISK OF INJURY

- Do not open shop light. No serviceable parts inside.

### WARNING: RISK OF FIRE

- Most dwellings built before 1985 have a supply wire rated 60°C. Do not overload the circuit and wiring.

Consult a qualified electrician.

- This device complies with part 15 of the FCC Rules. Operation is subject to the following 2 conditions:

(1) This device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation. Note: This equipment has been tested and found to comply with the limits for a Class B digital device, pursuant to part 15 of the FCC Rules. These limits are designed to provide reasonable protection against harmful interference in a residential installation. This equipment generates, uses and can radiate radio frequency energy and, if not installed and used in accordance with the instructions, may cause harmful interference to radio communications. However, there is no guarantee that interference will not occur in a particular installation. If this equipment does cause harmful interference to radio or television reception, which can be determined by turning the equipment off and on, the user is encouraged to try to correct the interference by one or more of the following measures: Reorient or relocate the receiving antenna. Increase the separation between the equipment and receiver. Connect the equipment into an outlet on a circuit different from that to which the receiver is connected. Consult the dealer or an experienced radio/TV technician for help.


- Not for use with dimmers.
- This portable luminaire has a polarized plug (one blade is wider than the other) as a feature to reduce the risk of electric shock. This plug will fit in a polarized outlet only one way. If the plug does not fit fully in the outlet, reverse the plug. If it still does not fit, contact a qualified electrician. Never use with an extension cord unless plug can be fully inserted. Do not alter the plug.

## MODEL

SL3 Series

### INCLUDED IN BOX

- A: 1 – Fixture Assembly
- B: 4 – “S” Hooks
- C: 2 – Chains
- D: 2 – Screw Eye Hooks
- E: 6 – Wall Anchors
- F: 1 – Cable Ties
- G: 4 – #8 Screws



# MaxLite® Double Tube Shop Light

## Installation Instructions

For installation of SL3 Series Double Tube Shoplight; Estimated Assembly Time: 10 Minutes; Rated: 120V 60Hz 43W 0.5A

### HANGING INSTALLATION

**Disconnect the power by turning off the circuit breaker or by removing the appropriate fuse at the fuse box. Turning the power off using the light switch is not sufficient to prevent electrical shock.**

1. Install "J" hooks into ceiling (see warning below). (The plastic wall anchors (E) are recommended to be used if mounting onto plaster board). See Figure 1.

**WARNING:** "J" Hooks are for mounting onto wood ceiling or a plaster board surface (Recommend minimum 3/8" thick). Install each "J" hook (D) or other mounting/hook option exactly 46.2 inches apart. Check to make sure the hold is secure and appropriate for the weight of the shop light. Never hang on the shop light or hang any object from the shop light.

**WARNING:** DO NOT INSTALL on radiant-heating ceilings.

**WARNING:** These hooks are to engage the hanging chain only and not the electric cord.

2. Slide the "S" hook (B) through the opening at the top of the workshop lamp assembly (A) channel and the end of the chain (C), and press the two ends of the hook tightly with pliers. See Figure 2.
3. Attach the chain (C) to the "J" hook (D) or other hook type that fits your ceiling. After the store lights are hung, check whether they are securely installed. See Figure 3.
4. Plug the power cord into an outlet rated 120V/60Hz. (The cable ties (F) can be used to secure excess cord to the hanging chain.)




Figure 1.




Figure 2.




Figure 3.

### OPTIONAL FLUSH MOUNT INSTALLATION

1. Install 4 screws (G) on the mounting face with length spacing of 46.5" and width spacing of 3.23". Leave approximately 0.12" between the surface and screw. (Recommend to use screws with wall anchors (E) if mounting onto plaster board). See Figure 4.

2. Align shop light to the screws and slide to one side to secure it in place. The shop light should be firmly fixed against the screws. If not firmly fixed, remove the shop light and tighten the screws to a smaller gap distance to the surface. See Figure 5.

3. Plug the power cord into an outlet rated 120V/60Hz.




Figure 4.




Figure 5.


### LINKING MULTIPLE SHOPLIGHTS

#### IMPORTANT WARNING:

1. Insert the lamp plug of the required link into the socket of the previous lamp.

**WARNING:** The maximum number of connected lamps is 4.

**WARNING:** Do not link other electrical appliances.



# MaxLite® Double Tube Shop Light



## Standard Product Warranty

### TERMS & CONDITIONS

#### Introduction

This product warranty (the "Warranty") covers each of MaxLite's LED lighting fixtures, lamps, and controls (the "Product(s)") that are purchased while the Warranty is in effect, for a specified period of time (the "Warranty Period") from the earlier of the actual installation date or 90 days after the original date of purchase from a MaxLite authorized distributor/dealer. For each Product, the Warranty Period can be found in the most current versions of the MaxLite Standard Product Warranty Coverage document ("SPWC") and applicable MaxLite Product Data Sheet ("PDS").

#### Warranty Coverage

If a Product fails to operate during the Warranty Period as a result of defects in materials or workmanship, MaxLite will, at its option, repair it, replace it with the same Product (or, if the same Product is not reasonably available, with a product that is comparable in MaxLite's view) at no charge, or will issue a refund. MaxLite reserves the right to utilize new, reconditioned, refurbished, repaired, or remanufactured products or parts in the warranty replacement process.

#### General Terms and Conditions of the Warranty

1. The Warranty is effective for purchases of Products on and after July 22, 2019. MaxLite reserves the right to modify the Warranty from time to time; any such modifications shall be effective for all purchases made on and after the effective date of such modification.
2. The Warranty is applicable only to Products originally purchased from an authorized MaxLite distributor/dealer and is otherwise void.
3. Except for Products that qualify for a labor allowance per the SPWC, MaxLite is not responsible for any of the labor costs or other expenses associated with Product removal or installation.
4. The Warranty is void if the Product is operated outside its normal operating conditions per the applicable PDS, has been installed for an application for which it is not rated, or has been subject to accident, neglect, abuse, misuse, or Acts of God, and shall only be effective if the Product has been used, installed, and maintained in accordance with MaxLite's written instructions.
5. The Warranty shall not apply to any Product which is used, installed, operated, or maintained in violation of any applicable standard, code, or instructions for use, including without limitation, those contained in the Standards for Safety of Underwriters Laboratory, Inc (UL); the National Electric Code (NEC); Standards for the American National Standards Institute (ANSI); or, in Canada, the Canadian Standards Association (CSA).
6. The Warranty does not cover any 3rd party devices or products used in conjunction with the Product unless they are purchased from or provided by MaxLite to be used specifically with the Product.
7. Repaired and/or replacement products are warranted by MaxLite for the remainder of the failed Product's original Warranty Period.
8. The Warranty shall not apply to Products, parts, advice, assistance, or service which a) MaxLite furnishes as a courtesy or for no fee, and/or b) that are purchased and/or used outside of the United States or Canada.
9. In the event that LEDs fail to operate, such shall constitute a Product defect under the Warranty only if at least 15% of the LEDs per product have stopped illuminating.
10. The Warranty does not cover any cosmetic Product defects, including without limitation, damage to the painted Product finish or other finish or coating. Nor does the Warranty cover any lumen drop-off or CCT (color temperature) variations experienced by a Product.
11. Only an Officer of MaxLite, or a designee appointed in writing by an Officer of MaxLite is authorized to change, modify or extend the terms of this Warranty.
12. The Warranty and all matters connected with the performance thereof shall be construed, interpreted, applied and governed in all respects by the laws of the State of New Jersey in the United States of America. Any action, suit or proceeding arising out of or relating to this Limited Warranty and/or to the purchase of Products covered by this Limited Warranty, shall be venued exclusively in the State or Federal courts located within the State of New Jersey (U.S.A.).
13. To make a claim under the Warranty, customer must notify MaxLite (or MaxLite's designee) in writing, during the Warranty Period, of the Product failure. All claims must be initiated using the warranty claim process found on MaxLite's website.
14. Before providing Warranty coverage, MaxLite or its designee(s): (i) may require that you provide evidence of the purchase and/or installation date (e.g. a copy of original receipt/invoice, customer order number, etc.); and (ii) shall have the right but not the obligation to inspect the relevant project job site.
15. Warranty coverage is only available if the original purchaser is not in default or arrears on any portion of its payment obligations to MaxLite for the defective Product.

#### LIMITATION OF LIABILITY

THIS WARRANTY IS EXCLUSIVE, AND IS THE SOLE REMEDY FOR ANY AND ALL CLAIMS, WHETHER IN CONTRACT, IN TORT OR OTHERWISE ARISING FROM THE FAILURE OF PRODUCT AND IS IN LIEU OF ALL OTHER WARRANTIES, EXPRESS OR IMPLIED, INCLUDING ALL WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE, WHICH WARRANTIES ARE HEREBY EXPRESSLY DISCLAIMED TO THE EXTENT PERMITTED BY LAW AND, IN ANY EVENT, SHALL BE LIMITED TO THE WARRANTY PERIOD SPECIFIED ABOVE. THE LIABILITY OF MAXLITE SHALL BE LIMITED TO THE TERMS OF THE EXPRESS WARRANTY SET FORTH HEREIN. IN NO EVENT WILL MAXLITE BE LIABLE FOR ANY SPECIAL, INCIDENTAL OR CONSEQUENTIAL DAMAGES INCLUDING, WITHOUT LIMITATION, DAMAGES RESULTING FROM LOSS OF USE, PROFITS, BUSINESS OR GOODWILL, LABOR COSTS, REMOVAL OR INSTALLATION COSTS, WHETHER OR NOT MAXLITE HAS BEEN ADVISED OF THE POSSIBILITY THEREOF. UNDER NO CIRCUMSTANCES SHALL MAXLITE'S ENTIRE LIABILITY FOR A DEFECTIVE PRODUCT EXCEED THE PURCHASE PRICE OF THAT PRODUCT (EXCLUDING LABOR WARRANTY COVERAGE WHERE SPECIFICALLY OFFERED BY MAXLITE). WARRANTY SERVICES PROVIDED UNDER THESE TERMS AND CONDITIONS DO NOT ENSURE THE UNINTERRUPTED OPERATION OF PRODUCTS; MAXLITE SHALL NOT BE LIABLE FOR DAMAGES CAUSED BY ANY DELAYS INVOLVING WARRANTY SERVICE.

This Warranty gives you specific legal rights and you may also have other rights that may vary from state to state. Because some states or jurisdictions do not allow the exclusion or limitation of liability for consequential or incidental damages, such limitation may not apply to you.