




SUMNER*
A Southwire Company

PRODUCT CATALOG



SUMNER.COM

*Trademark of Sumner Manufacturing Co., LLC. Registered in the U.S.

OUR STORY

Sumner*, a Southwire Company, is a recognized leading manufacturer of material lifts, jack stands, welding tools, material carts and other tools and equipment for the construction market. We are a key supplier to the welding and mechanical contracting industries and have a market presence in more than 50 countries around the world. We maintain manufacturing and sales operations in Texas, Canada, China, the United Kingdom and the Netherlands.

Founded in 1965, our operations began to meet the need for good welding tools and lifting equipment to make pipe installations easier and safe. Early success in the business led the way for us to continually meet the needs of a wide variety of contractors, and we continue to provide a range of equipment options that promote safety and efficiency on the jobsite.

SUMNER* MANUFACTURING

At Sumner* Manufacturing, our welding customers are very important to us. One of our primary goals as a manufacturer is to provide our customers with high quality, competitively priced tools. Welders are not only our customers, we learn from welders in the field what products are needed to make their jobs easier. These ideas help us to design and build new and better products. In essence, our customers are part of our Research & Development department, and without their input, we would be unable to continually offer great new products.

Another important part of our philosophy at Sumner* is our commitment to safety. All Sumner* employees are dedicated to the safety of the individuals who use our products. We understand that price is always a concern to our users, but we will never sacrifice quality or safety just to save costs. We know the demands expected of all Sumner* products, and each is built for years of use. It could be said that Sumner* tools are built the way the welder would make them. As a result, our tools are not only considered the best in the market, but also the most reliable to get the job done efficiently and safely.

TABLE OF CONTENTS

WELDING

Center Punches	5
Clamps	6
ULTRA™ Clamp.....	6
ULTRA™ Qwik Clamp.....	6
ULTRA™ Fit.....	7
ULTRA™ Qwik Fit.....	7
Clamp Champ.....	8
DX Clamp	9
Internal Fit-Up	9
Pins	10
Flange Spreader.....	11
Adjust-A-Fit™	12
Expansion Plugs	13
Purges	14
Weld Gas Analyzer	14
Purge Star*	14
Purge Buddy.....	15
Ring Purge.....	16
Welding Gage.....	17
Rotary Ground Clamp.....	17
Fit Kits™	18
Squares	19
Levels	22
Welder's Stool	23

JACKS

Heavy Duty Jacks	25
Pro Jack*	26
Fold-A-Jack*	27
FAT Jack™	28
Hi Boy™	29
FAB SAF™	30
Adjust-A-Roll™	31
Mini-Roll.....	32
Pro Roll™	33
Big V™	34
MAX JAX*	35

MAX JAX* 2.....	36
Beam JAX™	37
Reel Mac™	38
Hold Down Devices	39
Hold-E*	39

CARTS & STORAGE

Cricket™	44
Grasshopper™	45
Handi-Bench	46
Pipe Mac™	47
Hanger Mac™	48
Bundle Mac™	49
Mac Rack™	49
Mac Rack II™	49
Cylinder Carts	50

LIFTS

EL-405 Stacker	55
Roust-A-Bout™	56
FAB-MATE™	57
Short Stack™	57
Series 1900	58
Series 2000	59
Series 2100	60
Series 2200	61
Series 2300	62
Series 2400	63
Series 2500	64
Series 2600	65
Eventer™	66

GANTRIES

GH3/4T	71
GH2T	72
GH5T	73

CORDS

Royal® Outdoor Extension Cords.....	75
-------------------------------------	----

MATERIAL HANDLING

Pallet Jacks	77
6 Pac Mac™	78
10 Pac Mac™	78
Caddy Mac™	79
Spool Mac™	79
Stor Mac™	80
Tainer Mac™	81
Weldbox™	82
Storage Cabinets.....	83
Piano Box	84
Field Office.....	85
Compact Chest	86

HOISTS

Lever Hoists.....	88
Premium Lever Hoists.....	89
Premium Lever Hoists w/ Overload Protection.....	90
Chain Block Hoists.....	91
Premium Chain Block Hoists	92
Premium Chain Block Hoists w/ Overload Protection.....	94

WELDING

Universal Center Punch
Clamps

ULTRA™ Clamp

ULTRA™ Qwik Clamp

ULTRA™ Fit

ULTRA™ Qwik Fit

Clamp Champ

DX Clamp

Internal Fit-Up Clamp

Pins

Flange Spreader

Adjust-A-Fit™

Adjust-A-Flange™

Plugs

Purges

Expansion Plugs

Weld Gas Analyzer

Purge Star*

Purge Buddy

Ring Purge

Welding Gage

Rotary Ground Clamp

Fit Kits™

Squares

Magnetic Fixtures

Levels

Welder's Stool



UNIVERSAL CENTER PUNCH



The Sumner* Center punches have magnetic arms that attach to the steel surface to assure accurate location when using the punches spring-loaded striking hammer.

SPECIAL FEATURES:

- Available with fixed or adjustable magnet arms to accommodate steel pipe or tanks
- Push-button spring-loaded striking hammer
- Removable digital leveling gauge with magnetic base
- Alignment marks for centering
- Digital gauge can be used as angle finder

SPECIFICATIONS

ITEM #	DESCRIPTION	MODEL #	UPC	MINIMUM PIPE CAPACITY	MAXIMUM PIPE CAPACITY
784590	Universal Center Punch with Inclinometer	UCPUNCH	661165845907	4"	UNLIMITED
784590	Universal Center Punch with Inclinometer	UCPUNCH	661165845907	4"	8"
OPTIONAL ACCESSORY					
779546	Inclinometer Digital Angle Finder	CPINCLINE	661165795462		

ULTRA™ CLAMP



The Sumner* ULTRA™ Clamp is a fast, accurate fit-up tool for pipe to pipe, pipe to fitting and other fit-up needs.

SPECIAL FEATURES:

- Accurate fit-up of 1" through 12" pipe
- Rugged frame, built for jobsite use
- Stainless steel alignment screws
- Operating handle repositions for close work
- Fine adjustment screws for quick fit-up
- Lightweight for overhead work
- Available in three sizes



SPECIFICATIONS

ITEM #	DESCRIPTION	MODEL #	UPC	MINIMUM PIPE CAPACITY	MAXIMUM PIPE CAPACITY
781130	ULTRA™ Clamp for 1-2.5" Pipe	UC1-2.5	661165811308	1"	2.5"
781150	ULTRA™ Clamp for 2-6" Pipe	UC2-6	661165811506	2"	6"
781170	ULTRA™ Clamp for 5-12" Pipe	UC5-12	661165811704	5"	12"

ULTRA™ QWIK CLAMP



The Sumner* ULTRA™ Qwik Clamp is a fast, accurate fit-up tool for pipe to pipe, pipe to fitting and other fit-up needs with a quick button release.

SPECIAL FEATURES:

- Push button design allows for rapid action setting and fine tune thread adjustment
- Accurate fit-up of 1" through 12" pipe
- Rugged frame, built for jobsite use
- Stainless steel alignment screws
- Operating handle repositions for close work
- Fine adjustment screws for quick fit-up
- Lightweight for overhead work
- Available in three sizes



SPECIFICATIONS

ITEM #	DESCRIPTION	MODEL #	UPC	MINIMUM PIPE CAPACITY	MAXIMUM PIPE CAPACITY
781510	ULTRA™ Qwik Clamp for 1-2.5" Pipe	UQC1-2.5	661165815108	1"	2.5"
781520	ULTRA™ Qwik Clamp for 2-6" Pipe	UQC2-6	661165815207	2"	6"
781530	ULTRA™ Qwik Clamp for 5-12" Pipe	UQC5-12	661165815306	5"	12"

ULTRA™ FIT



The Sumner* ULTRA™ Fit is a fast, accurate fit-up tool for pipe to pipe, pipe to fitting and other fit-up needs.

SPECIAL FEATURES:

- Accurate fit-up of 1" through 12" pipe
- Rugged frame, built for jobsite use
- Stainless steel alignment screws
- Operating handle repositions for close work
- Fine adjustment screws for quick fit-up
- Lightweight for overhead work
- Available in three sizes



SPECIFICATIONS

ITEM #	DESCRIPTION	MODEL #	UPC	MINIMUM PIPE CAPACITY	MAXIMUM PIPE CAPACITY
781265	ULTRA™ Fit for 1-2.5" Pipe	UF1-2.5	661165812657	1"	2.5"
781275	ULTRA™ Fit for 2-6" Pipe	UF2-6	661165812756	2"	6"
781285	ULTRA™ Fit for 5-12" Pipe	UF5-12	661165812855	5"	12"

ULTRA™ QWIK FIT



The Sumner* ULTRA™ Qwik Fit is a fast, accurate fit-up tool for pipe to pipe, pipe to fitting and other fit-up needs with a quick button release.

SPECIAL FEATURES:

- Push button design allows for rapid action setting and fine tune thread adjustment
- Accurate fit-up of 1" through 12" pipe
- Rugged frame, built for jobsite use
- Stainless steel contacts & alignment screws
- Operating handle repositions for close work
- Fine adjustment screws for quick fit-up
- Lightweight for overhead work
- Available in three sizes



SPECIFICATIONS

ITEM #	DESCRIPTION	MODEL #	UPC	MINIMUM PIPE CAPACITY	MAXIMUM PIPE CAPACITY
781540	ULTRA™ Qwik Fit for 1-2.5" Pipe	UQF1-2.5	661165815405	1"	2.5"
781550	ULTRA™ Qwik Fit for 2-6" Pipe	UQF2-6	661165815504	2"	6"
781560	ULTRA™ Qwik Fit for 5-12" Pipe	UQF5-12	661165815603	5"	12"

CLAMP CHAMP™



The Sumner® Clamp Champ™ is an advanced solution for today's problem fit ups! The Clamp Champ™ is built for the welder who takes pride in doing his job right the first time. Constructed from years of trouble free job site use, the versatile Clamp Champ™ makes pipe fit-up simple and accurate – without the need of a helper. The Clamp Champ™ is similar to a pipe vise with fast, easy set up and solid chain engagement.

SPECIAL FEATURES:

- Easy grip knurled adjustment knob works with gloved hands for precision alignment
- Leveling and supporting device quickly and accurately sets gap
- Drop forged handle and wing nuts designed for rough field use and easy adjustment with gloved hands
- Fast action chain lock system for fast set-up
- Flared jack bars are easy to add or remove to accommodate a wide range of pipe diameters
- Jack bar screws allows welder to square and space the fit-up easily

SPECIFICATIONS

ITEM #	DESCRIPTION	MODEL #	UPC	MINIMUM PIPE CAPACITY	MAXIMUM PIPE CAPACITY
781000	Clamp Champ™ Standard Kit for 1"-10" Pipe	CCKIT1-10	661165810004	1"	10"
780999	Clamp Champ™ Stainless Steel Kit for 1"-10" Pipe	CCKITSS1-10	661165809992	1"	10"
780998	Clamp Champ™ Standard Kit for 1"-16" Pipe	CCKIT1-16	661165809985	1"	16"
780997	Clamp Champ™ Stainless Steel Kit for 1"-16" Pipe	CCKITSS1-16	661165809978	1"	16"
781250	Clamp Champ™ Standard Kit II for 10"-36" Pipe	CCKIT10-36	661165812503	10"	36"
781251	Clamp Champ™ Stainless Steel Kit II For 10"-36" Pipe	CCKITSS10-36	661165812510	10"	36"
781031	Clamp Champ™ Standard Conversion Kit For Up To 16" Pipe	CCCKSTD16	661165810318	10"	16"
781032	Clamp Champ™ Stainless Steel Conversion Kit For Up To 16" Pipe	CCCKSS16	661165810325	10"	16"
781252	Clamp Champ™ Standard Conversion Kit II For 36"-48" Pipe	CCCKSTD36-48	661165812527	36"	48"
781253	Clamp Champ™ Stainless Steel Conversion Kit II For 36"-48" Pipe	CCCKSS36-48	661165812534	36"	48"

DX CLAMP



The Sumner* DX Clamp is a lightweight drop forged pipe fit-up tool.

SPECIAL FEATURES:

- Fit-up tool for 1"-14" pipe
- Adjustment screws offer hardened steel ball contact with pipe
- Available in five sizes

SPECIFICATIONS

ITEM #	DESCRIPTION	MODEL #	UPC	MINIMUM PIPE CAPACITY	MAXIMUM PIPE CAPACITY
781570	DX Clamp for 1"-3" Pipe	DX1-3	661165815702	1"	3"
781571	DX Clamp for 2"-5" Pipe	DX2-5	661165815719	2"	5"
781572	DX Clamp for 4"-7" Pipe	DX4-7	661165815726	4"	7"
781573	DX Clamp for 5"-9" Pipe	DX5-9	661165815733	5"	9"
781574	DX Clamp for 10"-14" Pipe	DX10-14	661165815740	10"	14"

INTERNAL FIT-UP CLAMP



The Sumner* Internal Fit-Up Clamp is an internal pipe alignment tool that can be used on all standard weld neck and slip-on flanges.

SPECIAL FEATURES:

- Independent adjustment allows for alignment even if internal dimensions differ
- One-piece construction the Internal Fit-Up Clamp is built for durability and reliability
- Simple and quick one-man operation allows for one jaw to clamp the pipe inside diameter and the second jaw to clamp on the flange
- Stainless Steel contact points
- Available in three sizes
- NOTE: The Internal Fit-Up Clamp is an alignment tool. A separate lifting device to support the flange weight is recommended.

SPECIFICATIONS

ITEM #	DESCRIPTION	MODEL #	UPC	MINIMUM PIPE CAPACITY	MAXIMUM PIPE CAPACITY
784100	Internal Fit-Up Clamp for 2"-4" Pipe	IC2-4	661165841008	2"	4"
784102	Internal Fit-Up Clamp for 4"-8" Pipe	IC4-8	661165841022	4"	8"
784103	Internal Fit-Up Clamp for 8"-12" Pipe	IC8-12	661165841039	8"	12"

FLANGE PINS

QWIKP



The Sumner* Flange Pins are designed for fast, accurate alignment of carbon pipe flanges.

SPECIAL FEATURES:

- Available Quick installing pins options works to level flange (two-hole) for tack and weld-out
- Toolless install pins work as convenient reference points to level flange for tack and weld-out
- Hardened pins automatically center on 5/8" to 2-5/8" holes
- Features Acme threads for maximum clamping power
- Uses push-button Qwik pin nuts for fast action alignment

ST-258



FLANGLVLR



SPECIFICATIONS

ITEM #	DESCRIPTION	MODEL #	UPC	MINIMUM PIPE CAPACITY	MAXIMUM PIPE CAPACITY
781235	Qwik Pins* for 5/8" to 1-5/8" Flange Holes (set of 2)	QWIKP	661165812350	5/8"	1-5/8"
780430	Flange Pins for 5/8" to 1-5/8" Flanges Holes (set of 2)	ST-106	661165804300	5/8"	1-5/8"
780429	Stainless Steel Flange Pins for 5/8" to 1-5/8" Flanges Holes (set of 2)	ST-206	661165804294	5/8"	1-5/8"
780650	Flange Pins for 1-1/2" to 2-5/8" Flanges Holes (set of 2)	ST-258	661165806502	1-1/2"	2-5/8"
781240	Qwik Pins* Flange Leveler for 5/8" to 1-5/8" Flange Holes (set of 2)	FLANGLVLR	661165812404	5/8"	1-5/8"

FLANGE SPREADER



The Sumner* manual flange spreader is designed for use in most pipe fitting applications.

SPECIAL FEATURES:

- Can be used for 150 lbs to 1,500 lbs flanges
- Hardened wedge for safe splitting
- Large feed screw
- Drive can be rotated by 1-3/8" wrench or 1/2" (12 mm) bar
- Compact design - strong enough for touch jobs
- 4 models available to cover flange ranges from 1" to 24"

SPECIFICATIONS

ITEM #	DESCRIPTION	MODEL #	UPC	SPREAD	PIN DIAMETER	150 LBS	300 LBS	400 LBS	600 LBS	900 LBS	1,500 LBS
784003	3" Flange Spreader	ST-301	661165840032	3"	5/8"	1"-6"	3/4"-4"	1/2"-2"	-	-	-
784002	4" Flange Spreader	ST-302	661165840025	4"	3/4"	2"-12"		1"-4"	1"-4"	1"-2"	1"-2"
784001	5" Flange Spreader	ST-303	661165840018	5"	7/8"	5"-24"			2"-6"	1"-4"	1"-3"
784000	6-3/8" Flange Spreader	ST-304	661165840001	6-3/8"	1"	10"-24"	7"-24"		4"-10"	1"-8"	1"-5"

HYDRAULIC FLANGE SPREADER



The Sumner* hydraulic flange spreader is designed for use in most heavy duty pipe fitting applications.

SPECIAL FEATURES:

- 10 ton flange splitter to tackle the tough jobs
- Spreader arms adjust from 2-3/4" to 8-1/2"
- Spring return, single action cylinder
- Hardened wedge for safe splitting
- Hand pump and 6 ft hose available as accessories

SPECIFICATIONS

ITEM #	DESCRIPTION	MODEL #	UPC	CAPACITY	CYLINDER CAPACITY	CYLINDER STROKE	FLANGE PIN SIZE	150 LBS	300 LBS	400 LBS	600 LBS	900 LBS	1,500 LBS
784004	Hydraulic Flange Spreader	ST-310	661165840049	9 X 92 MM	10 TON	2"	1-1/4"-1-5/8"	22"-42"	16"-28"	14"-24"	12"-20"	8"-16"	4"-8"
OPTIONAL HYDRAULIC FLANGE SPREADER ACCESSORY													
ITEM #	DESCRIPTION	MODEL #	UPC	CAPACITY	CYLINDER CAPACITY								
777010	Hand Hydraulic Pump for Flange Spreader with Quick Disconnect	HHPUMP	661165770100	6 FT									

ADJUST-A-FIT™



The Sumner* Adjust-A-Fit™ is an alignment tool for fittings that uses gravity to make lining up fittings a trouble-free one man operation.

SPECIAL FEATURES:

- Uses gravity to align fittings for loads up to 45 degrees
- Fastens directly onto fittings for loads up to 1,000 lbs
- Threaded shaft assembly is hardened for long tool life
- Cloverleaf setscrew and threaded shaft handle work from either side

SPECIFICATIONS

ITEM #	DESCRIPTION	MODEL #	UPC	LOAD CAPACITY
780420	Adjust-A-Fit™	ST-104	661165804201	1,000 LBS


ADJUST-A-FLANGE™



The Sumner* Adjust-A-Flange™ when used with the Adjust-A-Fit™ is an alignment tool for fittings that uses gravity to make lining up fittings a trouble-free one man operation

SPECIAL FEATURES:

- Fits all flanges for 5" pipe and larger with bolt holes 3/4" to 1-5/8" (19 to 42 mm)
- Used in combination with the Adjust-A-Fit to bring pipe flanges to exact plumb for tack and weld-out
- Handles loads up to 1,000 lbs
- Flange nuts serve as convenient reference points to check level



SPECIFICATIONS

ITEM #	DESCRIPTION	MODEL #	UPC	LOAD CAPACITY	MINIMUM FLANGE HOLE	MAXIMUM FLANGE HOLE
780425	Adjust-A-Flange™	ST-105	661165804256	1,000 LBS	3/4"	1-5/8"

NYLON EXPANSION PLUGS

Sumner* Nylon Expansion Plugs are ideal for pipework leak testing of drains, pools, spas and purging.

SPECIAL FEATURES:

- Rubber rings are resistant to many chemicals and sea water corrosion
- Hollow shaft with screw cap for sealing or venting
- Available individually or as a kit



SPECIFICATIONS

ITEM #	DESCRIPTION	MODEL #	UPC	RANGE (INCH)	LENGTH OF SEAL
786055	3/4 - 4" Expansion Plug Kit*	NEP3/4-4KIT	661165860559	.7-4.33	.78-1.38"
786060	3/4" Nylon Expansion Plugs	NEP3/4-4KIT	661165860603	.7-.95	.78"
786061	1" Nylon Expansion Plugs	NEP1	661165860610	.90-1.26	1"
786062	1-1/4" Nylon Expansion Plugs	NEP1-1/4	661165860627	1.22-1.65	1.22"
786063	1-1/2" Nylon Expansion Plugs	NEP1-1/2	661165860634	1.46-2.13	1.22"
786064	2" Nylon Expansion Plugs	NEP2	661165860641	1.89-2.56	1.18"
786065	2 1/2" Nylon Expansion Plugs	NEP2-1/2	661165860658	2.36-3.03	1.26"
786066	3" Nylon Expansion Plugs	NEP3/4-4KIT	661165860665	2.76-3.43	1.18"
786067	3 1/2" Nylon Expansion Plugs	NEP3-1/2	661165860672	3.27-3.82	1.18"
786068	4" Nylon Expansion Plugs	NEP4	661165860689	3.74-4.33	1.38"
779395	10MM X 1/4" HOSE BARB	HBARB10X1/4	661165793956	3/4-1-1/4	
779396	1/2" BSP X 3/8" HOSE BARB	HBARB1/2X3/8	661165793963	1-1/2-6	
OPTIONAL PLUG					
786070	6" Aluminum Expansion Plugs	NEP4	661165860702	5.83-6.38	1.46"

*Includes 2 of each of the Nylon Plugs and Hose Barbs (does not include the 786070)

WELD GAS ANALYZER



The Sumner* argo-naught oxygen analyzer for welding with accuracy to .1%.

SPECIAL FEATURES:

- Compact but durable housing
- Air and water-tight storage case included
- High measurement accuracy
- Quick response time
- Clear, large display


SPECIFICATIONS

ITEM #	DESCRIPTION	MODEL #	UPC
779281	Argo-Naught Weld Gas Analyzer	WGA	661165792812
779330	Argo-Naught Replacement Oxygen Sensor	OXYSENS	661165793307

PURGE STAR*



The Sumner* two bag fast install inflatable purge star systems are ideal for pipes 2" to 16".



SPECIAL FEATURES:

- Purge 2"-16" pipe in less than 3 minutes to less than 1% oxygen content
- Reduce argon usage
- Increase weld production rate
- Improve weld quality
- Designed for years of use
- Single inflation or double inflation

SPECIFICATIONS

ITEM #	DESCRIPTION	MODEL #	UPC	MAXIMUM PIPE CAPACITY	HOSE TYPE
788001	2" Inflatable Purge Star*	SHPS2	661165792607	2"	SINGLE
788003	3" Inflatable Purge Star*	SHPS3	661165792614	3"	SINGLE
788004	4" Inflatable Purge Star*	SHPS4	661165792621	4"	SINGLE
788006	6" Inflatable Purge Star*	SHPS6	661165792638	6"	SINGLE
788007	8" Inflatable Purge Star*	SHPS8	661165792645	8"	SINGLE
788008	10" INFLATABLE PURGE STAR*	SHPS10	661165792652	10"	SINGLE
788009	12" Inflatable Purge Star*	DHPS12	661165792669	12"	DOUBLE
788010	14" Inflatable Purge Star*	DHPS14	661165792676	14"	DOUBLE
788011	16" Inflatable Purge Star*	DHPS16	661165792683	16"	DOUBLE

PURGE BUDDIES

Save time and argon with the Sumner* Purge Buddy systems.



SPECIAL FEATURES:

- Inflatable Pipe Stopper for pipes between 2"-36"
- Latex bladder surrounded by fire resistant fabric
- Pull loops for inside of the pipe
- 4.8 ft inflation hose
- Inflates with standard bicycle pump
- Heat resistant to 210° F

SPECIFICATIONS

ITEM #	DESCRIPTION	MODEL #	UPC	MAXIMUM PIPE CAPACITY
786080	2" Purge Buddy	PB2	661165860801	2"
786081	3" Purge Buddy	PB3	661165860818	3"
786082	4" Purge Buddy	PB4	661165860825	4"
786083	5" Purge Buddy	PB5	661165860832	5"
786084	6" Purge Buddy	PB6	661165860849	6"
786085	8" PURGE BUDDY	PB8	661165860856	8"
786086	10" Purge Buddy	PB10	661165860863	10"
786087	12" Purge Buddy	PB12	661165860870	12"
786088	14" Purge Buddy	PB14	661165860887	14"
786089	16" Purge Buddy	PB16	661165860894	16"
786090	18" Purge Buddy	PB18	661165860900	18"
786091	20" Purge Buddy	PB20	661165860917	20"
786092	22" Purge Buddy	PB22	661165860924	22"
786093	24" Purge Buddy	PB24	661165860931	24"
786094	28" Purge Buddy	PB28	661165860948	28"
786095	30" Purge Buddy	PB30	661165860955	30"
786096	32" Purge Buddy	PB32	661165860962	32"
786097	36" Purge Buddy	PB36	661165860979	36"

RING PURGE



Save time and argon with the Sumner* Ring Purge systems.

SPECIAL FEATURES:

- Double hose inflation: Red for dam inflation; Black to fill the weld chamber
- Exclusive dam dump valve deflates dam quickly after weld is completed
- Consists of a high temperature heat protective sleeve
- Purge 18"-80" pipe to less than 1% oxygen content in 10 minutes
- Designed for years of use

SPECIFICATIONS

ITEM #	DESCRIPTION	MODEL #	UPC	MAXIMUM PIPE CAPACITY
786009	18" Ring Purge	RP18	661165860092	18'
786010	20" Ring Purge	RP20	661165860108	20"
786011	22" Ring Purge	RP22	661165860115	22"
786012	24" Ring Purge	RP24	661165860122	24"
786013	26" Ring Purge	ROP26	661165860139	26"
786014	28" Ring Purge	RP28	661165860146	28"
786015	30" Ring Purge	RP30	661165860153	30"
786016	32" Ring Purge	RP32	661165860160	32"
786017	34" Ring Purge	RP34	661165860177	34"
786018	36" Ring Purge	RP36	661165860184	36"
786021	42" Ring Purge	RP42	661165860214	42"
786024	48" Ring Purge	RP48	661165860245	48"
786028	56" Ring Purge	RP56	661165860283	56"
786030	60" Ring Purge	RP60	661165860306	60"
786036	72" Ring Purge	RP72	661165860368	72"
786040	80" Ring Purge	RP80	661165860405	80"

WELDING GAGE



The Sumner* welding gage measures internal hi-lo misalignment and root gap spacing.

SPECIAL FEATURES:

- Accurate quick check of internal hi-lo
- Root weld spacing with little effort
- Available in both imperial and metric

SPECIFICATIONS

ITEM #	DESCRIPTION	MODEL #	UPC
781900	Welding Gage Imperial	WGAGEI	661165819007
781901	Welding Gage Metric	WGAGEM	661165819014

ROTARY GROUND CLAMP



The Sumner* Rotary Ground Clamp is designed to put an end to tangled ground leads.

SPECIAL FEATURES:

- Rotary head turns with the pipe - puts an end to ground lead twist, tangle and wear
- Provides quick, positive ground for roll-out welding of pipe and fittings.
- Cuts down on weld pinholes caused by poor grounding
- Attaches and detaches in seconds
- Makes up ground leads three ways lug, clamp-on and bare cable
- Positive anti-arc bearings take loads up to 400 amps
- Clamps on pipe lips up to 1"



SPECIFICATIONS

ITEM #	DESCRIPTION	MODEL #	UPC	MAXIMUM PIPE CAPACITY
780435	Rotary Ground Clamp	ST-107	661165804355	1"

WELDING

FIT KITS™ TOOLS



The professional pipe fitter's welding clamp kit.

FIT KIT™ 2 - 6"

- A compact pipe fit-up kit containing Sumner's most commonly used fit-up tools
- Each Fit Kit 2 - 6" contains:
 - 2-6" Ultra™ Clamp (Stock # 781150)
 - 2-6" Ultra™ Fit (Stock # 781275)
 - 4-8" Internal Fit-Up Clamp (Stock # 784102)
 - Set of carbon steel Flange Pins (Stock # 780430)
 - MCB Level (Stock # 58281640)
 - Weldbox™ 2008 for storage (Stock # 779910)

FIT KIT™ 2 - 12"

- The Sumner Fit Kit 2 - 12" provides everything the pipe fitter needs, complete with Weldbox™ 3617 for storage
- Each Fit Kit™ 2 - 12" contains:
 - Four (4) Fold-A-Jacks* (Stock # 781300)
 - 2-6" Ultra™ Clamp (Stock # 781150)
 - 5-12" Ultra™ Clamp (Stock # 781170)
 - 2-6" Ultra™ Fit (Stock # 781275)
 - 5-12" Ultra™ Fit (Stock # 781285)
 - 2-4" Internal Fit-Up Clamp (Stock # 784100)
 - 4-8" Internal Fit-Up Clamp (Stock # 784102)
 - 8-12" Internal Fit-Up Clamp (Stock # 784103)
 - MCB Level (Stock # 58281640)
 - Steel Square (Stock # 781920)
 - Set of Qwik Pins* (Stock # 781235)
 - Weldbox™ 3617 for storage (Stock # 779928)



SPECIFICATIONS

ITEM #	DESCRIPTION	MODEL #	UPC
780324	Fit Kits™ for 2-6" Pipe	FK2-6	661165803242
780315	Fit Kits™ for 2-12" Pipe	FK2-12	661165803150

MUL-T-SQUARE*



The Sumner* Mul-T-Square* tool consists of two 45 degree blades that slide effortlessly in an industrial-strength plastic handle.

SPECIAL FEATURES:

- Lightweight durable aluminum construction
- Handles up to 8" flanges and up to 14" fittings
- Versatile for measuring 45° and 90° angle
- Blades marked with both imperial and metric units
- Comes with 10" and 14" arms
- Also available with 30" arms



SPECIFICATIONS

ITEM #	DESCRIPTION	MODEL #	UPC	ARM LENGTH
790000	Mul-T-Square* w/Standard Blades	MTS	661165900002	10" AND 14"
790030	Mul-T-Square* w/Extended Blade	MTSE	661165900309	30"
790021	Mul-T-Square* Blades only (2)	MTSBLADE	661165900217	10" AND 14"
790026	Mul-T-Square* Extended Blades only (2)	MTSEXTBLADE	661165900262	30"
790001	Mul-T-Square* Handle Only	790001	661165900019	

STANDARD SQUARE



Aluminum standard squares from Sumner* are marked with both imperial and metric units.

SPECIAL FEATURES:

- 24" x 16" standard square

SPECIFICATIONS

ITEM #	DESCRIPTION	MODEL #	UPC
781921	Aluminum Square	ALSQ	661165819212

MAGNETIC HOLDER



Sumner* magnetic holders can be used to position a standard builder's square for layout work or to create an ideal burning guide.

SPECIAL FEATURES:

- Use Magnetic Holders with a standard square to create an ideal torch guide
- Sold in packages of three (3)
- Holds squares up to 1/8" thick



SPECIFICATIONS

ITEM #	DESCRIPTION	MODEL #	UPC
781895	Magnetic Holders (3)	MAGHOLD	661165818956

MULTI PURPOSE MAGNETIC FIXTURES



The Sumner* Angle Welding Fixture accurately positions flat and round ferrous metal for welding and assembly.

SPECIAL FEATURES:

- Holds angles at 30°, 45°, 60°, 75° and 90°
- Strong magnets allow for a hands-free hold
- Capable of 48.5 lbs of holding force
- Available in 4 options: small, medium, large and multiple angle fixtures

SPECIFICATIONS

ITEM #	DESCRIPTION	MODEL #	UPC
781885	Multiple Angle Welding Fixture	MZWF	661165818857
781886	Small Angle Welding Fixture	SAWF	661165818864
781887	Medium Angle Welding Fixture	MAWF	661165818871
781888	Large Angle Welding Fixture	LAWF	661165818888



MAGNETIC TORCH GUIDE KIT



Sumner* magnetic torch guide can be used to layout work or to create an ideal burning guide.

SPECIAL FEATURES:

- Use to create an ideal burning guide
- Kit includes a 24" stainless steel cutting rail and (2) magnetic holders

SPECIFICATIONS

ITEM #	DESCRIPTION	MODEL #	UPC
781896	Magnetic Torch Guide	MAGTRCH	661165818963

POCKET LEVEL



The Sumner* Pocket Level is compact to accommodate many fit-up tasks.

SPECIAL FEATURES:

- Twin vial construction reads 0° and 90°
- Tough ABS plastic with a strong magnetic base
- Easy to read high impact acrylic bubble vials

ACCU-LEVEL



The Sumner* Accu-level is a high-accuracy, portable level designed for pipe fitting and welding applications.

SPECIAL FEATURES:

- Features three vials (0°, 45° and 90°)
- Made with rugged die cast aluminum
- Grooved based that fits on pipe and conduit
- Earthen magnetic base
- Comes with belt holster

TORPEDO LEVEL



The Southwire™ Conduit Bending Level has high-visibility vials that are easy to read.

SPECIAL FEATURES:

- Three leveling vials set at 0°, 45°, and 90°
- Integrated light illuminates vials for better visibility
- Lightweight and durable aluminum construction
- Easy to read high impact acrylic bubble vials
- V-grooved edge helps hold the level in place on pipe or conduit
- Water and impact resistant

MCBLEVEL



The Sumner* Pocket Level is compact to accommodate many fit-up tasks.

SPECIAL FEATURES:

- Four leveling vials set at 0°, 30°, 45°, and 90°
- Four powerful magnets for hands-free operation
- Easy to read high impact acrylic bubble vials
- V-grooved edge helps hold the level in place on pipe or conduit
- Lightweight and durable aluminum construction
- Set screw secures level to conduit

SPECIFICATIONS

ITEM #	DESCRIPTION	MODEL #	UPC
781947	Pocket Level	PLVL	661165819472
781950	Accu-level	ALVL	661165819502
58281840	Torpedo Level 9"	LVLTOR9	032886911026
58281640	Conduit Bending Level 6"	MCBLEVEL	032886908606

WELDER'S STOOL



The Sumner* tractor style welder's stool is designed specifically for fabrication shops.

SPECIAL FEATURES:

- Stamped steel seat with air holes
- Designed for comfort even during 8 hour shifts
- High strength steel construction
- Uses Sumner lock washer for quick height adjustment
- 300 lbs capacity
- Max. height: 22"
- Min. height: 15"

SPECIFICATIONS

ITEM #	DESCRIPTION	MODEL #	UPC
785800	Welder's Stool	WS1	661165858006

JACKS

Heavy Duty Jacks

Pro Jack*

Fold-A-Jack*

Fat Jack™

Hi Boy™

Fab™ Saf Jack

Adjust-A-Rolls™

Mini Roll

Pro Roll™

Big V™

Max Jax*

Max Jax* 2

Beam Jax™

Reel Mac™

Hold Down Device

Hold E*



HEAVY DUTY JACKS



The Sumner* Heavy Duty jacks are a fixed leg stand constructed of rugged 1" steel tubing.

SPECIAL FEATURES:

- Designed for large loads up to 2,500 lbs depending on the head option
- Patented Fall Guard™ feature allows 1" safety zone around lock washer
- Set screw can lock jack head to stand for transportation - no loose pieces
- 1-1/2" ACME fine adjustment thread with large, convenient adjustment handle
- Breaks down for easy storage
- Available with 7 head options



SPECIFICATIONS

ITEM #	DESCRIPTION	MODEL #	UPC	LOAD CAPACITY
HI HEAVY DUTY				
780375	Hi Heavy Duty Jack w/Vee Head	ST-801	661165803754	2500 lbs
780376	Hi Heavy Duty Jack w/Roller Head	ST-802	661165803761	2000 lbs
780377	Hi Heavy Duty Jack w/Bar Stock Head	ST-803	661165803778	2000 lbs
780378	Hi Heavy Duty Jack w/Stainless Steel Rollers	ST-804	661165803785	2000 lbs
780379	Hi Heavy Duty Jack w/Stainless Steel Vee Head	ST-805	661165803792	2500 lbs
780380	HI HEAVY DUTY JACK W/BALL TRANSFER HEAD	ST-806	661165803808	1000 lbs
780381	Hi Heavy Duty Jack w/Rubber Wheels	ST-807	661165803815	1000 lbs
LOW-HEAVY DUTY				
780385	Lo Heavy Duty Jack w/Vee Head	ST-901	661165803853	2500 lbs
780386	Lo Heavy Duty Jack w/Roller Head	ST-902	661165803860	2000 lbs
780387	Lo Heavy Duty Jack w/Bar Stock Head	ST-903	661165803877	2000 lbs
780388	Lo Heavy Duty Jack w/Stainless Steel Rollers	ST-904	661165803884	2000 lbs
780389	Lo Heavy Duty Jack w/Stainless Steel Vee Head	ST-905	661165803891	2500 lbs
780390	Lo Heavy Duty Jack w/Ball Transfer Head	ST-906	661165803907	1000 lbs
780391	Lo Heavy Duty Jack w/Rubber Wheels	ST-907	661165803914	1000 lbs
HI HEAVY DUTY PLUS				
780326	Hi Heavy Duty Jack Plus w/Ribbed Vee	HIHDPLUS	661165803266	3500 lbs

PRO JACK*



The Sumner* Pro Jack* is an economical fixed leg stand.

SPECIAL FEATURES:

- Designed for large loads up to 2,000 lbs
- Patented Fall Guard™ feature allows 1" safety zone around lock washer.
- Set screw can lock jack head to stand for transportation - no loose pieces.
- 1-1/2" ACME fine adjustment thread with large, convenient adjustment handle.
- Available with 7 head options.

SPECIFICATIONS

ITEM #	DESCRIPTION	MODEL #	UPC	LOAD CAPACITY
780471	Hi Pro Jack* w/Vee Head	ST-871	661165804713	2000 lbs
780472	Hi Pro Jack* w/Roller Head	ST-872	661165804720	2000 lbs
780473	Hi Pro Jack* w/Bar Stock Head	ST-873	661165804737	2000 lbs
780474	Hi Pro Jack* w/Stainless Steel Rollers	ST-874	661165804744	2000 lbs
780475	Hi Pro Jack* w/Stainless Steel Vee Head	ST-875	661165804751	2000 lbs
780476	Hi Pro Jack* w/Ball Transfer Head	ST-876	661165804768	1000 lbs
780477	Hi Pro Jack* w/Rubber Wheels	ST-877	661165804775	1000 lbs

FOLD-A-JACK*



The Sumner* Fold-A-Jack* is a light weight, collapsible, tri-leg pipe stand available in two heights to serve most fabrication sites.

SPECIAL FEATURES:

- Designed for large loads up to 2,500 lbs
- Patented Fall Guard™ feature allows 1" safety zone around lock washer
- Easy grip carrying handle for breakdown and transportation
- Set screw can lock jack head to stand for transportation - no loose pieces
- 1-1/2" ACME fine adjustment thread with large, convenient adjustment handle
- Available with 7 head options

SPECIFICATIONS

ITEM #	DESCRIPTION	MODEL #	UPC	LOAD CAPACITY
HI FOLD-A-JACK*				
781300	Hi Fold-A-Jack* w/Vee Head	ST-881	661165813005	2500 lbs
781301	Hi Fold-A-Jack* w/Roller Head	ST-882	661165813012	2000 lbs
781302	Hi Fold-A-Jack* w/Bar Stock Head	ST-883	661165813029	2000 lbs
781303	Hi Fold-A-Jack* w/Stainless Steel Rollers	ST-884	661165813036	2000 lbs
781304	Hi Fold-A-Jack* w/Stainless Steel Vee Head	ST-885	661165813043	2500 lbs
781305	Hi Fold-A-Jack* w/Ball Transfer Head	ST-886	661165813050	1000 lbs
781306	Hi Fold-A-Jack* w/Rubber Wheels	ST-887	661165813067	1000 lbs
LOW FOLD-A-JACK*				
781310	Lo Fold-A-Jack* w/Vee Head	ST-981	661165813104	2500 lbs
781311	Lo Fold-A-Jack* w/Roller Head	ST-982	661165813111	2000 lbs
781313	Lo Fold-A-Jack* w/Stainless Steel Roller Head	ST-983	661165813135	2000 lbs
781314	Lo Fold-A-Jack* w/Stainless Steel Vee Head	ST-984	661165813142	2500 lbs
781315	Lo Fold-A-Jack* w/Ball Transfer Head	ST-985	661165813159	1000 lbs
781316	Lo Fold-A-Jack* w/Rubber Wheels	ST-986	661165813166	1000 lbs

JACKS

FAT JACK™



The Sumner* Fat Jack™ is a collapsible base constructed of rugged 1.25" steel tubing.

SPECIAL FEATURES:

- Designed for large loads up to 6,000 lbs
- Easy grip carrying handle for breakdown and transportation
- Double locking pin system for fast height adjustment
- 1-1/2" ACME fine adjustment thread with large, convenient adjustment handle
- Breaks down for easy storage
- Available with 2 head options and 2 sizes

SPECIFICATIONS

ITEM #	DESCRIPTION	MODEL #	UPC	LOAD CAPACITY
MAXI FAT JACK™				
785250	Maxi FAT Jack™ w/ Vee Head	MAXIFJVH	661165852509	6000 lbs
785255	Maxi FAT Jack™ w/ Roller Head	MAXIFJRH	661165852554	6000 lbs
MIDI FAT JACK™				
785251	Midi FAT Jack™ w/ Vee Head	MIDIFJVH	661165852516	6000 lbs
785256	Midi FAT Jack™ w/ Roller Head	MIDIFJRH	661165852561	6000 lbs
MINI FAT JACK™				
785252	Mini FAT Jack™ w/ Vee Head	MINIFJVH	661165852523	6000 lbs
785257	Mini FAT Jack™ w/ Roller Head	MINIFJRH	661165852578	6000 lbs
OPTIONAL ACCESSORY				
785220	Roller Head	785220	661165852202	6000 lbs

HI BOY™



The Sumner* Hi Boy™ is a collapsible base constructed of rugged 1.25" steel tubing

SPECIAL FEATURES:

- Designed for loads up to 1,000 lbs
- Height range of 39" to 72"
- Easy grip carrying handle for breakdown and transportation
- Double locking pin system for fast height adjustment
- 1-1/2" ACME fine adjustment thread with large, convenient adjustment handle
- Breaks down for easy storage

SPECIFICATIONS

ITEM #	DESCRIPTION	MODEL #	UPC	LOAD CAPACITY
783250	Hi Boy™ Jack w/Vee Head	HIBOY	661165832501	1000 lbs

FAB SAF™ JACK



The Sumner* FAB SAF™ jacks are a fixed leg wide base stand constructed of rugged 1" steel tubing.

SPECIAL FEATURES:

- Designed for large loads up to 3,500 lbs capacity on the vee head and 2,500 lbs capacity on the roller head
- 30" Wide Heavy Duty Base for added stability
- Patented Fall Guard™ feature allows 1" safety zone around lock washer
- Set screw can lock jack head to stand for transportation - no loose pieces
- 1-1/2" ACME fine adjustment thread with large, convenient adjustment handle
- Breaks down for easy storage
- Available with 2 head options

SPECIFICATIONS

ITEM #	DESCRIPTION	MODEL #	UPC	LOAD CAPACITY
780395	FAB SAF™ Jack w/Vee Head	FABSAFV	661165803952	3500 lbs
780400	FAB SAF™ Jack w/Roller Head	FABSAFRH	661165804003	2500 lbs

ADJUST-A-ROLLS™



The Sumner* Adjust-A-Roll™ has a wide four legged base and quick change head making it ideal for pipe rotation and fabrication.

SPECIAL FEATURES:

- Large 1/2" to 36" or 2,500 lbs. pipe capacity • 30" Wide Heavy Duty Base for added stability
- Bronze bearing design reduces arcing
- Large handle makes for easy adjustment even with a gloved hand
- Smooth roller adjustment accessible from either side
- Quick change head and fine adjustment screw for precise pipe rotation
- Available with 5 head attachments and 3 sizes

SPECIFICATIONS

ITEM #	DESCRIPTION	MODEL #	UPC	LOAD CAPACITY
HI ADJUST-A-ROLL™				
780365	Hi Adjust-A-Roll™ w/Roller Wheels	ST-601	661165803655	2500 lbs
780366	Hi Adjust-A-Roll™ w/Ball Transfer Head	ST-602	661165803662	1000 lbs
780367	Hi Adjust-A-Roll™ w/Rubber Wheels	ST-603	661165803679	1200 lbs
780368	Hi Adjust-A-Roll™ w/Stainless Steel Wheels	ST-604	661165803686	2000 lbs
780369	Hi Adjust-A-Roll™ w/Bar Stock Head	ST-605	661165803693	2500 lbs
780399	HI ADJUST-A-ROLL™ HI, BASE ONLY	ST60BASE	661165803990	2500 lbs
LO ADJUST-A-ROLL™				
780370	Lo Adjust-A-Roll™ w/Roller Wheels	ST-701	661165803709	2500 lbs
780371	Lo Adjust-A-Roll™ w/Ball Transfer Head	ST-702	661165803716	1000 lbs
780372	Lo Adjust-A-Roll™ w/Rubber Wheels	ST-703	661165803723	1200 lbs
780373	Lo Adjust-A-Roll™ w/Stainless Steel Wheels	ST-704	661165803730	2000 lbs
780359	Lo Adjust-A-Roll™ w/Bar Stock Head	ST-705	661165803594	2000 lbs
780405	Lo Adjust-A-Roll™ Base Only	ST70BASE	661165804058	2500 lbs
TABLE ADJUST-A-ROLL™				
780360	Table Adjust-A-Roll™ w/Roller Wheels	ST-501	661165803600	2500 lbs
780361	Table Adjust-A-Roll™ w/Ball Transfer Head	ST-502	661165803617	1000 lbs
780362	Table Adjust-A-Roll™ w/Rubber Wheels	ST-503	661165803624	1200 lbs
780363	Table Adjust-A-Roll™ w/Stainless Steel Wheels	ST-504	661165803631	2000 lbs
780364	Table Adjust-A-Roll™ w/Bar Stock Head	ST-505	661165803648	2000 lbs
780500	Table Adjust-A-Roll™ Base Only	ST50BASE	661165805000	2500 lbs

MINI-ROLL



The Sumner* Mini-Roll™ has a wide four legged base and quick change head making it ideal for pipe rotation and fabrication.

SPECIAL FEATURES:

- Large 1/2" to 36" or 3,500 lbs pipe capacity
- Small footprint of 11" wide by 22" long
- Bronze bearing design reduces arcing
- Large handle makes for easy adjustment even with a gloved hand
- Smooth roller adjustment accessible from either side
- Quick change head and fine adjustment screw for precise pipe rotation
- Available with 5 head attachments

SPECIFICATIONS

ITEM #	DESCRIPTION	MODEL #	UPC	LOAD CAPACITY
785280	Mini-Roll w/ AL Roller Wheels	ST-551	661165852806	2500 lbs
785281	Mini-Roll w/ Ball Transfer Head	ST-552	661165852813	1000 lbs
785282	Mini-Roll w/ Rubber Wheels	ST-553	661165852820	1200 lbs
785283	Mini-Roll w/ Stainless Steel Wheels	ST-554	661165852837	2000 lbs
785284	Mini-Roll w/ Bar Stock Head	ST-555	661165852844	2000 lbs
785288	Mini-Roll w/ Stainless Steel Ball Transfer Head	ST-556	661165852882	1000 lbs
785285	Mini-Roll, Base Only	ST-55BASE	661165852851	2500 lbs

PRO ROLL™



The Sumner* Pro Roll™ has a wide four legged base and adjustable height making it ideal for pipe rotation and fabrication.

SPECIAL FEATURES:

- Large 1/2" to 36" or 2,500 lbs pipe capacity
- Bronze bearing design reduces arcing
- Large handle makes for easy adjustment even with a gloved hand
- Smooth roller adjustment accessible from either side
- Quick change head and fine adjustment screw for precise pipe rotation
- Available with 5 head attachments

SPECIFICATIONS

ITEM #	DESCRIPTION	MODEL #	UPC	LOAD CAPACITY
780441	Pro Roll™ w/ AL Roller Wheels	ST-401	661165804416	2500 lbs
780442	Pro Roll™ w/Ball Transfer Head	ST-402	661165804423	1000 lbs
780443	Pro Roll™ w/Rubber Wheels	ST-403	661165804430	1200 lbs
780444	Pro Roll™ w/Stainless Steel Wheels	ST-404	661165804447	2000 lbs
780446	Pro Roll™ w/Bar Stock Head	ST-405	661165804461	2000 lbs
780440	Pro Roll™ , Base Only	ST-40BASE	661165804409	2500 lbs

BIG V™



The Sumner* Big V™ is a heavy duty jack stand and is built tough for the demands of larger pipes.

SPECIAL FEATURES:

- Designed for large pipe the Big V™ can hold up to 2,500 lbs
- The large 12" vee head supports pipe sizes ranging from 4" to 36"
- Fast action adjustment handle
- Wide base tri-stand provides superior balance
- 8 different head options available



SPECIFICATIONS

ITEM #	DESCRIPTION	MODEL #	UPC	LOAD CAPACITY
780260	Big V™ (Basic) with Standard Big Vee Head	BIGVB	661165802603	2500 lbs
OPTIONAL BIG V™ ACCESSORIES				
781382	Stainless Steel Sleeves (4)	MJ-SS	661165813821	4500 lbs
781383	Ball Transfers (2)	MJ-BT	661165813838	1000 lbs
781394	Rubber Wheel Kit (4)	MJ-RB	661165813944	1000 lbs
781397	Stainless Steel Ball Transfers (2)	MJ-BTSS	661165813975	1200 lbs
781406	Aluminum Roller Head Kit (4)	MJ-RH	661165814064	4500 lbs
781407	Stainless Steel Roller Head Kit (4)	MJ-RHSS	661165814071	2000 lbs

MAX JAX*



781403

The Sumner* MAX JAX* fabrication stands are the ideal 5-legged stand for fit-up, rotating and welding.

SPECIAL FEATURES:

- Designed for loads up to 4,500 lbs
- Designed to hold 6" to 36" pipe (781403) or 4" to 36" pipe (781460)
- Large 12" roller vee head included
- 5-leg base construction ensures stability
- Available in fixed base design or with 8" casters
- Optional head attachments available



781460



SPECIFICATIONS

ITEM #	DESCRIPTION	MODEL #	UPC	LOAD CAPACITY
781460	MAX JAX* Basic - includes vee head & leveling pads	MJAXB	661165814606	4500 lbs
781403	MAX JAX* Kit No. 1 - includes roller head kit and casters	MJAXKIT1	661165814033	4500 lbs
OPTIONAL MAX JAX* ACCESSORIES				
781382	Stainless Steel Sleeves (4)	MJ-SS	661165813821	4500 lbs
781383	Ball Transfers (2)	MJ-BT	661165813838	1000 lbs
781394	Rubber Wheel Kit (4)	MJ-RB	661165813944	1000 lbs
781397	Stainless Steel Ball Transfers (2)	MJ-BTSS	661165813975	1200 lbs
781406	Aluminum Roller Head Kit (4)	MJ-RH	661165814064	4500 lbs
781407	Stainless Steel Roller Head Kit (4)	MJ-RHSS	661165814071	2000 lbs
781464	Caster Kit (5) Standard	MJ-CK	661165814644	4500 lbs
781465	Caster Kit (5) Steel Casters	MJ-CKS	661165814651	4500 lbs
781050	Hold Down Device	HDD-01	661165810509	
781056	Hold Down Device Chain Ext. Kit (12")	HDD-EXT	661165810561	

MAX JAX* 2 STAND



786450

The Sumner* MAX JAX* 2 upgraded fabrication stands are the ideal high and low stand for fit-up, rotating and welding.

SPECIAL FEATURES:

- Designed for loads up to 4,500 lbs
- Designed to hold 4" to 36" pipe
- Dual height range of 21.5" to 32" low or 26.5" to 36" high
- 5-leg base construction with adjustable 6" casters ensure stability
- Optional head attachments available



786451

SPECIFICATIONS

ITEM #	DESCRIPTION	MODEL #	UPC	LOAD CAPACITY
786451	MAX JAX* Kit 2 w/Drop Slot Head	MJAX2RR	661165864519	4500 lbs
786450	MAX JAX* Kit 2 w/Large Vee & Rollers	MJAX2	661165864502	4500 lbs
OPTIONAL MAX JAX* ACCESSORIES				
781382	Stainless Steel Sleeves (4)	MJ-SS	661165813821	4500 lbs
781383	Ball Transfers (2)	MJ-BT	661165813838	1000 lbs
781394	Rubber Wheel Kit (4)	MJ-RB	661165813944	1200 lbs
781397	Stainless Steel Ball Transfers (2)	MJ-BTSS	661165813975	1000 lbs
781406	Aluminum Roller Head Kit (4)	MJ-RH	661165814064	4500 lbs
781407	Stainless Steel Roller Head Kit (4)	MJ-RHSS	661165814071	2000 lbs
781464	Caster Kit (5) Standard	MJ-CK	661165814644	4500 lbs
781465	Caster Kit (5) Steel Casters	MJ-CKS	661165814651	4500 lbs
781050	Hold Down Device	HDD-01	661165810509	
781056	Hold Down Device Chain Ext. Kit (12")	HDD-EXT	661165810561	

BEAM JAX™

The Sumner* Beam Jax™ are designed to secure beams for fabrication.

SPECIAL FEATURES:

- Designed for loads up to 2,500 lbs
- Designed for beams up to 24"
- Clamping device centers load on stand and holds material in place
- 5-leg base construction ensures stability
- Reversible beam fork design
- Detachable handle can be rotated out of operator's way
- Available as a kit with leveling pads or casters 8" casters



781486



781485

SPECIFICATIONS

ITEM #	DESCRIPTION	MODEL #	UPC	LOAD CAPACITY
781485	Basic Beam Jax™ - includes leveling pads	BJAX	661165814859	2500 lbs
781486	Beam Jax™ Kit - includes casters	BJAXKIT	661165814866	2500 lbs

REEL MAC™



The Sumner* Reel Mac™ jack stands are a heavy duty version of the traditional reel stand with capacity up to 3,750 lbs

SPECIAL FEATURES:

- Designed for large loads up to 2,500 lbs
- Height range of 13" - 45" depending on jack
- Extra strength double locking pin for quick set up
- 1-1/2" ACME fine adjustment thread with large, convenient adjustment handle
- Designed to work with the Sumner Reel/Econo Mac Spindles

SPECIFICATIONS

ITEM #	DESCRIPTION	MODEL #	UPC	LOAD CAPACITY
REEL MAC™				
780941	Reel Mac™ No. 60	CJ02	661165809411	2500 lbs
780942	Reel Mac™ No. 70	CJ01	661165809428	2500 lbs
780943	Reel Mac™ No. 80	CJ03	661165809435	2500 lbs
OPTIONAL REEL MAC™ ACCESSORIES				
780229	No. 61 Reel Mac™ Spindle (62")	SA60	661165802290	5000 lbs
780230	No. 71 Reel Mac™ Spindle (76")	SA70	661165802306	5000 lbs

HOLD DOWN DEVICE



The Sumner* Hold Down Device is ideal for securing material on vee head jacks for transportation and fit-ups.

SPECIAL FEATURES:

- Designed for use on up to 12" pipe
- Heavy duty design featuring high tensile strength chain
- 12" chain extensions available for increased capacity

SPECIFICATIONS

ITEM #	DESCRIPTION	MODEL #	UPC	MAXIMUM PIPE CAPACITY
781050	Hold Down Device	HDD-01	661165810509	12"
781056	Hold Down Device Chain Ext. Kit (12")	HDD-EXT	661165810561	12"

HOLD-E*



The Sumner* Hold-E* Pipe Clamp is designed to quickly secure pipe or tubing to vee head jack stands.

SPECIAL FEATURES:

- Designed for 3/4" to 6" pipe or 1" to 6-1/2" tubing
- Push button design allows for rapid action setting and fine tune thread adjustment
- Jobsite ready with a heavy duty design
- Large threads and vee jaw provide a secure clamping force
- Available in 2 options

SPECIFICATIONS

ITEM #	DESCRIPTION	MODEL #	UPC	MINIMUM PIPE CAPACITY	MAXIMUM PIPE CAPACITY
785000	Hold-E*	HOLDE	661165850000	3/4"	6"
784999	Stainless Steel Hold-E*	HOLDESS	661165849998	3/4"	6"

JACKS

SPECIFICATIONS

PIPE STAND	PART #	DESCRIPTION	LOAD CAPACITY	MIN PIPE CAPACITY	MAX PIPE CAPACITY	MIN. HEIGHT	MAX HEIGHT	WIDTH	LENGTH	WEIGHT
FOLD-A-JACK™										
	781300	HI FAJ - Vee	2,500 lbs	1/8" (3 mm)	24" (600 mm)	28" (71 cm)	49" (125 cm)	22" (56 cm)	22" (56 cm)	25 lbs
	781301	HI FAJ - AL Roller	2,000 lbs	1-1/4" (30 mm)	24" (600 mm)					28 lbs
	781302	HI FAJ - Bar Stock	2,000 lbs	1/8" (3 mm)	10" (250 mm)					25 lbs
	781303	HI FAJ - SS Roller	2,000 lbs	1-1/4" (30 mm)	24" (600 mm)					29 lbs
	781304	HI FAJ - SS Vee	2,500 lbs	1/8" (3 mm)	24" (600 mm)					24 lbs
	781305	HI FAJ - Ball Trans	1,000 lbs	3/8" (10 mm)	12" (300 mm)					29 lbs
	781306	HI FAJ - Rubber Whls	1,200 lbs	1-1/2" (40 mm)	24" (600 mm)	21" (51 cm)	36" (89 cm)	15-1/2" (39 cm)	15-1/2" (39 cm)	26 lbs
	781310	LO FAJ - Vee	1,000 lbs	1/8" (3 mm)	24" (600 mm)					21 lbs
	781311	LO FAJ - AL Roller	2,000 lbs	1-1/4" (30 mm)	24" (600 mm)					24 lbs
	781313	LO FAJ - SS Roller	2,000 lbs	1-1/4" (30 mm)	24" (600 mm)					24 lbs
	781314	LO FAJ - SS Vee	2,500 lbs	1/8" (3 mm)	24" (600 mm)					22 lbs
	781315	LO FAJ - Ball Trans	1,000 lbs	3/8" (10 mm)	12" (300 mm)					25 lbs
	781316	LO FAJ - Rubber Whls	1,200 lbs	1-1/2" (40 mm)	24" (600 mm)					22 lbs
HEAVY DUTY JACK™										
	781375	HI HD - Vee	2,500 lbs	1/8" (3 mm)	24" (600 mm)	28" (71 cm)	49" (125 cm)	22" (56 cm)	22" (56 cm)	24 lbs
	781376	HI HD - AL Roller	2,000 lbs	1-1/4" (30 mm)	24" (600 mm)					27 lbs
	781377	HI HD - Bar Stock	2,000 lbs	1/8" (3 mm)	10" (250 mm)					24 lbs
	781378	HI HD - SS Roller	2,000 lbs	1-1/4" (30 mm)	24" (600 mm)					28 lbs
	781379	HI HD - SS Vee	2,500 lbs	1/8" (3 mm)	24" (600 mm)					24 lbs
	781380	HI HD - Ball Trans	1,000 lbs	3/8" (10 mm)	12" (300 mm)					27 lbs
	781381	HI HD - Rubber Whls	1,200 lbs	1-1/2" (40 mm)	24" (600 mm)	21" (51 cm)	36" (89 cm)	15-1/2" (39 cm)	15-1/2" (39 cm)	26 lbs
	781385	LO HD - Vee	2,500 lbs	1/8" (3 mm)	24" (600 mm)					19 lbs
	781386	LO HD - AL Roller	2,000 lbs	1-1/4" (30 mm)	24" (600 mm)					22 lbs
	781387	LO HD - Bar Stock	2,000 lbs	1/8" (3 mm)	24" (600 mm)					18 lbs
	781388	LO HD - SS Roller	2,000 lbs	1-1/4" (30 mm)	24" (600 mm)					22 lbs
	781389	LO FAJ - SS Vee	2,500 lbs	1/8" (3 mm)	24" (600 mm)					19 lbs
	781390	LO FAJ - Ball Trans	1,000 lbs	3/8" (10 mm)	12" (300 mm)					22 lbs
	781391	LO FAJ - Rubber Whls	1,200 lbs	1-1/2" (40 mm)	24" (600 mm)					21 lbs
HEAVY DUTY JACK™ PLUS										
	780326	HD PLUS - Vee	3,500 lbs	1/8" (3 mm)	24" (600 mm)	28" (71 cm)	49" (125 cm)	22" (56 cm)	22" (56 cm)	24 lbs
PRO JACK™										
	780471	HI PRO - Vee	2,000 lbs	1/8" (3 mm)	24" (600 mm)	28" (71 cm)	49" (125 cm)	24" (61 cm)	24" (61 cm)	23 lbs
	780472	HI PRO - AL Roller	2,000 lbs	1-1/4" (30 mm)	24" (600 mm)					26 lbs
	780473	HI PRO - Bar Stock	2,000 lbs	1/8" (3 mm)	10" (250 mm)					23 lbs
	780474	HI PRO - SS Roller	2,000 lbs	1-1/4" (30 mm)	24" (600 mm)					26 lbs
	780475	HI PRO - SS Vee	2,000 lbs	1/8" (3 mm)	24" (600 mm)					24 lbs
	780476	HI PRO - Ball Trans	1,000 lbs	3/8" (10 mm)	12" (300 mm)					28 lbs
	780477	HI PRO - Rubber Whls	1,200 lbs	1-1/2" (40 mm)	24" (600 mm)					25 lbs

PIPE STAND	PART #	DESCRIPTION	LOAD CAPACITY	MIN PIPE CAPACITY	MAX PIPE CAPACITY	MIN. HEIGHT	MAX HEIGHT	WIDTH	LENGTH	WEIGHT
FAT JACK™										
	785250	Maxi Fat Jack™ - Vee	6,000 lbs	1/8" (3 mm)	36" (900 mm)	36"	61" (154.9 cm)	34" (86.3 cm)	34" (86.3 cm)	47 lbs
	785251	Midi Fat Jack™ - Vee				26.5"	44.5" (113 cm)	21" (53.3 cm)	21" (53.3 cm)	37 lbs
	785252	Mini Fat Jack™ - Vee				16"	28.5" (72.4 cm)	19" (48.3 cm)	19" (48.3 cm)	28 lbs
	785255	Maxi Fat Jack™ - AL Roller			24" (600 mm)	36"	61" (154.9 cm)	34" (86.3 cm)	34" (86.3 cm)	47 lbs
	785256	Midi Fat Jack™ - AL Roller				26.5"	44.5" (113 cm)	21" (53.3 cm)	21" (53.3 cm)	37 lbs
	785257	Mini Fat Jack™ - AL Roller				16"	28.5" (72.4 cm)	19" (48.3 cm)	19" (48.3 cm)	28 lbs
FAB SAF™ JACK										
	780395	FAB SAF™ - Vee	3,500 lbs	1/8" (3 mm)	36" (900 mm)	32" (81 cm)	52" (132 cm)	30" (76 cm)	30" (76 cm)	26 lbs
	780400	FAB SAF™ - Roller	2,500 lbs	1-1/4" (30 mm)	24" (600 mm)					26 lbs
HI BOY™										
	783250	HI BOY™	1,000 lbs	1/8" (3 mm)	24" (600 mm)	39" (98 cm)	72" (180 cm)	38" (97 cm)	38" (97 cm)	45 lbs
ADJUST-A-ROLL™										
	780365	HI AAR - Alum Whls	2,500 lbs	1/2" (12 mm)	36" (900 mm)	31" (78 cm)	23" (58 cm)	32" (81 cm)		35 lbs
	780366	HI AAR - Ball Trans	1,000 lbs							38 lbs
	780367	HI AAR - Rubber Whls	1,200 lbs							34 lbs
	780368	HI AAR - SS Whls	2,000 lbs							35 lbs
	780369	HI AAR - Bar Stock	2,000 lbs							39 lbs
	780370	LO AAR - Alum Whls	2,500 lbs	1/2" (12 mm)	36" (900 mm)	24" (61 cm)	22" (56 cm)	31" (79 cm)		24 lbs
	780371	LO AAR - Ball Trans	1,000 lbs							24 lbs
	780372	LO AAR - Rubber Whls	1,200 lbs							32 lbs
	780373	LO AAR - SS Whls	2,000 lbs							34 lbs
	780359	LO AAR - Bar Stock	2,000 lbs							37 lbs
	780360	TBL AAR - Alum Whls	2,500 lbs	1/2" (12 mm)	36" (900 mm)	7" (18 cm)	6-1/4" (16 cm)	22" (56 cm)		22 lbs
	780361	TBL AAR - Ball Trans	1,000 lbs			5-3/4" (15 cm)				22 lbs
	780362	TBL AAR - Rubber Whls	1,200 lbs			7" (18 cm)				20 lbs
	780363	TBL AAR - SS Whls	2,000 lbs			7" (18 cm)				22 lbs
	780364	TBL AAR - Bar Stock	2,000 lbs			5-3/4" (15 cm)				24 lbs
PRO ROLL™										
	780441	PRO ROLL™ - Alum Whls	2,500 lbs	1/2" (12 mm)	36" (900 mm)	29" (79 cm)	43" (109 cm)	23" (58 cm)	32" (81 cm)	47 lbs
	780442	PRO ROLL™ - Ball Trans	1,000 lbs							49 lbs
	780443	PRO ROLL™ - Rubber Whls	1,200 lbs							45 lbs
	780444	PRO ROLL™ - SS Whls	2,000 lbs							47 lbs
	780446	PRO ROLL™ - Bar Stock	2,000 lbs							49 lbs
BIG V* JACK										
	780260	BIG V*	2,500 lbs	4" (100 mm)	36" (900 cm)	29-1/2" (75 cm)	41" (109 cm)	29-1/2" (75 cm)	29-1/2" (75 cm)	36 lbs

JACKS

PIPE STAND	PART #	DESCRIPTION	LOAD CAPACITY	MIN PIPE CAPACITY	MAX PIPE CAPACITY	MIN. HEIGHT	MAX HEIGHT	WIDTH	LENGTH	WEIGHT
MAX JAX* & MAX JAX* 2										
	781460	Max Jax* Basic	4,500 lbs	4" (100 mm)	36" (900 mm)	21" (53 cm)	33" (84 cm)	29-5/8" (75 cm)	29-5/8" (75 cm)	68 lbs
	781403	Max Jax* Kit Includes Casters (Roller Head)				30-1/2" (78 cm)	42-1/2" (108 cm)	34" (100 cm)	34" (100 cm)	144 lbs
	781450	Max Jax* 2 Kit #1 (Vee Head)				52" (133 cm)	74" (188 cm)	37.5" (95 cm)	37.5" (95 cm)	106 lbs
	781451	Max Jax* 2 Kit #2 (Drop Slot Head)				20" (58 cm)	35" (91 cm)	37.5" (95 cm)	37.5" (95 cm)	127 lbs
MAX JAX* & MAX JAX* 2 HEAD STYLES										
	781382	SS Sleeves	4,500 lbs	4" (100 mm)	36" (900 mm)	N/A				8 lbs
	781383	Ball Trans	1,000 lbs	3/8" (9 mm)	36" (900 mm)					8 lbs
	781394	Rubber Whls	1,000 lbs	4" (100 mm)	36" (900 mm)					8 lbs
	781397	SS Ball Trans	1,000 lbs	3/8" (9 mm)	36" (900 mm)					5 lbs
	781406	AL Roller	4,500 lbs	4" (100 mm)	36" (900 mm)					8 lbs
	781407	SS Roller	2,000 lbs	4" (100 mm)	36" (900 mm)					8 lbs
HEAD STYLES FOR SUMNER'S PRO JACK*, HEAVY DUTY & FOLD-A-JACK* STANDS										
HEAD STYLE		PART #	DESCRIPTION					CAPACITY	PIPE SIZE MAXIMUM	
	780518		Standard Vee Head					2,500 lbs	24" (600 mm)	
	780498		Standard Vee Head w/SS Sleeve							
	780518		Standard Vee Head					1,000 lbs	12" (300 mm)	
	780551		Ball Transfer Head							
	780518		Standard Vee Head							
	780274		Ball Transfer Head (Stainless Steel)							
	780514		Roller Head Assy. w/Aluminum Wheels					2,500 lbs	24" (600 mm)	
	780517		Roller Head Assy. w/SS Wheels							
	780499		Rubber Roller Wheel Head					1,000 lbs	24" (600 mm)	
	780519		Bar Stock Head for Hi Jack					2,000 lbs	24" (600 mm)	
	780944		Bar Stock Head for Low Jack							

CARTS & STORAGE

Cricket™
Grasshopper™
Handi-Bench
Pipe Mac™
Hanger Mac™
Bundle Mac™
Mac Rack I™
Mac Rack II™
Small Double Cylinder Carts
Medium Double Cylinder Carts
Single Cylinder Carts
Double Cylinder Carts



CRICKET™

The Sumner* Cricket™ is a versatile material and pipe cart.

SPECIAL FEATURES:

- Transports 20 ft pipe lengths up to 1,000 lbs
- Comes with ratchet hold-down strap and 16" tubed tires
- Weights only 82 lbs and can be shipped UPS
- Quick handle disconnect for compact storage
- Carries up to 12" diameter pipe
- Also available with Flat Free Tires



SPECIFICATIONS

ITEM #	DESCRIPTION	MODEL #	UPC	MAXIMUM PIPE DIAMETER	LOAD CAPACITY
782699	Cricket™	CRKT	661165826999	12"	1,000 lbs
782685	Cricket™ w/Flat Free Tires	CRKTFF	661165826852	12"	1,000 lbs

GRASSHOPPER™

The Sumner* Grasshopper is a large capacity manual pipe dolly

SPECIAL FEATURES:

- Enables one person to lift 2,000 lbs unassisted
- Special sliding chain block design accommodates long and short loads
- Carries up to 20" diameter pipe, tool boxes, fittings and valves
- Fits through 35" openings
- Large diameter tire allows for construction site mobility
- Chains can be used to lock wheels for security

SPECIFICATIONS

ITEM #	DESCRIPTION	MODEL #	UPC	MAXIMUM PIPE DIAMETER	LOAD CAPACITY
780351	Grasshopper™	ST-401	661165803518	20"	2,000 lbs



HANDI-BENCH



The Sumner* Handi-Bench is a versatile shop table.

SPECIAL FEATURES:

- Tough #9 expanded metal top
- 600 lbs load capacity
- 1" square tube frame
- Collapsible design for storage
- Convenient 36" work height
- Compact and lightweight
- 24" x 40" work surface
- Complete with built-in torch holder
- Optional 8" wheel kit



SPECIFICATIONS

ITEM #	DESCRIPTION	MODEL #	UPC	LOAD CAPACITY
783980	Handi-Bench	HB604	661165839807	600 lbs

PIPE MAC™



783230



The Sumner* Pipe Mac™ is purpose built to transport large pipes and pipe bundles.

SPECIAL FEATURES:

- Transports 2,000 lbs of pipe individually or up to a height of 34"
- Six 6" heavy duty casters
- Center-positioned casters make rolling the Pipe Mac™ easy and enables quick cart rotation for tight turns
- Removable posts for compact storage
- Stacks when not in use
- Simple but rugged attachment prevents pipe from rolling while the Pipe Mac™ is in motion
- Included Vee Attachment easily slips over the four post holders - no tools required



783240

SPECIFICATIONS

ITEM #	DESCRIPTION	MODEL #	UPC	LOAD CAPACITY
783230	Pipe Mac™ w/Vee	PMAC	661165832303	2,000 lbs
OPTIONAL ACCESSORY				
783240	Pipe Mac™ Vee Attachment only	PMACVEE	661165832402	

CARTS & STORAGE

HANGER MAC™



The Sumner* Hanger Mac™ is a patented pipe hanger and transportation solution.

SPECIAL FEATURES:

- Eliminates multiple handling and reduces fabrication transport costs
- Available with or without wire mesh base
- Patented stacking feature: Stack similar carts together or with other Stacking Macs
- Hanger Mac™ cart holds 40 6-8" and 120 2-4" pipe hangers
- Folds for compact storage and transportation without tools



SPECIFICATIONS

ITEM #	DESCRIPTION	MODEL #	UPC
785650	Hanger Mac™ without mesh base	HMACI	661165856507
785651	Hanger Mac™ with mesh base	HMACII	661165856514

BUNDLE MAC™



The Sumner* Bundle Mac™ is designed to transport large quantities of conduit, strut, threaded rod, pvc pipe or copper tubing in one large cradle.

SPECIAL FEATURES:

- Arms fold easily with plunger pins for compact storage
- 1,000 lbs load capacity
- Patented stacking feature: stack similar carts together or with other Stacking Mac Rack products
- Shipped assembled with 6" heavy duty casters
- Durable powder coat finish

SPECIFICATIONS

ITEM #	DESCRIPTION	MODEL #	UPC	LOAD CAPACITY
783320	Bundle Mac™	BMAC	661165833201	1,000 lbs

MAC RACK I™ & MAC RACK II™



The Sumner* Mac Rack™ is a mobile jobsite conduit and pipe storage cart.

SPECIAL FEATURES:

- 1,000 lbs weight capacity
- Double wall square tubing
- Eight storage sections
- Arms fold easily with plunger pins for compact storage
- Shipped assembled with 6" heavy duty casters
- Durable powder coat finish
- Patented stacking feature: Stack similar carts together or with other Stacking Macs
- Mac Rack II™ has a mesh deck for material storage

SPECIFICATIONS

ITEM #	DESCRIPTION	MODEL #	UPC	LOAD CAPACITY
783317	Mac Rack I™	MRACKI	661165833171	1,000 lbs
783299	Mac Rack II™	MRACKII	661165832990	1,000 lbs

CARTS & STORAGE

SMALL DOUBLE CYLINDER CARTS



782426

782428

The Sumner* 209 cylinder carts are rated to carry (2) cylinders up to 9" in diameter.

SPECIAL FEATURES:

- The cylinder carts feature a balanced design for comfortable handling on smooth, level surfaces
- Carts come in a variety of configurations including wheel, accessory and tank support options
- Handle grips offer better control and stability
- Supports a 244-330 CF oxygen tank
- Supports 145 CF acetylene tank
- ** Lifting eye carts comply with ASME B30.20, AWS D14.1 and AISC codes.
- ***Fire-rated wall complies with OSHA 1926.350 & OSHA 1910.253.

SPECIFICATIONS

ITEM #	DESCRIPTION	MODEL #	UPC
782420	Cylinder Cart - 209-10S - 10" wheel	209-10S	661165824209
782421	Cylinder Cart - 209-10SB - 10" wheel	209-10SB	661165824216
782422	Cylinder Cart - 209-10P - 10" wheel	209-10P	661165824223
782424	Cylinder Cart - 209-14S - 14" wheel	209-14S	661165824247
782425	Cylinder Cart - 209-14SB - 14" wheel	209-14SB	661165824254
782426	Cylinder Cart - 209-16P - 16" wheel	209-16P	661165824261
782427	Cylinder Cart - 209-16PB - 16" wheel	209-16PB	661165824278
782428	Cylinder Cart - 209-16F - 16" wheel	209-16F	661165824285
782439** / ***	Cylinder Cart - 209-14SB-LF - 14" wheel	209-14SB-LF	661165824391
782441** / ***	Cylinder Cart - 209-14SB-L - 14" wheel	209-14SB-L	661165824414
782443** / ***	Cylinder Cart - 209-16PB-LF - 16" wheel	209-16PB-LF	661165824438
782444** / ***	Cylinder Cart - 209-16FB-LF - 16" wheel	209-16FB-LF	661165824445

MEDIUM DOUBLE CYLINDER CARTS



The Sumner* 213 cylinder carts are rated to carry (2) cylinders up to 13" in diameter.

SPECIAL FEATURES:

- The cylinder carts feature a balanced design for comfortable handling on smooth, level surfaces
- Carts come in a variety of configurations including wheel, accessory and tank support options
- Handle grips offer better control and stability
- Supports a 244-330 CF oxygen tank
- Supports 145 CF acetylene tank
- Includes Tool Tray
- **Lifting eye carts comply with ASME B30.20, AWS D14.1 and AISC codes
- ***Fire-rated wall complies with OSHA 1926.350 & OSHA 1910.253

SPECIFICATIONS

ITEM #	DESCRIPTION	MODEL #	UPC
782475	Cylinder Cart - 213-25W - 25" wheel	213-25W	661165824759
782480	Cylinder Cart - 213-14S - 14" wheel	213-14S	661165824803
782476** / ***	Cylinder Cart - 213-25WB-LF - 25" wheel	213-25WB-LF	661165824766
782491** / ***	Cylinder Cart - 213-14SB-LF - 14" wheel	213-14SB-LF	661165824919
782493** / ***	Cylinder Cart - 213-14SB-L - 14" wheel	213-14SB-L	661165824933
782495** / ***	Cylinder Cart - 213-16PB-LF - 16" wheel	213-16PB-LF	661165824957
782496** / ***	Cylinder Cart - 213-16FB-LF - 16" wheel	213-16FB-LF	661165824964
782497** / ***	Cylinder Cart - 213-25PB-LF - 25" wheel	213-25PB-LF	661165824971
782482	Cylinder Cart - 213-16P - 16" wheel	213-16P	661165824827
782483	Cylinder Cart - 213-16PB - 16" wheel	213-16PB	661165824834

CARTS & STORAGE

SINGLE CYLINDER CART



The Sumner* 108 cylinder cart is rated to carry (1) cylinder up to 8" in diameter and the Sumner* 112 cylinder cart is rated to carry (1) cylinder up to 12" in diameter.

SPECIAL FEATURES:

- The cylinder carts feature a balanced design for comfortable handling on smooth, level surfaces
- Carts come in a variety of configurations including wheel, accessory and tank support options
- Handle grips offer better control and stability
- Supports 50-80 CF oxygen tank or 40 CF acetylene tank

SPECIFICATIONS

ITEM #	DESCRIPTION	MODEL #	UPC
782375	Cylinder Cart - 108-8S - 8" wheel	108-8S	661165823752
782385	Cylinder Cart - 112-10S - 10" wheel	112-10S	661165823851
782386	Cylinder Cart - 112-10P - 10" wheel	112-10P	661165823868

DOUBLE CYLINDER CART



The Sumner* 207 cylinder cart is rated to carry (2) cylinders up to 7" in diameter and the Sumner* 208 cylinder cart is rated to carry (2) cylinders up to 8" in diameter.

SPECIAL FEATURES:


- The cylinder carts feature a balanced design for comfortable handling on smooth, level surfaces
- Carts come in a variety of configurations including wheel, accessory and tank support options
- Handle grips offer better control and stability
- Supports 50-80 CF oxygen tank or 40 CF acetylene tank

SPECIFICATIONS

ITEM #	DESCRIPTION	MODEL #	UPC
782359	Cylinder Cart - 207-10S - 10" wheel	207-10S	661165823592
782360	Cylinder Cart - 207-8S - 8" wheel	207-8S	661165823608
782379	Cylinder Cart - 208-8S - 8" wheel	208-8S	661165823790
782380	Cylinder Cart - 208-10S - 10" wheel	208-10S	661165823806

HOW TO READ SUMNER* CYLINDER CART PRODUCT DESCRIPTIONS

X X X - X X X X - X X



WHEEL	PART #	DESCRIPTION	DIAMETER	WIDTH	BORE	BEARING	LOAD CAPACITY	FITS CARTS
CYLINDER CART WHEELS								
	779024	Semi-pneumatic	8" (200 mm)	1.75" (44 mm)	0.5" (13 mm)	Powder Metal Bushing	80 lbs	108 207 208
	779031	Semi-pneumatic	8" (200 mm)	2" (50 mm)	0.5" (13 mm)	Steel Bushing	400 lbs	207 208
	779011	Semi-pneumatic	10" (250 mm)	2.75" (70 mm)	5/8" (16 mm)	Bronze Bushing	400 lbs	112 207 208 209
	779027	Pneumatic	10" (250 mm)	3.5" (89 mm)	5/8" (16 mm)	Bronze Bushing	350 lbs	112 209
	779028	Semi-pneumatic	14" (355 mm)	1.75" (44 mm)	5/8" (16 mm)	Bronze Bushing	150 lbs	209 213
	779104	Flat Free	16" (400 mm)	4.8" (120 mm)	1" (25 mm)	Powder Metal Bushing	380 lbs	209 213
	779107	Pneumatic	16" (400 mm)	4.8" (120 mm)	1" (25 mm)	Powder Metal Bushing	380 lbs	209 213
	780521	Pneumatic	25" (50 mm)	4" (100 mm)	1.25" (32 mm)	Bronze Bushing	800 lbs	213
	782575	Steel	25" (50 mm)	2" (50 mm)	1.25" (32 mm)	Bronze Bushing	800 lbs	213

2 = Carries two cylinders 13 = 13" Maximum cylinder diameter 16 = 16" Wheel size F = Flat free tire B = Belly bar L = Lifting eye F = Firewall

SPECIFICATIONS

LIFTS

EL-405 Stacker Lift

Roust-A-Bout™

FAB-MATE™

Short Stack™

1900 Series

2000 Series

2100 Series

2200 Series

2300 Series

2400 Series

2500 Series

2600 Series

Eventer™



EL-405 STACKER LIFT

The Sumner* EL-405 Stacker lift is ideal for warehouse and service departments.

SPECIAL FEATURES:

- Designed for loads up to 400 lbs
- Lifting height of up to 53 in.
- Two speed winch handle allows for onsite flexibility
- Quick action wheel brake immobilizes load
- Large lifting surface for boxes and materials
- Extension strap kit available



SPECIFICATIONS

ITEM #	DESCRIPTION	MODEL #	UPC	LIFTING HEIGHT	LOAD CAPACITY
784650	EL-405 Stacker Lift	EL-405	661165846508	53"	400 lbs
OPTIONAL STACKER LIFT ACCESSORY					
784685	Extension Strap Kit	ESK6600	661165846850		

ROUST-A-BOUT™



The Sumner* Roust-A-Bout™ lift enables one man to lift and place loads in tight locations that would be impossible with other lifts.

SPECIAL FEATURES:

- Designed for loads up to 1,500 lbs
- Rugged 8" casters for horizontal movement
- Vertical adjustments made by 2-winch system allowing for separate operation of load and mast elevation
- Variable 4-speed load winch
- Ideal for use in the shop or on the jobsite
- Quickly breaks down for storage and transportation
- Available in 4 models plus a powder coated or galvanized finish



SPECIFICATIONS

ITEM #	DESCRIPTION	MODEL #	UPC	LIFTING HEIGHT	LOAD CAPACITY
780300	R-100 Roust-A-Bout™	R-100	661165803006	15 FT	1,500 lbs
780301	R-150 Roust-A-Bout™	R-150	661165803013	15 FT	1,500 lbs
780302	R-180 Roust-A-Bout™	R-180	661165803020	18 FT	1,500 lbs
780303	R-250 Roust-A-Bout™	R-250	661165803037	25 FT	1,500 lbs
780195	R-100G Roust-A-Bout™- Galvanized	R-100G	661165801958	15 FT	1,500 lbs
780194	R-150G Roust-A-Bout™- Galvanized	R-150G	661165801941	15 FT	1,500 lbs
780197	R-180G Roust-A-Bout™- Galvanized	R-180G	661165801972	18 FT	1,500 lbs
780196	R-250G Roust-A-Bout™- Galvanized	R-250G	661165801965	25 FT	1,500 lbs
OPTIONAL ROUST-A-BOUT™ ACCESSORIES					
781060	R/Z-100/Z-150 Tee Head Ext.	THE100/150	661165810608		
781061	R/Z-180/Z-200 Tee Head Ext.	THE180/200	661165810615		
781062	R/Z-250 Tee Head Ext.	THE250	661165810622		

FAB-MATE™



The Sumner* FAB-MATE™ is a versatile lift designed so one person can position fittings, align flanges or move plate.

SPECIAL FEATURES:

- Sumner* built winch with lifting capacity up to 1,000 lbs
- Lifting height of up to 7 ft
- Rugged 8" casters for horizontal movement
- Designed for use with the Sumner* Adjust-A-Fit™ and Adjust-A-Flange™

SPECIFICATIONS

ITEM #	DESCRIPTION	MODEL #	UPC	LIFTING HEIGHT	LOAD CAPACITY
783900	FAB-MATE™ Lift	FMATE	661165839005	7 FT	1,000 lbs

SHORT STACK



The Sumner* 2000 Series Short Stack Lifts offer a more compact design without compromising lifting capacity.

SPECIAL FEATURES:

- Designed for loads up to 800 lbs & fits easily through doorways
- Easily flown in using the integrated lifting eye
- Pulley Guard provides 360° of cable protection
- Forks reverse to maximize lifting height
- Plunger pins eliminate extra tools and loose parts
- Quickly breaks down for storage and transportation
- Load cable that feeds inside mast - No more exposed cable just inches away from operator's face
- Multiple accessories available
- Available in 2 models plus a powder coated or galvanized finish

SPECIFICATIONS

ITEM #	DESCRIPTION	MODEL #	UPC	LIFTING HEIGHT	LOAD CAPACITY
784094	2012S Short Stack Lift	2012S	661165840940	12 FT	800 lbs
784085	2016S Short Stack Lift	2016S	661165840858	16 FT	800 lbs
784093	2012S Short Stack Lift - Galvanized	2012SG	661165840933	12 FT	800 lbs
784086	2016S Short Stack Lift - Galvanized	2016SG	661165840865	16 FT	800 lbs
OPTIONAL ACCESSORIES					
783881	Mast Brake Kit	2000MBK	661165838817		
783705	Pipe Cradle (pair)	PCRADLE	661165837056		
783642	Boom Assembly	BOOMA	661165836424		
786320	Tray Assembly	TA	661165863208		
783691	Fork Extension Kit	CFEXTKIT	661165836912		

SERIES 1900



The Sumner* Series 1900 lifts are designed for shipping and receiving, lifting heavy materials on and off shelves and HVAC work.

SPECIAL FEATURES:

- Designed for loads up to 350 lbs or 400 lbs
- Forks reverse to maximize lifting height
- Easily breaks down for transport and storage
- 2-position straddle base
- 5" wheels to transport over rough terrain
- Two-speed winch handle offers leverage and speed
- Available in 2 models



SPECIFICATIONS

ITEM #	DESCRIPTION	MODEL #	UPC	LIFTING HEIGHT	LOAD CAPACITY
782050	Series 1908	1908	661165820508	8 FT	350 lbs
782051	Series 1910	1910	661165820515	10 FT	400 lbs

SERIES 2000



The Sumner* Series 2000 lifts are ideal for wider, heavier loads in the construction and HVAC markets

SPECIAL FEATURES:

- Designed for loads up to 650 lbs, 800 lbs, or 1000 lbs
- Fits easily through doorways
- Easily flown in using the integrated lifting eye
- Pulley Guard provides 360° of cable protection
- Forks reverse to maximize lifting height
- Plunger pins eliminate extra tools and loose parts
- Quickly breaks down for storage and transportation
- Load cable that feeds inside mast - No more exposed cable just inches away from operator's face
- Multiple accessories available
- Available in 3 models plus a powder coated or galvanized finish

SPECIFICATIONS

ITEM #	DESCRIPTION	MODEL #	UPC	LIFTING HEIGHT	LOAD CAPACITY
783700	2010 Material Lift	2010	661165837001	10 FT	1,000 lbs
783701	2015 Material Lift	2015	661165837018	15 FT	800 lbs
783702	2020 Material Lift	2020	661165837025	20 FT	800 lbs
783703	2025 Material Lift	2025	661165837032	25 FT	650 lbs
783223	2010 Material Lift - Galvanized	2010G	661165832235	10 FT	1,000 lbs
783224	2015 Material Lift - Galvanized	2015G	661165832242	15 FT	800 lbs
783228	2020 Material Lift - Galvanized	2020G	661165832280	20 FT	800 lbs
783229	2025 Material Lift - Galvanized	2025G	661165832297	25 FT	650 lbs
OPTIONAL ACCESSORIES					
783881	Mast Brake Kit	2000MBK	661165838817		
783705	Pipe Cradle (pair)	PCRADLE	661165837056		
783642	Boom Assembly	BOOMA	661165836424		
786320	Tray Assembly	TA	661165863208		
783691	Fork Extension Kit	CFEXTKIT	661165836912		

SERIES 2100



The Sumner* Series 2100 Contractor Lifts are ideal for construction, HVAC and industrial work.

SPECIAL FEATURES:

- Designed for loads up to 650 lbs
- Fits easily through doorways
- Easily flown in using the integrated lifting eye
- Pulley Guard provides 360° of cable protection
- Forks reverse to maximize lifting height
- Plunger pins eliminate extra tools and loose parts
- Quickly breaks down for storage and transportation
- Load cable that feeds inside mast - No more exposed cable just inches away from operator's face
- Multiple accessories available
- Available in 3 models plus a powder coated or galvanized finish

SPECIFICATIONS

ITEM #	DESCRIPTION	MODEL #	UPC	LIFTING HEIGHT	LOAD CAPACITY
783650	2112 Contractor Lift	2112	661165836509	12 FT	650 lbs
783651	2118 Contractor Lift	2118	661165836516	18 FT	650 lbs
783652	2124 Contractor Lift	2124	661165836523	24 FT	650 lbs
783225	2112 Contractor Lift - Galvanized	2112G	661165832259	12 FT	650 lbs
783226	2118 Contractor Lift - Galvanized	2118G	661165832266	18 FT	650 lbs
783227	2124 Contractor Lift - Galvanized	2124G	661165832273	24 FT	650 lbs
OPTIONAL ACCESSORIES					
783881	Mast Brake Kit	2000MBK	661165838817		
783881	Mast Brake Kit	2000MBK	661165838817		
783705	Pipe Cradle (pair)	PCRADLE	661165837056		
783642	Boom Assembly	BOOMA	661165836424		
786320	Tray Assembly	TA	661165863208		
783691	Fork Extension Kit	CFEXTKIT	661165836912		
783765	Two Speed Winch Handle Kit (2100 only)	2SWHKIT	661165837650		

SERIES 2200 LIL FT HOISTER™

The Sumner* Series 2200 Lil FT Hoister™ lifts are compact feature rich lifts making them an ideal tool in a variety of applications.

SPECIAL FEATURES:

- Designed for loads up to 300 lbs
- Forks reverse to maximize lifting height
- Plunger pins eliminate extra tools and loose parts
- Two 2" casters permit easy handling of heavy loads
- Quickly breaks down for storage and transportation
- Load strap that feeds inside mast - No more exposed cable just inches away from operator's face
- Highly adaptable with multiple accessories available
- Available in 2 models



SPECIFICATIONS

ITEM #	DESCRIPTION	MODEL #	UPC	LIFTING HEIGHT	LOAD CAPACITY
784308	2208 Lil FT Hoister™	2208	661165843088	8 FT	300 lbs
784310	2210 Lil FT Hoister™	2210	661165843101	10 FT	300 lbs
OPTIONAL ACCESSORIES					
784240	Aluminum Tray	ALTRAY2200	661165842401		
784218	Wheel Brake Assembly	WBA2200	661165842180		
784258	Dually Wheel Kit	DUALWKIT	661165842586		

LIFTS

SERIES 2300

The Sumner* Series 2300 Drywall/HVAC lifts are Ideal for lifting drywall and lighter HVAC ducts.

SPECIAL FEATURES:

- Lifts loads up to 150lbs up to 11' 2-3/4" or 14' 9-3/4"
- Solid, safe construction
- Lightweight - 99lbs
- Two speed winch handle
- Quick, tool free assembly
- One person operation
- Tilts 65 degrees for drywall installation
- Available in 2 models



SPECIFICATIONS

ITEM #	DESCRIPTION	MODEL #	UPC	LI FTING HEIGHT	LOAD CAPACITY
784345	2311 Drywall Li ft	2311	661165843453	11 FT	150 lbs
784330	2311 HVAC Cradle Li ft	2311HVAC	661165843309	11 FT	150 lbs
784346	2315 Drywall Li ft	2315	661165843460	15 FT	150 lbs
784332	2315 HVAC Cradle Li ft	2315HVAC	661165843323	15 FT	150 lbs
OPTIONAL ACCESSORIES					
784355	Drywall Cradle Only	DWCRADLE	661165843552		
784474	HVAC/Electrical Cradle Only	HVACCRADLE	661165844740		
784510	Drywall Li ft Cart	DWCART	661165845105		

SERIES 2400



The Sumner* Series 2400 Contractor Lifts are compact with a rugged design for a variety of construction applications

SPECIAL FEATURES:

- Designed for loads up to 450 lbs
- Easily breaks down to just over 5 ft for easy storage and transportation
- Plunger pins eliminate extra tools and loose parts
- Compact design fits in most vans and SUVs
- Forks reverse to maximize lifting height
- Pulley Guard provides 360° of cable protection
- Load cable that feeds inside mast - No more exposed cable just inches away from operator's face
- Multiple accessories available
- Available in 2 models plus a powder coated or galvanized finish



SPECIFICATIONS

ITEM #	DESCRIPTION	MODEL #	UPC	LIFTING HEIGHT	LOAD CAPACITY
784750	2412 Contractor Li ft	2412	661165847505	12 FT	450 lbs
784751	2416 Contractor Li ft	2416	661165847512	16 FT	450 lbs
784752	2412 Contractor Li ft - Galvanized	2412G	661165847529	12 FT	450 lbs
784753	2416 Contractor Li ft - Galvanized	2416G	661165847536	16 FT	450 lbs
OPTIONAL ACCESSORIES					
784755	Mast Break Kit 2412	SBA2412	661165847550		
784756	Mast Break Kit 2416	SBA2416	661165847567		
784695	Fork Extension Install Kit	FEXTKIT2400	661165846959		
784830	Mast Hold-Down, Bar Type 2412	MHDBAR2412	661165848304		
783705	Pipe Cradle (pair)	PCRADLE	661165837056		
784320	Steel Tray	STRAY2400	661165843200		

SERIES 2500



The Sumner* Series 2500 lift is an inovative counter balance lift that features a compact design.

SPECIAL FEATURES:

- Designed for loads up to 650 lbs, 800 lbs, or 1000 lbs
- Fits easily through doorways
- Easily flown in using the integrated lifting eye
- Pulley Guard provides 360° of cable protection
- Forks reverse to maximize lifting height
- Plunger pins eliminate extra tools and loose parts
- Quickly breaks down for storage and transportation
- Load cable that feeds inside mast - No more exposed cable just inches away from operator's face
- Multiple accessories available

SPECIFICATIONS

ITEM #	DESCRIPTION	MODEL #	UPC	LI FTING HEIGHT	LOAD CAPACITY
786510	Series 2510 Li ft - Galvanized	2510G	661165865103	10 FT	1,000 lbs
786511	Series 2515 Li ft - Galvanized	2515G	661165865110	15 FT	800 lbs
786512	Series 2520 Li ft - Galvanized	2520G	661165865127	20 FT	800 lbs
786513	Series 2525 Li ft - Galvanized	2525G	661165865134	25 FT	650 lbs
OPTIONAL ACCESSORIES					
783705	Pipe Cradle (pair)	PCRADLE	661165837056		
784320	Steel Tray	STRAY2400	661165843200		
786645	Boom Assembly, CB Li ft	BOOMACB	661165866452		
786750	Glass Boom Assembly, CB Li ft	GBACB	661165867503		

SERIES 2600



The Sumner* Series 2600 Big Lift is ideal for any job with confined spaces and large lifting requirements.

SPECIAL FEATURES:

- Designed for loads up to 1,100 lbs
- Forks reverse to maximize lifting height
- Sumner* built 2-speed winch system
- Quickly breaks down for storage and transportation
- Fast adjusting steering handle for centering lift
- Plunger pins eliminate extra tools and loose parts
- Multiple accessories available
- Available in 2 models plus a powder coated or galvanized finish

SPECIFICATIONS

ITEM #	DESCRIPTION	MODEL #	UPC	LIFTING HEIGHT	LOAD CAPACITY
783065	2610 The Big Li ft	2610	661165830651	10 FT	1,100 lbs
783067	2615 The Big Li ft	2615	661165830675	15 FT	1,100 lbs
783066	2610 The Big Li ft - Galvanized	2610G	661165830668	10 FT	1,100 lbs
783068	2615 The Big Li ft - Galvanized	2615G	661165830682	15 FT	1,100 lbs
OPTIONAL ACCESSORIES					
783882	Safety Brake Assy for 2610	SBA2610/10	661165838824		
783883	Safety Brake Assy for 2615	SBA2615/15	661165838831		
783163	Fork Extension Kit, 2600 Series Li fts	FEK2600	661165831634		
784569	Pipe Cradle Assembly, 2600 Li ft (1 Pair)	PCA2600	661165845693		

LIFTS

EVENTER™ SERIES



The Sumner* Eventer™ black bodied lift series is specifically designed to meet the needs of theatrical and entertainment industries.

SPECIAL FEATURES:

- Available accessories for lifting and support speakers, lights and other stage equipment
- Sumner* built winch with lifting capacities from 500 lbs
- Compact design with quick assembly and breakdown
- Forks reverse to maximize lifting height
- Included leveling pads to ensure stability
- Black, anodized aluminum telescoping masts fade out on the stage
- Available in 3 models



SPECIFICATIONS

ITEM #	DESCRIPTION	MODEL #	UPC	LIFTING HEIGHT	LOAD CAPACITY
784760	Eventer™ 16 ft	EV16	661165847604	16 FT	500 lbs
783801	Eventer™ 20 ft	EV20	661165838015	20 FT	800 lbs
783800	Eventer™ 25 ft	EV25	661165838008	25 FT	650 lbs
OPTIONAL EVENTER™ 16 FT ACCESSORIES					
784880	Eventer™ 16 ft boom (fully extended)	B00M16	661165848809		
784915	Eventer™ 16 ft hook block kit	HBK16	661165849158		
784055	Eventer™ 16 ft sound array bar	SAB16	661165840551		
OPTIONAL EVENTER™ 20 FT AND 25 FT ACCESSORIES					
783766	Eventer™ 20 ft And 25 ft Hook Block Kit	HBK20	661165837667		
784060	Eventer™ 20 ft And 25 ft Sound Array Bar	SAB20	661165840605		

OPTIONS FOR SUMNER* LI FTS		
LI FT MODEL	AVAILABLE OPTIONS	
EL-405 STACKER LI ft 	EL-405 Extension Strap Kit - PN 784685 	
ROUST-A-BOUT R-SERIES 	R/Z-100/Z-150 Tee Head Ext. - 781060 R/Z-180/Z-200 Tee Head Ext. - 781061 R/Z-250 Tee Head Ext. - 781062 	Galvanized Finish - R-100G 780195 R-150G 780194 R-180G 780197 R-250G 780196 
SERIES 2000 MATERIAL LI ft 	Cable Stay Brake - PN 783881	
	Pipe Cradle - PN 783705 	Foot Jack - PN 784070 
	Boom Carriage - PN 783642 	Tray - PN 786320 
	Fork Extensions - PN 783691 	

OPTIONS FOR SUMNER* LI FTs		
LI FT MODEL	AVAILABLE OPTIONS	
SERIES 2100 CONTRACTOR LI ft 	Cable Stay Brake - PN 783663	
	Pipe Cradle - PN 783705 	Foot Jack - PN 784070 
	Boom Carriage - PN 783642 	Tray - PN 786320 
	Fork Extensions - PN 783691 	Two Speed Winch Handle Kit - PN 783765 (Factory Installed) 
SERIES 2200 LIL ft HOISTER LI ft 	Aluminum Tray - PN 784240 	Wheel Brake Kit - PN 784218 
	"Dually" Wheel Kit - PN 784258 	
SERIES 2300 DRYWALL / HVAC LI ft 	Drywall Li ft Truck - PN 784510 	

OPTIONS FOR SUMNER* LI FTs		
LI FT MODEL	AVAILABLE OPTIONS	
SERIES 2400 CONTRACTOR LI ft 	Cable Stay Brake - PN 784755	
	Pipe Cradle - PN 783705 	Tray - PN 784320 
	Fork Extensions - PN 784695 	
SERIES 2500 COUNTER WEIGHT LI ft 	Pipe Cradle - PN 783705	
	Tray - PN 786320	
	Boom Assembly - PN 786645 	Glass Boom Assembly- PN 786750 
SERIES 2600 "Axel" the Big LI ft 	Safety Brakes Series 2610- PN 783882 Series 2615- PN 783883	
	Fork Extensions - PN 783163	
	Pipe Cradle - PN 784569	

GANTRIES

GH3/4T Gantry Series

GH2T Gantry Series

GH5T Gantry Series



GANTRIES

GH3/4T



The Sumner* 3/4 Ton Gantry offers an industry leading compact 3-piece design to fit a variety of applications.

SPECIAL FEATURES:

- Designed for loads up to 3/4 metric tons (1,650 lbs)
- Lightweight & portable; aluminum frames & beam
- Quick two-person assembly & pinch point free
- Adjustable span
- Minimum pieces - 2 A-Frames with casters, Trolley, Cross Beam and attaching hardware *Chain hoist not included
- Available with 8" locking casters or 10" flat free double locking casters
- Unassisted height adjustment
- Available in 8 models

SPECIFICATIONS

ITEM #	DESCRIPTION	MODEL #	UPC	LI FTING HEIGHT	LOAD CAPACITY
785301	GH3/4T with 8" Caster & 15 ft Beam	GH3/4T-8x15	661165853018	15 FT	3/4 TON
785303	GH3/4T with 8" Caster & 12 ft Beam	GH3/4T-8X12	661165853032	12 FT	3/4 TON
785305	GH3/4T with 8" Caster & 10 ft Beam	GH3/4T-8x10	661165853056	10 FT	3/4 TON
785307	GH3/4T with 8" Caster & 8 ft Beam	GH3/4T-8x8	661165853070	8 FT	3/4 TON
785300	GH3/4T with 10" Double FF Tires & 15 ft Beam	GH3/4T-10X15	661165853001	15 FT	3/4 TON
785302	GH3/4T with 10" Double FF Tires & 12 ft Beam	GH3/4T-10X12	661165853025	12 FT	3/4 TON
785304	GH3/4T with 10" Double FF Tires & 10 ft Beam	GH3/4T-10X10	661165853049	10 FT	3/4 TON
785306	GH3/4T with 10" Double FF Tires & 8 ft Beam	GH3/4T-10X8	661165853063	8 FT	3/4 TON
OPTIONAL GH3/4T GANTRY ACCESSORIES					
785320	GH3/4T 15 ft Beam Only	3/4TBEAM15	661165853209		
785321	GH3/4T 12 ft Beam Only	3/4TBEAM12	661165853216		
785322	GH3/4T 10 ft Beam Only	3/4TBEAM10	661165853223		
785323	GH3/4T 8 ft Beam Only	3/4TBEAM8	661165853230		
785600	GH3/4T Trolley Assembly	GH3/4TROL	661165856002		

GANTRIES

GH2T



The Sumner* 2 Ton Gantry offers an industry leading compact 3-piece design to fit a variety of applications.

SPECIAL FEATURES:

- Designed for loads up to 2 metric tons (4,400 lbs)
- Lightweight & portable; aluminum frames & beam
- Quick two-person assembly, pinch point free & adjustable span
- Minimum pieces - 2 A-Frames with casters, Trolley, Cross Beam and attaching hardware *Chain hoist not included
- 8" locking casters & available in 4 models

SPECIFICATIONS

ITEM #	DESCRIPTION	MODEL #	UPC	LI FTING HEIGHT	LOAD CAPACITY
785100	GH2T-15 with 15 ft Beam	GH2T-15x15	661165851007	15 FT	2 TON
785101	GH2T-12 with 12 ft Beam	GH2T-12X12	661165851014	12 FT	2 TON
785102	GH2T-10 with 10 ft Beam	GH2T-10x10	661165851021	10 FT	2 TON
785103	GH2T-8 with 8 ft Beam	GH2T-8x8	661165851038	8 FT	2 TON
OPTIONAL GH2T GANTRY ACCESSORIES					
785073	GH2T 15 ft Beam Only	2TBEAM15	661165850734		
785074	GH2T 12 ft Beam Only	2TBEAM12	661165850741		
785075	GH2T 10 ft Beam Only	2TBEAM10	661165850758		
785076	GH2T 8 ft Beam Only	2TBEAM8	661165850765		
785160	GH2T Trolley Assembly	GH2TROL	661165851601		

GH5T



The Sumner* 5 Ton Gantry offers an industry leading compact 3-piece design to fit a variety of applications.

SPECIAL FEATURES:

- Designed for loads up to 5 metric tons (11,000 lbs)
- Lightweight & portable; Aluminum frames & beam
- Quick two-person assembly & pinch point free & adjustable span
- Minimum pieces - (2) A-Frames with casters, Trolley, Cross Beam and attaching hardware *Chain hoist not included
- 8" locking casters & available in 3 models

SPECIFICATIONS

ITEM #	DESCRIPTION	MODEL #	UPC	LIFTING HEIGHT	LOAD CAPACITY
785805	GH5T-15 with 15 ft Beam	GH2T-15x15	661165858051	15 FT	5 TON
785806	GH5T-12 with- 12 ft Beam	GH2T-12X12	661165858068	12 FT	5 TON
785807	GH5T-10 with 10 ft Beam	GH2T-10x10	661165858075	10 FT	5 TON
OPTIONAL GH5T GANTRY ACCESSORIES					
785815	GH5T 15 ft Beam Only	5TBEAM15	661165858150		
785816	GH5T 12 ft Beam Only	5TBEAM12	661165858167		
785817	GH5T 10 ft Beam Only	5TBEAM10	661165858174		
785895	GH5T Trolley Assembly	GH5TROL	661165858952		

CORDS

Royal® Premium Outdoor Extension Cords



ROYAL® PREMIUM OUTDOOR EXTENSION CORDS



Thermoset rubber jacketed cords have superior resistance to high temperature environments without losing the chemical and abrasion resistance. Harsh applications may include heavy industrial work, welding, and metal fabrication.

SPECIAL FEATURES:


- Temperature rating of -40°F to 194°F
- 125 voltage rating
- Abrasion, chemical, and oil resistant
- Common Applications: welder, angle grinder, rotary hammer drill

SPECIFICA-

PART #	WIRE GA/COND	WIRE TYPE	COLOR	125V RATING	LENGTH
3677SW0008	12/3	SJ00W	BLACK	15A	25 FT
3678SW0008	12/3	SJ00W	BLACK	15A	50 FT
3679SW0008	12/3	SJ00W	BLACK	15A	100 FT
3687SW0008	12/3	SJ00W	YELLOW	15A	25 FT
3688SW0008	12/3	SJ00W	YELLOW	15A	50 FT
3689SW0008	12/3	SJ00W	YELLOW	15A	100 FT

MATERIAL HANDLING

Pallet Jacks
6 Pac Mac™
10 Pac Mac™
Caddy Mac™ 1
Caddy Mac™ 2
Caddy Mac™ 3
Spool Mac™
Handi Mac™
Stor Mac™ 60
Stor Mac™ 48
Stor Mac™ 30
Tainer Mac™ 60
Tainer Mac™ 40
Tainer Mac™ 30
KD Tainer Mac™ 60
KD Tainer Mac™ 45
KD Tainer Mac™ 30
Weldbox™ 3617
Weldbox™ 2812
Weldbox™ 2008
Bi-Fold Cabinet
Two Door Cabinet
Piano Boxes
Field Office
Compact Chest
Mini Compact Chest



PALLET JACKS



779765



779766

The Sumner* low profile 20" or 27" pallet jack will handle heavy lifting for you with it's 2.5" low profile fork height allowing for easy engagement of most pallets.

SPECIAL FEATURES:

- 6,600 lbs weight capacity
- Three-function handle controls raising, lowering and neutral
- Welded all-steel frame and tough powder coat finish provides maximum durability and protection
- Minimum Fork height of 2.5"
- Maximum lift height of 6.25"
- 180° turning radius
- 2-1/2 inch low profile allows for easy engagement of pallets

SPECIFICATIONS

ITEM #	DESCRIPTION	MODEL #	UPC	LOAD CAPACITY
779765	27"x48" Pallet Jack	PJ27	661164797657	6,600 lbs
779766	20"x48" Pallet Jack	PJ20	661164797664	6,600 lbs

MATERIAL HANDLING

6 PAC MAC™



PM06

Mobile wire dispensing cart.

SPECIAL FEATURES:

- Stores in one-third the space of conventional dispensers
- Reel Spindles fold and lock for convenient storage
- Fits through 30" doorway
- Two 10" wheels with locking 8" caster for easy maneuverability
- Welded wire guides for easy payoff
- Stores up to (6) 2,500 ft (18" diameter) of wire



SPECIFICATIONS

ITEM #	DESCRIPTION	MODEL #	UPC
783350	6 PACK MAC™	PM06	661165833508

10 PAC MAC™



PM10

Mobile wire dispensing cart.

SPECIAL FEATURES:

- Handle/Guide loop position controlled by plunger: 4-positions, no loose parts
- Spindles fold up and lock
- Mast swivels 360 degrees, but can be locked in a fixed position
- Stores up to (10) 2500 ft Spools (18" diameter) of wire
- 4-heavy duty, 8" locking casters
- Feed handle and guide loops are built into one part



SPECIFICATIONS

ITEM #	DESCRIPTION	MODEL #	UPC
783366	10 PACK MAC™	10PMAC	661165833669

CADDY MAC™



CADDY MAC™ spool and wire transport dolly.

SPECIAL FEATURES:

- Made in America
- Removable spindles swing out for convenient loading of wire spools
- Unique spindle locking system means no loose pieces
- Rugged 8" wheels for easy transportation



SPECIFICATIONS

ITEM #	DESCRIPTION	MODEL #	UPC
783398	CADDY MAC™ #1	CMAC1	661165833980
783395	CADDY MAC™ #2	CMAC2	661165833959
783400	CADDY MAC™ #3	CMAC3	661165834000
OPTIONAL CADDY MAC™ ACCESSORY			
783490	HANDI MAC™ WIRE DISPENSER	HANDMAC	661165834901

SPOOL MAC™



Security Storage Cabinet

SPECIAL FEATURES:

- Made in America
- Tall steel frame construction
- 10" wheels for easy transport over rough terrain
- Rollers on spool arm allow for smooth reel rotation and easy payoff
- No loose pieces to account for
- Folding design allows for compact storage
- Fits through 32" doorways

SPECIFICATIONS

ITEM #	DESCRIPTION	MODEL #	UPC
783444	SPOOL MAC™	SMAC	661165834444

MATERIAL HANDLING

STORE MAC™

SM60



SM30



Security Storage Cabinet

SPECIAL FEATURES:

- Made in America
- Four 6" heavy duty casters (standard)
- For high visibility storage
- Reinforced frame and door
- Removable shelves
- Lockable doors
- Load capacity 1,500 lbs

SM48



SPECIFICATIONS

ITEM #	DESCRIPTION	MODEL #	UPC	HEIGHT	WIDTH	DEPTH	WEIGHT
784920	STOR MAC™ 60	SMAC60	661165849202	58.5"	62.5"	32"	362 lbs
785921	STOR MAC™ 48	SMAC48	661165859218	58"	51.5"	33.75"	310 lbs
785920	STOR MAC™ 30	SMAC30	661165859201	58"	31.5"	33.75"	210 lbs

TAINER MAC™

TM60B



A Mobile, heavy-duty stacking container.

SPECIAL FEATURES:

- Made in America
- Transports 1,500 lbs of material
- Large storage capacity
- Four 6" heavy duty lockable casters
- Posts for stacking and steering
- Stacks with other Sumner* Stacking Macs
- Knockdown version breaks down for easy storage

TM30B



TM45B



SPECIFICATIONS

ITEM #	DESCRIPTION	MODEL #	UPC	HEIGHT	WIDTH	DEPTH	WEIGHT
784990	TAINER MAC™ 60	TM60B	661165849905	40"	32"	56"	200 lbs
784989	TAINER MAC™ 40	TM45B	661165849899	37"	30"	45"	190 lbs
784988	TAINER MAC™ 30	TM30B	661165849882	37"	30"	30"	145 lbs
KNOCKDOWN TAINER MAC™							
784987	KD TAINER MAC™ 60	KM60	661165849785	40"	32"	56"	200 lbs
784986	KD TAINER MAC™ 45	KM45	661165849868	40"	30"	45.5"	190 lbs
784985	KD TAINER MAC™ 30	KM30	661165849851	40"	30"	30"	145 lbs

MATERIAL HANDLING

WELDBOX™

WB3617



The ideal storage chest for all welders and electricians.

SPECIAL FEATURES:

- Two-point latching system requires only one lock
- Caster ready
- 16-gauge steel construction
- Reinforced frame and door
- Power-coat finish for superior durability and corrosion resistance

WB2812



WB2008



SPECIFICATIONS

ITEM #	DESCRIPTION	MODEL #	UPC	HEIGHT	WIDTH	DEPTH	WEIGHT
779928	WELDBOX™ 3617	WB3617		17"	36"	22.5"	97.9 lbs
779911	WELDBOX™ 2812	WB2812		12"	28.375"	11"	30.8 lbs
779910	WELDBOX™ 2008	WB2008		8.5"	20.125"	9.5"	12.1 lbs

STORAGE CABINETS

CB603065

CB602460

The Southwire™ storage cabinets have heavy duty shelves and large vertical storage area, you can easily organize and secure your tools.

SPECIAL FEATURES:

- Recessed locking system for protection against theft with one-time lock installation
- Heavy-duty 16-gauge steel construction with fully arc-welded seams
- Powder-coat finish for superior durability and corrosion resistance
- The Southwire™ Bi-Fold Cabinet includes casters



SPECIFICATIONS

ITEM #	DESCRIPTION	MODEL #	UPC	HEIGHT	WIDTH	DEPTH	WEIGHT
598227	Bi-Fold Cabinet	CB603065	032886959943	65"	120"	14"	470 lbs
598228	Two-Door Cabinet	CB602460	032886959950	60"	60"	24"	385 lbs

MATERIAL HANDLING

PIANO BOX

PB603049



PB603034



Piano Boxes feature shelves, an interior storage grid for hanging items, gas spring guards to protect springs from shifting-load damage and at-a-glance easy access for small, big and in-between tools, equipment and supplies. With 3 size options available, this box is ideal for storage and security on the jobsite, workshop or in the plant.

SPECIAL FEATURES:

- Recessed locking system for protection against theft with one-time lock installation
- Heavy-duty 16-gauge steel construction with fully arc-welded seams
- Powder-coat finish for superior durability and corrosion resistance
- Four-way caster ready skids allow access from any side, making it easier and faster to transport (Casters not included)
- Gas spring guards to prevent damage from shifting loads



PB483048

SPECIFICATIONS

ITEM #	DESCRIPTION	MODEL #	UPC	HEIGHT	WIDTH	DEPTH	WEIGHT
598224	Piano Box	PB603049	032886959912	48.5"	60"	30"	337 lbs
598223	Piano Box	PB483048	032886959905	48"	48"	30"	287 lbs
598222	Piano Box	PB603034	032886959899	34"	60"	30"	282 lbs

FIELD OFFICE



F0604482

Field office offers a large workstation with shelved storage and a single locking point, allowing you to control and secure any jobsite.

SPECIAL FEATURES:

- Field office offers a large workstation with shelved storage and a single locking point, allowing you to control and secure any jobsite.
- Heavy-duty 16-gauge steel construction with fully arc-welded seams
- Powder-coat finish for superior durability and corrosion resistance
- Four-way caster ready skids allow access from any side, making it easier and faster to transport (Casters not included)
- Dual gas springs for smooth, one-handed lift, one spring locks securely in place
- Adjustable and removable split shelves let you organize your storage in the lower cabinets

SPECIFICATIONS

ITEM #	DESCRIPTION	MODEL #	UPC	HEIGHT	WIDTH	DEPTH	WEIGHT
598225	Field Office	F0604482	032886959929	82"	60"	44"	678 lbs

MATERIAL HANDLING

COMPACT CHEST

CC482423



The Southwire™ compact chests are highly mobile storage solution that stores easily in about any location.

SPECIAL FEATURES:

- Recessed locking system for protection against theft with one-time lock installation
- Heavy-duty 16-gauge steel construction with fully arc-welded seams
- Powder-coat finish for superior durability and corrosion resistance
- Four-way caster ready skids allow access from any side, making it easier and faster to transport (Casters not included)
- The Mini Compact Chest includes a built-in tool tray




SPECIFICATIONS

ITEM #	DESCRIPTION	MODEL #	UPC	HEIGHT	WIDTH	DEPTH	WEIGHT
598226	Compact Chest	CC482423	032886959936	22.5"	48"	24"	145 lbs
630360	Mini Compact Chest	CC191932	032886963612	19"	19"	32"	73 lbs

HOISTS

Sumner fts new line of Hoists offer an innovative, heavy-duty, manual design to tackle your toughest lifts up to 20 tons! This new line of Lever and Chain Block Hoists also offers a premium option that includes a single fused brake design and zinc phosphate load chain for superior corrosion resistance. Each hoist also comes with an easily removable top hook and hard-steel load sheave rollers. All of Sumner fts Hoists meet ANSI/ASME, OSHA and CE Hoisting Standards with our premium models being serviceable for your safety.



LEVER HOIST



Sumner fits Lever Hoists arm you with the strength you need to lift, move and hold heavy materials on a jobsite or in a work shop! Sumner Lever Hoists all come with a steel construction and 360° ratchet with short strokes. Available in 1/4 to 6 ton lifting weight capacities.

SPECIAL FEATURES:

- Meet all ANSI/ASME, OSHA and CE Hoisting Standards
- Top Hook is easily removable
- Hard Steel Load Sheave Rollers
- 1.5x Safety Tested

SPECIFICATIONS

ITEM #	STOCK #	DESCRIPTION	LIFTING WEIGHT CAPACITY
787536	LH025C05	1/4 Ton Lever Hoist with 5 ft Chain Fall	1/4 TON
787537	LH025C10	1/4 Ton Lever Hoist with 10 ft Chain Fall	1/4 TON
787538	LH025C15	1/4 Ton Lever Hoist with 15 ft Chain Fall	1/4 TON
787539	LH050C05	1/2 Ton Lever Hoist with 5 ft Chain Fall	1/2 TON
787540	LH050C10	1/2 Ton Lever Hoist with 10 ft Chain Fall	1/2 TON
787541	LH050C15	1/2 Ton Lever Hoist with 15 ft Chain Fall	1/2 TON
787542	LH075C05	3/4 Ton Lever Hoist with 5 ft Chain Fall	3/4 TON
787543	LH075C10	3/4 Ton Lever Hoist with 10 ft Chain Fall	3/4 TON
787544	LH075C15	3/4 Ton Lever Hoist with 15 ft Chain Fall	3/4 TON
787545	LH075C20	3/4 Ton Lever Hoist with 20 ft Chain Fall	3/4 TON
787546	LH150C05	1-1/2 Ton Lever Hoist with 5 ft Chain Fall	1-1/2 TON
787547	LH150C10	1-1/2 Ton Lever Hoist with 10 ft Chain Fall	1-1/2 TON
787548	LH150C15	1-1/2 Ton Lever Hoist with 15 ft Chain Fall	1-1/2 TON
787549	LH150C20	1-1/2 Ton Lever Hoist with 20 ft Chain Fall	1-1/2 TON
787550	LH300C05	3 Ton Lever Hoist with 5 ft Chain Fall	3 TON
787551	LH300C10	3 Ton Lever Hoist with 10 ft Chain Fall	3 TON
787552	LH300C15	3 Ton Lever Hoist with 15 ft Chain Fall	3 TON
787553	LH300C20	3 Ton Lever Hoist with 20 ft Chain Fall	3 TON
787554	LH600C05	6 Ton Lever Hoist with 5 ft Chain Fall	6 TON
787555	LH600C10	6 Ton Lever Hoist with 10 ft Chain Fall	6 TON
787556	LH600C15	6 Ton Lever Hoist with 15 ft Chain Fall	6 TON
787557	LH600C20	6 Ton Lever Hoist with 20 ft Chain Fall	6 TON

PREMIUM LEVER HOISTS



Sumner lifts Premium Lever Hoists offer an innovative and heavy-duty design to tackle your toughest lifts of various sizes! Our premium lever hoists include a single fused brake design and zinc phosphate load chain for superior corrosion resistance. Available in .8 to 9 ton lifting weight capacities.

SPECIAL FEATURES:

- No Preload Required
- Meet all ANSI/ASME, OSHA and CE Hoisting Standards
- Top Hook is easily removable
- Hard Steel Load Sheave Rollers
- 1.5x Safety Tested
- Unique zinc phosphate chain design

SPECIFICATIONS

ITEM #	STOCK #	DESCRIPTION	LI FTING WEIGHT CAPACITY
787480	PLH080C05	.8 Ton Lever Hoist with 5 ft Chain Fall	.8 TON
787481	PLH080C10	.8 Ton Lever Hoist with 10 ft Chain Fall	.8 TON
787482	PLH080C15	.8 Ton Lever Hoist with 15 ft Chain Fall	.8 TON
787483	PLH080C20	.8 Ton Lever Hoist with 20 ft Chain Fall	1 TON
787484	PLH100C05	1 Ton Lever Hoist with 5 ft Chain Fall	1 TON
787485	PLH100C10	1 Ton Lever Hoist with 10 ft Chain Fall	1 TON
787486	PLH100C15	1 Ton Lever Hoist with 15 ft Chain Fall	1 TON
787487	PLH100C20	1 Ton Lever Hoist with 20 ft Chain Fall	1 TON
787488	PLH160C05	1.6 Ton Lever Hoist with 5 ft Chain Fall	1.6 TON
787489	PLH160C10	1.6 Ton Lever Hoist with 10 ft Chain Fall	1.6 TON
787490	PLH160C15	1.6 Ton Lever Hoist with 15 ft Chain Fall	1.6 TON
787491	PLH160C20	1.6 Ton Lever Hoist with 20 ft Chain Fall	1.6 TON
787496	PLH320C05	3.2 Ton Lever Hoist with 5 ft Chain Fall	3.2 TON
787497	PLH320C10	3.2 Ton Lever Hoist with 10 ft Chain Fall	3.2 TON
787498	PLH320C15	3.2 Ton Lever Hoist with 15 ft Chain Fall	3.2 TON
787499	PLH320C20	3.2 Ton Lever Hoist with 20 ft Chain Fall	3.2 TON
787500	PLH630C05	6.3 Ton Lever Hoist with 5 ft Chain Fall	6.3 TON
787501	PLH630C10	6.3 Ton Lever Hoist with 10 ft Chain Fall	6.3 TON
787502	PLH630C15	6.3 Ton Lever Hoist with 15 ft Chain Fall	6.3 TON
787503	PLH630C20	6.3 Ton Lever Hoist with 20 ft Chain Fall	6.3 TON
787504	PLH900C05	9 Ton Lever Hoist with 5 ft Chain Fall	9 TON
787505	PLH900C10	9 Ton Lever Hoist with 10 ft Chain Fall	9 TON
787506	PLH900C15	9 Ton Lever Hoist with 15 ft Chain Fall	9 TON
787507	PLH900C20	9 Ton Lever Hoist with 20 ft Chain Fall	9 TON

PREMIUM LEVER HOIST WITH OVERLOAD PROTECTION

Sumner lifts Premium Lever Hoists with Overload Protection offers an innovative and heavy-duty design to tackle your toughest lifts of various sizes! Our premium lever hoists include a single fused brake design and zinc phosphate load chain for superior corrosion resistance. Available in .8 to 9 ton lifting weight capacities.

SPECIAL FEATURES:

- No Preload Required
- Meet all ANSI/ASME, OSHA and CE Hoisting Standards
- Top Hook is easily removable
- Hard Steel Load Sheave Rollers
- 1.5x Safety Tested
- Unique zinc phosphate chain design

SPECIFICATIONS

ITEM #	STOCK #	DESCRIPTION	LIFTING WEIGHT CAPACITY
787508	PLH080C05W0	.8 Ton Lever Hoist with 5 ft Chain Fall w/ Overload Protection	.8 TON
787509	PLH080C10W0	.8 Ton Lever Hoist with 10 ft Chain Fall w/ Overload Protection	.8 TON
787510	PLH080C15W0	.8 Ton Lever Hoist with 15 ft Chain Fall w/ Overload Protection	.8 TON
787511	PLH080C20W0	.8 Ton Lever Hoist with 20 ft Chain Fall w/ Overload Protection	.8 TON
787512	PLH100C05W0	1 Ton Lever Hoist with 5 ft Chain Fall w/ Overload Protection	1 TON
787513	PLH100C10W0	1 Ton Lever Hoist with 10 ft Chain Fall w/ Overload Protection	1 TON
787514	PLH100C15W0	1 Ton Lever Hoist with 15 ft Chain Fall w/ Overload Protection	1 TON
787515	PLH100C20W0	1 Ton Lever Hoist with 20 ft Chain Fall w/ Overload Protection	1 TON
787516	PLH160C05W0	1.6 Ton Lever Hoist with 5 ft Chain Fall w/ Overload Protection	1.6 TON
787517	PLH160C10W0	1.6 Ton Lever Hoist with 10 ft Chain Fall w/ Overload Protection	1.6 TON
787518	PLH160C15W0	1.6 Ton Lever Hoist with 15 ft Chain Fall w/ Overload Protection	1.6 TON
787519	PLH160C20W0	1.6 Ton Lever Hoist with 20 ft Chain Fall w/ Overload Protection	1.6 TON
787524	PLH320C05W0	3.2 Ton Lever Hoist with 5 ft Chain Fall w/ Overload Protection	3.2 TON
787525	PLH320C10W0	3.2 Ton Lever Hoist with 10 ft Chain Fall w/ Overload Protection	3.2 TON
787526	PLH320C15W0	3.2 Ton Lever Hoist with 15 ft Chain Fall w/ Overload Protection	3.2 TON
787527	PLH320C20W0	3.2 Ton Lever Hoist with 20 ft Chain Fall w/ Overload Protection	3.2 TON
787528	PLH630C05W0	6.3 Ton Lever Hoist with 5 ft Chain Fall w/ Overload Protection	6.3 TON
787529	PLH630C10W0	6.3 Ton Lever Hoist with 10 ft Chain Fall w/ Overload Protection	6.3 TON
787530	PLH630C15W0	6.3 Ton Lever Hoist with 15 ft Chain Fall w/ Overload Protection	6.3 TON
787531	PLH630C20W0	6.3 Ton Lever Hoist with 20 ft Chain Fall w/ Overload Protection	6.3 TON
787532	PLH900C05W0	9 Ton Lever Hoist with 5 ft Chain Fall w/ Overload Protection	9 TON
787533	PLH900C10W0	9 Ton Lever Hoist with 10 ft Chain Fall w/ Overload Protection	9 TON
787534	PLH900C15W0	9 Ton Lever Hoist with 15 ft Chain Fall w/ Overload Protection	9 TON
787535	PLH900C20W0	9 Ton Lever Hoist with 20 ft Chain Fall w/ Overload Protection	9 TON



CHAIN BLOCK HOISTS



Sumner lifts Chain Block Hoists are designed to thrive in light industrial applications work with capacities ranging from 1/2-10 tons. Sumner lifts Chain Block Hoist build on our legacy of reliable vertical lifting.

SPECIAL FEATURES:

- Meet all ANSI/ASME, OSHA and CE Hoisting Standards
- Top Hook is easily removable
- Hard Steel Load Sheave Rollers
- 1.5x Safety Tested

SPECIFICATIONS

ITEM #	STOCK #	DESCRIPTION	LI FTING WEIGHT CAPACITY
787558	CB050C10	1/2 Ton Chain Hoist with 10 ft Chain Fall	1/2 TON
787559	CB050C15	1/2 Ton Chain Hoist with 15 ft Chain Fall	1/2 TON
787560	CB050C20	1/2 Ton Chain Hoist with 20 ft Chain Fall	1/2 TON
787561	CB050C30	1/2 Ton Chain Hoist with 30 ft Chain Fall	1/2 TON
787562	CB100C10	1 Ton Chain Hoist with 10 ft Chain Fall	1 TON
787563	CB100C15	1 Ton Chain Hoist with 15 ft Chain Fall	1 TON
787564	CB100C20	1 Ton Chain Hoist with 20 ft Chain Fall	1 TON
787565	CB100C30	1 Ton Chain Hoist with 30 ft Chain Fall	1 TON
787566	CB150C10	1-1/2 Ton Chain Hoist with 10 ft Chain Fall	1-1/2 TON
787567	CB150C15	1-1/2 Ton Chain Hoist with 15 ft Chain Fall	1-1/2 TON
787568	CB150C20	1-1/2 Ton Chain Hoist with 20 ft Chain Fall	1-1/2 TON
787569	CB150C30	1-1/2 Ton Chain Hoist with 30 ft Chain Fall	1-1/2 TON
787570	CB200C10	2 Ton Chain Hoist with 10 ft Chain Fall	2 TON
787571	CB200C15	2 Ton Chain Hoist with 15 ft Chain Fall	2 TON
787572	CB200C20	2 Ton Chain Hoist with 20 ft Chain Fall	2 TON
787573	CB200C30	2 Ton Chain Hoist with 30 ft Chain Fall	2 TON
787574	CB300C10	3 Ton Chain Hoist with 10 ft Chain Fall	3 TON
787575	CB300C15	3 Ton Chain Hoist with 15 ft Chain Fall	3 TON
787576	CB300C20	3 Ton Chain Hoist with 20 ft Chain Fall	3 TON
787577	CB300C30	3 Ton Chain Hoist with 30 ft Chain Fall	3 TON
787578	CB500C10	5 Ton Chain Hoist with 10 ft Chain Fall	5 TON
787579	CB500C15	5 Ton Chain Hoist with 15 ft Chain Fall	5 TON
787580	CB500C20	5 Ton Chain Hoist with 20 ft Chain Fall	5 TON
787581	CB500C30	5 ton Chain Hoist with 30 ft Chain Fall	5 TON
787582	CB1KC10	10 ton Chain Hoist with 10 ft Chain Fall	10 TON
787583	CB1KC15	10 ton Chain Hoist with 15 ft Chain Fall	10 TON
787584	CB1KC20	10 ton Chain Hoist with 20 ft Chain Fall	10 TON
787585	CB1KC30	10 ton Chain Hoist with 30 ft Chain Fall	10 TON

PREMIUM CHAIN BLOCK HOISTS

Sumner lifts Premium Chain Block Hoists Lift low headroom design is ideal for your 1/4-20 ton lifting needs. Meets all ANSI/ASME, OSHA and CE Hoisting Standards.

SPECIAL FEATURES:

- Top Hook is easily removable
- Hard Steel Load Sheave Rollers
- 1.5x Safety Tested
- Unique zinc phosphate chain design

SPECIFICATIONS

ITEM #	STOCK #	DESCRIPTION	LIFTING WEIGHT CAPACITY
787400	PCB025C10	1/4 Ton Chain Hoist with 10 ft Chain Fall	1/4 TON
787401	PCB025C15	1/4 Ton Chain Hoist with 15 ft Chain Fall	1/4 TON
787402	PCB025C20	1/4 Ton Chain Hoist with 20 ft Chain Fall	1/4 TON
787403	PCB025C30	1/4 Ton Chain Hoist with 30 ft Chain Fall	1/4 TON
787404	PCB050C10	1/2 Ton Chain Hoist with 10 ft Chain Fall	1/2 TON
787405	PCB050C15	1/2 Ton Chain Hoist with 15 ft Chain Fall	1/2 TON
787406	PCB050C20	1/2 Ton Chain Hoist with 20 ft Chain Fall	1/2 TON
787407	PCB050C30	1/2 Ton Chain Hoist with 30 ft Chain Fall	1/2 TON
787408	PCB100C10	1 Ton Chain Hoist with 10 ft Chain Fall	1 TON
787409	PCB100C15	1 Ton Chain Hoist with 15 ft Chain Fall	1 TON
787410	PCB100C20	1 Ton Chain Hoist with 20 ft Chain Fall	1 TON
787411	PCB100C30	1 Ton Chain Hoist with 30 ft Chain Fall	1 TON
787412	PCB150C10	1-1/2 Ton Chain Hoist with 10 ft Chain Fall	1-1/2 TON
787413	PCB150C15	1-1/2 Ton Chain Hoist with 15 ft Chain Fall	1-1/2 TON
787414	PCB150C20	1-1/2 Ton Chain Hoist with 20 ft Chain Fall	1-1/2 TON
787415	PCB150C30	1-1/2 Ton Chain Hoist with 30 ft Chain Fall	1-1/2 TON
787416	PCB200C10	2 Ton Chain Hoist with 10 ft Chain Fall	2 TON
787417	PCB200C15	2 Ton Chain Hoist with 15 ft Chain Fall	2 TON
787418	PCB200C20	2 Ton Chain Hoist with 20 ft Chain Fall	2 TON
787419	PCB200C30	2 Ton Chain Hoist with 30 ft Chain Fall	2 TON
787420	PCB300C10	3 Ton Chain Hoist with 10 ft Chain Fall	3 TON
787421	PCB300C15	3 Ton Chain Hoist with 15 ft Chain Fall	3 TON
787422	PCB300C20	3 Ton Chain Hoist with 20 ft Chain Fall	3 TON
787423	PCB300C30	3 Ton Chain Hoist with 30 ft Chain Fall	3 TON
787424	PCB500C10	5 Ton Chain Hoist with 10 ft Chain Fall	5 TON
787425	PCB500C15	5 Ton Chain Hoist with 15 ft Chain Fall	5 TON
787426	PCB500C20	5 Ton Chain Hoist with 20 ft Chain Fall	5 TON
787427	PCB500C30	5 Ton Chain Hoist with 30 ft Chain Fall	5 TON




PREMIUM CHAIN BLOCK HOISTS CONT.



SPECIFICATIONS

ITEM #	STOCK #	DESCRIPTION	LI FTING WEIGHT CAPACITY
787428	PCB1KC10	10 Ton Chain Hoist with 10 ft Chain Fall	10 TON
787429	PCB1KC15	10 Ton Chain Hoist with 15 ft Chain Fall	10 TON
787430	PCB1KC20	10 Ton Chain Hoist with 20 ft Chain Fall	10 TON
787431	PCB1KC30	10 Ton Chain Hoist with 30 ft Chain Fall	10 TON
787432	PCB1.5KC10	15 Ton Chain Hoist with 10 ft Chain Fall	15 TON
787433	PCB1.5KC15	15 Ton Chain Hoist with 15 ft Chain Fall	15 TON
787434	PCB1.5KC20	15 Ton Chain Hoist with 20 ft Chain Fall	15 TON
787435	PCB1.5KC30	15 Ton Chain Hoist with 30 ft Chain Fall	15 TON
787436	PCB2KC10	20 Ton Chain Hoist with 10 ft Chain Fall	20 TON
787437	PCB2KC15	20 Ton Chain Hoist with 15 ft Chain Fall	20 TON
787438	PCB2KC20	20 Ton Chain Hoist with 20 ft Chain Fall	20 TON
787439	PCB2KC30	20 Ton Chain Hoist with 30 ft Chain Fall	20 TON

PREMIUM CHAIN BLOCK HOISTS WITH OVERLOAD PROTECTION



Sumner lifts Premium Chain Block Hoists Lift low headroom design is ideal for your 1/4-20 ton lifting needs. Meets all ANSI/ASME, OSHA and CE Hoisting Standards.

SPECIAL FEATURES:

- Top Hook is easily removable
- Hard Steel Load Sheave Rollers
- 1.5x Safety Tested
- Unique zinc phosphate chain design

SPECIFICATIONS

ITEM #	STOCK #	DESCRIPTION	LIFTING WEIGHT CAPACITY
787448	PCB100C10W0	1 Ton Chain Hoist with 10 ft Chain Fall w/ Overload Protection	1 TON
787449	PCB100C15W0	1 Ton Chain Hoist with 15 ft Chain Fall w/ Overload Protection	1 TON
787450	PCB100C20W0	1 Ton Chain Hoist with 20 ft Chain Fall w/ Overload Protection	1 TON
787451	PCB100C30W0	1 Ton Chain Hoist with 30 ft Chain Fall w/ Overload Protection	1 TON
787452	PCB150C10W0	1-1/2 Ton Chain Hoist with 10 ft Chain Fall w/ Overload Protection	1-1/2 TON
787453	PCB150C15W0	1-1/2 Ton Chain Hoist with 15 ft Chain Fall w/ Overload Protection	1-1/2 TON
787454	PCB150C20W0	1-1/2 Ton Chain Hoist with 20 ft Chain Fall w/ Overload Protection	1-1/2 TON
787455	PCB150C30W0	1-1/2 Ton Chain Hoist with 30 ft Chain Fall w/ Overload Protection	1-1/2 TON
787456	PCB200C10W0	2 Ton Chain Hoist with 10 ft Chain Fall w/ Overload Protection	2 TON
787457	PCB200C15W0	2 Ton Chain Hoist with 15 ft Chain Fall w/ Overload Protection	2 TON
787458	PCB200C20W0	2 Ton Chain Hoist with 20 ft Chain Fall w/ Overload Protection	2 TON
787459	PCB200C30W0	2 Ton Chain Hoist With 30 ft Chain Fall w/ Overload Protection	2 TON
787460	PCB300C10W0	3 Ton Chain Hoist With 10 ft Chain Fall w/ Overload Protection	3 TON
787461	PCB300C15W0	3 Ton Chain Hoist With 15 ft Chain Fall w/ Overload Protection	3 TON
787462	PCB300C20W0	3 Ton Chain Hoist With 20 ft Chain Fall w/ Overload Protection	3 TON
787463	PCB300C30W0	3 Ton Chain Hoist With 30 ft Chain Fall w/ Overload Protection	3 TON
787464	PCB500C10W0	5 Ton Chain Hoist With 10 ft Chain Fall w/ Overload Protection	5 TON
787465	PCB500C15W0	5 Ton Chain Hoist With 15 ft Chain Fall w/ Overload Protection	5 TON
787426	PCB500C20W0	5 Ton Chain Hoist With 20 ft Chain Fall w/ Overload Protection	5 TON
787427	PCB500C30W0	5 Ton Chain Hoist With 30 ft Chain Fall w/ Overload Protection	5 TON
787428	PCB1KC10W0	10 Ton Chain Hoist With 10 ft Chain Fall w/ Overload Protection	10 TON
787429	PCB1KC15W0	10 Ton Chain Hoist With 15 ft Chain Fall w/ Overload Protection	10 TON
787430	PCB1KC20W0	10 Ton Chain Hoist With 20 ft Chain Fall w/ Overload Protection	10 TON
787431	PCB1KC30W0	10 Ton Chain Hoist With 30 ft Chain Fall w/ Overload Protection	10 TON

PREMIUM CHAIN BLOCK HOISTS WITH OVERLOAD PROTECTION CONT.



SPECIFICATIONS

ITEM #	STOCK #	DESCRIPTION	LI FTING WEIGHT CAPACITY
787432	PCB1.5KC10W0	15 Ton Chain Hoist With 10 ft Chain Fall w/ Overload Protection	15 TON
787433	PCB1.5KC15W0	15 Ton Chain Hoist With 15 ft Chain Fall w/ Overload Protection	15 TON
787434	PCB1.5KC20W0	15 Ton Chain Hoist With 20 ft Chain Fall w/ Overload Protection	15 TON
787475	PCB1.5KC30W0	15 Ton Chain Hoist with 30 ft Chain Fall w/ Overload Protection	15 TON
787476	PCB2KC10W0	20 Ton Chain Hoist with 10 ft Chain Fall w/ Overload Protection	20 TON
787477	PCB2KC15W0	20 Ton Chain Hoist with 15 ft Chain Fall w/ Overload Protection	20 TON
787478	PCB2KC20W0	20 Ton Chain Hoist with 20 ft Chain Fall w/ Overload Protection	20 TON
787479	PCB2KC30W0	20 Ton Chain Hoist with 30 ft Chain Fall w/ Overload Protection	20 TON

HOISTS | Premium Chain Block Hoists
with Overload Protection

SOUTHWIRE WARRANTY

WHAT DOES THIS WARRANTY COVER?

FIVE-YEAR LIMITED WARRANTY ON CONTRACTOR EQUIPMENT

Under Southwire's Contractor Equipment 5-Year Limited Warranty, Southwire Company, LLC warrants that all Southwire Contractor Equipment will be free from manufacturer defects for a period of five (5) years from the date of the original end user's purchase. However, electrical components and consumable parts such as ropes, blades, dies, draw studs, grips, are excluded from this 5-Year Limited Warranty and are subject to the One-Year warranty terms. Under this 5-Year Limited Warranty, the following are also excluded and Southwire Company, LLC will have no liability for any of the following: normal wear and tear resulting from product use and damage arising out of misuse, abuse, modification, and improper product maintenance. This warranty also does not cover Southwire Contractor Equipment products that have been modified by any party other than Southwire Company, LLC or its authorized third party designee. This 5-Year Limited Warranty is not transferrable to or enforceable by any person other than the product's original end user.

THREE-YEAR LIMITED WARRANTY ON MATERIAL BOXES

Under Southwire's Material Boxes 3-Year Limited Warranty, Southwire Company, LLC warrants that all Southwire Material Boxes will be free from manufacturer defects for a period of three (3) years from the date of the original end user's purchase. Under this Three-Year Limited Warranty for Material Boxes, the following are excluded and Southwire Company, LLC will have no liability for any of the following: normal wear and tear resulting from product use and damage arising out of misuse, abuse, modification, and improper product maintenance. This warranty also does not cover Material Boxes that have been modified by any party other than Southwire Company, LLC or its authorized third party designee. This 3-Year Limited Warranty is not transferrable to or enforceable by any person other than the product's original end user.

ONE-YEAR LIMITED WARRANTY ON ELECTRICAL COMPONENTS AND CONSUMABLE PARTS (WITH 5-YEAR WARRANTY)

Under Southwire's 1-Year Limited Warranty, Southwire Company, LLC warrants that all electrical components and consumable parts such as ropes, blades, dies, draw studs, grips will be free from manufacturer defects for a period of one-year from the date of the original end user's purchase. Under this 1-Year Limited Warranty, Southwire Company, LLC will have no liability for any of the following: normal wear and tear resulting from product use and damage arising out of misuse, abuse, modification, and improper product maintenance. This warranty also does not cover Southwire electrical components and consumable parts that have been modified by any party other than Southwire Company, LLC or its authorized third party designee. This 1-Year Limited Warranty is not transferrable to or enforceable by any person other than the product's original end user.

ONE-YEAR LIMITED WARRANTY (STAND ALONE)

Under Southwire's 1-Year Limited Warranty, Southwire Company, LLC warrants that this product will be free from manufacturer defects for a period of one-year from the date of the original end user's purchase. Under this 1-Year Limited Warranty, Southwire Company, LLC will have no liability for any of the following: normal wear and tear resulting from product use and damage arising out of misuse, abuse, modification, and improper product maintenance. This warranty also does not cover Southwire products that have been modified by any party other than Southwire Company, LLC or its authorized third party designee. This 1-Year Limited Warranty is not transferrable to or enforceable by any person other than the product's original end user.

WARRANTY ON SOUTHWIRE ELECTRICIAN'S NON-ELECTRONIC HAND TOOLS

Southwire Company, LLC warrants this product to be free from defects in materials and workmanship for the life of the product. This warranty does not cover normal wear and tear resulting from product use, nor does it cover damage arising out of misuse, abuse, modification, and/or improper maintenance of the product. If the product breaches this warranty, Southwire will replace the product free of charge. If Southwire no longer manufactures the product, then it will, at its option, replace the nonconforming product with a substantially similar Southwire product or refund the purchase price.

SOUTHWIRE MAKES NO WARRANTY THAT THE PRODUCT WILL BE MERCHANTABLE OR FIT FOR ANY PARTICULAR PURPOSE. SOUTHWIRE MAKES NO OTHER WARRANTY, EXPRESSED OR IMPLIED, OTHER THAN THE WARRANTY SPECIFICALLY SET FORTH HEREIN. SOUTHWIRE WILL NOT BE LIABLE FOR ANY INCIDENTAL, CONSEQUENTIAL, INDIRECT, SPECIAL, OR PUNITIVE DAMAGES FOR ANY BREACH OF THIS WARRANTY.

This warranty is void if this product is used for rental purposes. No product reseller is authorized to extend any other warranty on Southwire's behalf relating to this product, and no such reseller warranty will be binding on Southwire. If the product needs to be serviced, please contact the Customer Service Department at 855-SW.TOOLS (855-798-6657) to obtain a return authorization from Southwire. The sender is responsible for all shipping, freight, insurance, and packaging costs associated with sending a product to Southwire. Southwire will not be responsible for lost or damaged products returned for service or returned under this warranty. All products returned to Southwire under this warranty should be mailed to:

Southwire Tools & Assembled Products Division
840 Old Bremen Road
Carrollton, GA 30117
Phone Number: 1.855.SW.TOOLS

Exclusion of Incidental, Consequential, Indirect, Special and Punitive Damages

SOUTHWIRE MAKES NO WARRANTY THAT SOUTHWIRE CONTRACTOR EQUIPMENT PRODUCTS WILL BE MERCHANTABLE OR FIT FOR ANY PARTICULAR PURPOSE. SOUTHWIRE MAKES NO OTHER WARRANTY, EXPRESSED OR IMPLIED, OTHER THAN THE RELEVANT WARRANTY SPECIFICALLY SET FORTH IN THIS WARRANTY SECTION. SOUTHWIRE WILL NOT BE LIABLE FOR ANY INCIDENTAL, CONSEQUENTIAL, INDIRECT, SPECIAL, OR PUNITIVE DAMAGES FOR ANY BREACH OF THIS LIMITED LIFETIME WARRANTY.

SOUTHWIRE WARRANTY

Some states do not allow the exclusion or limitation of incidental or consequential damages, so the above limitation or exclusion may not apply to you.

Southwire Tools & Assembled Products Division
Attn: Product Returns
840 Old Bremen Road
Carrollton, GA 30117
Phone Number: 1.855.SW.TOOLS

WARRANTY CLAIM INFORMATION/HOW DO YOU GET SERVICE?

For all warranty, customer service, and product return authorizations and inquiries, please contact Southwire fts Tools & Assembled Products at:

Southwire Tools & Assembled Products
Attention Product Returns
840 Old Bremen Road
Carrollton, GA, 30117
Phone Number: 1.855.SW.TOOLS

1. All warranty claims must be approved by Southwire fts Tools & Assembled Products Warranty Department prior to return of product. If Southwire determines that a product is defective, Southwire will, at its option, repair or replace defective products or defective product components, free of charge.
2. Upon approval, Southwire will issue a Product Return Authorization Form which will include instructions on how and where to return the product. The product serial number and the original date of delivery must be set forth on the Product Return Authorization Form.
3. Southwire will cover standard freight charges (Courier Ground rate) incurred in connection with products that Southwire ultimately determines to be defective.
4. All defective components and defective products that Southwire replaces under these Warranties will become Southwire's property and will be retained by Southwire.

REPAIR YOUR PRODUCT WHEN IT IS OUT OF WARRANTY

Southwire is happy to provide information about where a purchaser can send a product for repair at consumers ft own expense, please contact 1.855.SW.TOOLS or visit www.southwiretools.com/tools/home.do for more information about servicing for Southwire Products.

This warranty is void if this product is used for rental purposes. No product reseller is authorized to extend any other warranty on Southwire fts behalf relating to this product, and no such reseller warranty will be binding on Southwire. If the product needs to be serviced, please contact the Customer Service Department at 855-SW.TOOLS (855-798-6657) to obtain a return authorization from Southwire. The sender is responsible for all shipping, freight, insurance, and packaging costs associated with sending a product to Southwire. Southwire will not be responsible for lost or damaged products returned for service or returned under this warranty. All products returned to Southwire under this warranty should be mailed to:

Southwire Tools & Assembled Products Division
840 Old Bremen Road
Carrollton, GA 30117
Phone Number: 1.855.SW.TOOLS

WARRANTY | Southwire Warranty

SUMNER WARRANTY

WHAT DOES THIS WARRANTY COVER?

LIMITED LIFETIME WARRANTY ON SUMNER EQUIPMENT

Under Sumner's Equipment Limited Lifetime Warranty, Sumner Manufacturing Co., LLC warrants that all Sumner Equipment will be free from manufacturer defects for a Limited Lifetime except for moving parts deemed consumables from the date of the original end user's purchase. Products deemed as consumable products, components and parts such as steel cables, rollers, bearings, wheels, lift mast sections components are excluded from this Limited Lifetime Warranty and are subject to One - Year Limited Warranty terms. Sumner electrical components are excluded from this Limited Lifetime Warranty and are subject to One -Year Limited Warranty terms. Under this Limited Lifetime Warranty, the following are also excluded, and Sumner will have no liability for any of the following: normal wear and tear resulting from product use and damage arising out of misuse, abuse, modification, and improper product maintenance. This warranty also does not cover Sumner's Equipment products that have been modified by any party other than Sumner or its authorized third-party designee. This Limited Lifetime Warranty is not transferrable to or enforceable by any person other than the product's original end user.

THREE-YEAR LIMITED WARRANTY ON PALLET JACKS AND HYDRAULIC TOOLS

Under Sumner's 3-Year Limited Warranty, Sumner Manufacturing Co., LLC warrants that all Sumner Pallet Jacks and Hydraulic Tools will be free from manufacturer defects for a period of three (3) years from the date of the original end user's purchase. Under this Three-Year Limited Warranty for Pallet Jacks and Hydraulic Tools, the following are excluded and Sumner Manufacturing Co., LLC will have no liability for any of the following: normal wear and tear resulting from product use and damage arising out of misuse, abuse, modification, and improper product maintenance. This warranty also does not cover Pallet Jacks and Hydraulic Tools that have been modified by any party other than Sumner Manufacturing Co., LLC or its authorized third-party designee. This 3-Year Limited Warranty is not transferrable to or enforceable by any person other than the product's original end user.

ONE-YEAR LIMITED WARRANTY ON ALL PRODUCTS

Under Sumner's 1-Year Limited Warranty, Sumner Manufacturing Co., LLC warrants that all products will be free from manufacturer defects for a period of one-year from the date of the original end user's purchase. Under this 1-Year Limited Warranty, Sumner Manufacturing Co., LLC will have no liability for any of the following: normal wear and tear resulting from product use and damage arising out of misuse, abuse, modification, and improper product maintenance. This warranty also does not cover Sumner Equipment that has been modified by any party other than Sumner Manufacturing Co., LLC or its authorized third-party designee. This 1-Year Limited Warranty is not transferrable to or enforceable by any person other than the product's original end user.

EXCLUSION OF INCIDENTAL, CONSEQUENTIAL, INDIRECT, SPECIAL AND PUNITIVE DAMAGES SUMNER MANUFACTURING CO. LLC MAKES NO WARRANTY THAT SUMNER MANUFACTURING CO. LLC PRODUCTS WILL BE MERCHANTABLE OR FIT FOR ANY PARTICULAR PURPOSE. SUMNER MAKES NO OTHER WARRANTY, EXPRESSED OR IMPLIED, OTHER THAN THE RELEVANT WARRANTY SPECIFICALLY SET FORTH IN THIS WARRANTY SECTION. SOUTHWIRE WILL NOT BE LIABLE FOR ANY INCIDENTAL, CONSEQUENTIAL, INDIRECT, SPECIAL, OR PUNITIVE DAMAGES FOR ANY BREACH OF THIS LIMITED LIFETIME WARRANTY.

Some states do not allow the exclusion or limitation of incidental or consequential damages, so the above limitation or exclusion may not apply to you.

WARRANTY CLAIM INFORMATION/HOW DO YOU GET SERVICE?

For all warranty, customer service, and product return authorizations and inquiries, please contact Sumner at:

SUMNER WARRANTY

Sumner Manufacturing Co., LLC
7514 Alabonson Road
Houston, Texas 77088
Phone Number: 1.281.999.6900

Sumner – Canada
75 Saltman Drive, Unit 5
Cambridge, Ontario N3H 4R7
Phone Number: 1.519.653.5300

Sumner – U.K.
Unit 3 Kepton Road
Keytec 7 Business Park
Persore Worcestershire
WR10 2TA, UK
Phone Number: +44 (0) 1386 556278

Sumner – Netherlands
Handelsweg 26
3881LS Putten
The Netherlands
Phone Number: +31 (0) 85 489 0284

1. All warranty claims must be approved by Sumner's Warranty Department prior to return of product. If Sumner determines that a product is defective, Sumner will, at its option, repair or replace defective products or defective product components, free of charge.
2. Upon approval, Sumner will issue a Product Return Authorization Form which will include instructions on how and where to return the product. The product serial number and the original date of delivery must be set forth on the Product Return Authorization Form.
3. Sumner will cover standard freight charges (Courier Ground rate) incurred in connection with products that Sumner ultimately determines to be defective.
4. All defective components and defective products that Sumner replaces under these Warranties will become Sumner's property and will be retained by Sumner.

Repairing Your Product When it is Out of Warranty

Sumner is happy to provide information about where a purchaser can send a product for repair at consumers ft own expense, please contact 1.281.999.6900 or visit www.sumner.com for more information about servicing for Sumner Products.

WARRANTY | Southwire Warranty



SUMNER*



A Southwire Company

PRODUCT CATALOG

GET SOCIAL WITH US:



/SOUTHWIRETOOLS
/SOUTHWIRETOOLSLATINO



@SOUTHWIRETOOLS



@SOUTHWIRETOOLS
@SUMNERCO



SOUTHWIRETOOLS

Sumner - U.S. | 281-999-6900

Sumner - Canada | (519) 653-5300

Sumner - U.K. | +44 (0) 1386 556278

Sumner - Netherlands | +31 (0) 85 489 0284