

PRODUCT DATASHEET

F T5 8W CW BL

SYLVANIA Preheat T5 | Miniature preheat T5 lamps for magnetic ballast systems with starter use



Product features

- 6 inch lamps available in Cool White phosphor
- 9 inch lamps available in Cool White phosphor
- 12 inch lamps available in Soft (Warm) White and Cool White phosphor
- 21 inch lamps available in Soft (Warm) White and Cool White phosphor



TECHNICAL DATA

Additional product data

Base type	G5
Mercury content	2.5 mg
Design / version	Basic T5 short tubular, G5 base
Ordering Abbreviation	F8T5CWBL
Abbrev. With Packaging Info.	F8T5CWBL 6/CS 1/SKU
SKU UPC	0046135235269
NAED	23526
General Description	8W, 12" MOL, T5, preheat fluorescent lamp with miniature bi-pin bases, Utility Cool White phosphor, 4000K color temperature, 80 CRI, blister pack

Electrical data

Nominal Wattage	8.00 W
-----------------	--------

Photometrical data

Lumens	430 lm
Efficacy	53 lm/W
Color Temperature/CCT	4000 K
Color Rendering Index (CRI)	80
Light color	840

Dimensions & Weight

Overall length	288.29 mm
Diameter	0.63 in
Tube diameter	16 mm
Product weight	0.06 lb

Materials & Colors

Bulb shape	T5
------------	----

Lifespan

Service life	4500 h
Average Rated Life (hr)	7500

Logistical data

SKU Qty	1
---------	---

Case Qty	6
Case Length (in)	15.500
Case Width (in)	4.500
Case Depth (in)	2.375
Case Cube (ft)	0.096
Case Weight (lbs)	0.674
SKU UPC	0046135235269
Pallet Qty	2,964

Safety advice

- Starter required for operation.
- Operate on magnetic ballasts.
- Contains Mercury – Dispose of according to Local, State or Federal laws

DISCLAIMER

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.