



Rotating Wall Pack (Single & Double Module)


Applications:

- Recessed Downlighting
- New/Remodel Construction
- Residential/Commercial Lighting

Product Information:

- 0-10V dimmable integrated driver
- Durable die-cast aluminum housing
- IP-67 fully waterproof for hosing down.






Air Vents



Waterproof



Mount Hook



LED Chips

-  150 Watt
-  19500 Lumens
-  120-277V Dimmable
-  Integrated LED
-  IP67 Rated
-  12-2770V

RETAIL READY STAND OUT PACKAGING



Packaging subject to size change based on product size





ROUND UFO HIGHBAY

NW-UFO-
NW-UFO

LUMENS	3600
WATTAGE	25W
VOLTAGE	120-277V
TRIM	BZ-Bronze
COLOR TEMP	30/40/50K
BEAM ANGLE	35° Tilt
ROTATION	360°
LIFE HOURS	50,000
CRI	80
DIMMABLE	Yes

