



MASTERING OFFICE VERSATILITY

DUAL SELECTABLE VOLUMETRIC TROFFER AND DOOR KIT

The Volumetric Troffer and Door Kit series of luminaires from LEDVANCE offer the ultimate flexibility for both new construction and retrofit installations. Available in 1x4, 2x2, and 2x4 configurations. Choose between 3 different CCT options and a wide array of power inputs all in the same product. The luminaires can operate from 120 to 347 volts input, and are constructed from robust powder coated steel. This series also features a driver with a 12V auxiliary output and is designed with an optional sensor base to support field installable PIR sensors. The luminaires are DLC 5.1 standard and are available with optional emergency back-up batteries.

VALUE CLASS

VOLUMETRIC TROFFER



RETROFIT DOOR KIT



For more information, visit www.ledvanceUS.com/luminaires

LEDVANCE LLC
181 Ballardvale Street, Suite 203
Wilmington, MA 01887 USA
Phone 1-800-LIGHTBULB
(1-800-544-4828)

ORDERING GUIDE

VOLUME	6A	/	S0XX	UNH	D	8	SC7	/	XX	U	/	WH	/	E
PRODUCT NAME	GENERATION		SELECTABLE WATTAGE	VOLTAGE	DIMMING	CRI	SELECTABLE CCT		SIZE	MOUNTING		COLOR		OPTION
VOLUME = Volumetric Troffer RDORKIT= Retrofit Door Kit	6A = Generation 6A		S032 = 20/24/28/32W S044 = 24/32/39/44W S069 = 49/59/69W	UNH = 120-347V	D = 0-10V Dimming	8 = 80	SC7= 3500/ 4000/5000K		14 = 1x4 22 = 2x2 24 = 2x4	U = 15/16" and 9/16" T-grid ceilings		WH = White		Option = Emergency Battery Back-up

CONTRACTOR BENEFITS

- Lumen and CCT selectability offer the ultimate in versatility for a large variety of applications and installations
- Sensor base built into each fixture enables the simple field installation of optional PIR motion sensors

FEATURES

- Wattage selectability:
 - 1x4: 20/24/28/32 wattage selectable
 - 2x2: 20/24/28/32 wattage selectable
 - 2x4: 24/32/39/44 wattage selectable
 - 2x4: 49/59/69 wattage selectable
- All versions are 3500/4000/5000K CCT Selectable
- 120-347V input
- Field installable PIR sensors
- Up to 125 LPW
- DLC 5.1
- Ideal in retrofit and new construction applications
- Driver includes 12V auxiliary output
- Optional flange kits and surface mount kits available
- Optional emergency backup battery
- Compatible with field installable LINK™ components

OPTIONAL LEDVANCE LINK™ ACCESSORIES

Field Installable components compatible with Volumetric Troffer and Retrofit Door Kit



OR



62631

Bluetooth® Connectivity

62632

Bluetooth® Connectivity Plus
Daylight/Motion Sensors

62633



62631
Spec Sheet



62632 + 62633
Spec Sheet



SCAN TO FOLLOW US
ON SOCIAL MEDIA

LEDVANCE is a registered trademark. All other trademarks are those of their respective owners. Specifications subject to change without notice.



Volumetric Troffer
Spec Sheet



Retrofit Door Kit
Spec Sheet



Volumetric Troffer
Install Guide



Retrofit Door Kit
Install Guide